


Multilayer Diplexer
For LTE / 5GHz

DPX Series 1.0x0.5mm [EIA 0402] TYPE

P/N: **DPX105950DT-6012A2**

DPX105950DT-6012A2

SHAPES AND DIMENSIONS



Dimensions (mm)

L	W	T	а	b	С	d
1.00	0.50	0.33	0.30	0.20	0.10	0.12
+/-0.05	+/-0.05	Max	+/-0.10	+/-0.10	+/-0.10	+/-0.07

Terminal functions

(1)	Common Port				
(2)	GND				
(3)	High-Band Port				
(4)	Low-Band Port				

TERMINATION FINISH

Material
Sn plate

DPX105950DT-6012A2

ELECTRICAL CHARACTERISTICS

(Measurement)

Low-Band

Parameter	Eroguo	nev	/MH-/	TDK Spec		
rarameter	Frequency (MHz)			Min.	Тур.	Max.
Insertion Loss (dB)	2400	to	2500	•	0.37	0.50
Insertion Loss (dB)	2400	to	2500	-	-	0.60
(–40 to +85 °C)						
Return Loss@Low-Band (dB)	2400	to	2500	10	22	-
Attenuation (dB)	4800	to	6000	23	29.0	-
	7200	to	7500	23	29.0	-
Characteristic Impedance (ohm)				50	(Nomi	nal)

 $Ta = +25 + /-5 ^{\circ}C$

High-Band

Parameter	Freque	nov	/N/U-/	T	OK Sp	ec
raiailletei	rreque	псу	(1411 12)	Min.	Тур.	Max.
Insertion Loss (dB)	4900	to	5950	ı	0.56	0.80
Insertion Loss (dB)	4900	to	5950	-	-	1.00
(-40 to +85 °C)						
Return Loss@High-Band (dB)	4900	to	5950	10	15	-
Attenuation (dB)	30	to	2400	25	29	-
	2400	to	2500	32	41	-
	2500	to	2690	23	29	-
	9800	to	11900	20	30	-
Characteristic Impedance (ohm)		•		50	(Nomi	nal)

 $Ta = +25 + /-5 ^{\circ}C$



DPX105950DT-6012A2

ELECTRICAL CHARACTERISTICS

(Measurement)

Common

Parameter	Eroguo	nev	/N/LI-/\	TI	OK Sp	ес
Farameter	Freque	псу	(141112)	Min.	Тур.	Max.
Return Loss (dB)	2400	to	2500	10	22	-
(Common Port)	4900	to	5950	10	15	-
Characteristic Impedance (ohm)				50	(Nomi	nal)

 $Ta = +25 + /-5 ^{\circ}C$

MAXIMUM RATINGS


Parameter	TDK Spec	Conditions			
Operating temperature (°C)				–40 to +85 °C	
Storage temperature (°C)				–40 to +85 °C	
Power Handling (W) *1	Frequency (MHz)				
Common Port	2400	to	2500	1	CW
	4900	to	5950	1	CW
Low-Band	2400	to	2500	1	CW
High-Band	4900	to	5950	1	CW
Human Body Model: HBM	@Each Port (V)		+/-1000	100pF / 1500ohm	
Machine Model : MM	@Each Port (V)			+/-150	200pF / 0ohm
Charged Device Model : CDM	@Each Port (V)			+/-500	Humidity: 60%RH max

*1: Refer to 3GPP TS 38.101-1 V15.2.0




DPX105950DT-6012A2

FREQUENCY CHARACTERISTICS




DPX105950DT-6012A2

RECOMMENDED LAND PATTERN



unit: mm

EVALUATION BOARD



Material & Layer	Thickness
Copper Surface Pattern	0.035 mm
FR-4	0.10 mm
	0.018 mm
FR-4	0.30 mm
Copper Bottom GND	0.035 mm


- * Line width should be designed to match 50 ohm characteristic impedance depending on PCB material and thickness.
- ** The position of the throuh hole which have possibility of influence to the prerformance are indicated by dimension line.

ENVIRONMENT INFORMATION

RoHS Statement RoHS Compliance

TDK Corporation

RECOMMENDED REFLOW PROFILE



t: Time

	Drobe	acting	Soldering						
Preheating			Critical zon	e (T3 to T4)	Peak				
Tei	Temp. Time		Temp.	Time	Temp. Time				
T1	T2 t1 T3 t2		t2	T4	t3 *				
150°C	200°C	60 to 120sec	217°C	60 to 120sec	240 to 260°C	30 sec Max			

* t3 : Time within 5°C of actual peak temperature The maximum number of reflow is 3.


Note: Lead free solder is recommended.


Recommended solder is Sn-3.0Ag-0.5Cu. (M705 by Senju Metal Industry)

DPX105950DT-6012A2

PACKAGING STYLE

Reel Dimensions





Dimensions (mm)

	Α	В	C	D	Е	F	G	Н	J	K	t
I	0.62	1.12	8.0	3.5	1.75	2.0	2.0	4.0	1.5	0.37	0.2
L	+/-0.05	+/-0.05	+/-0.2	+/-0.05	+/-0.1	+/-0.05	+/-0.05	+/-0.05	+0.1/-0	MAX	+/-0.05

STANDARD PACKAGE QUANTITY
(pieces/reel)
10,000



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

↑ REMINDERS

The products listed on this specification sheet are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property. Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this specification sheet.

- 1. Aerospace/Aviation equipment
- 2. Transportation equipment (cars, electric trains, ships, etc.)
- 3. Medical equipment
- 4. Power-generation control equipment
- 5. Atomic energy-related equipment
- 6. Seabed equipment
- 7. Transportation control equipment
- 8. Public information-processing equipment
- 9. Military equipment
- 10. Electric heating apparatus, burning equipment
- 11. Disaster prevention/crime prevention equipment
- 12. Safety equipment
- 13. Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/equipment or providing backup circuits, etc., to ensure higher safety.