

PLUG:

MQ-212-031-161-41WS RECEPTACLE: MQ-222-031-2G3-4500 PLUG: MP-211-031-161-41WS RECEPTACLE: MP-221-031-2G3-4500 **PLUG** RECEPTACLE XXX-XXX-XXX-XXXX-XXX SERIES .050" Low Profile Metal I/O Connector MQ .050" Low Profile Metal I/O Connector MP .050" Low Profile Plastic I/O Connector MP .050" Low Profile Plastic I/O Connector (MQ & MP mate with MP, MQ, MR, MS receptacles) (MQ & MP mate with MP, MQ, MR, MS plugs) BODY 2-Row (Sizes 9 thru 37) 2-Row (Sizes 9 thru 37) 3 3-Row (Size 51) 3 3-Row (Size 51) BODY STYLE: BODY STYLE: 2 Plug, straight, with ears Receptacle, straight, with ears BODY MATERIAL: BODY MATERIAL: Polyphenylene Sulfide (MP only) Polyphenylene Sulfide (MP only) Polyphenylene Sulfide with electroless nickel shell Polyphenylene Sulfide with electroless nickel shell Polyphenylene Sulfide with electrodeposited Polyphenylene Sulfide with electrodeposited cadmium shell cadmium shell X Polyphenylene Sulfide with hard anodized Polyphenylene Sulfide with hard anodized black shell black shell Pure Electro-Deposited Aluminum Pure Electro-Deposited Aluminum Zinc Nickel Plating Zinc Nickel Plating K Nickel Polymer Plating Nickel Polymer Plating SIZE XXX 009, 015, 021, 025, 031, 037, 051 XXX 009, 015, 021, 025, 031, 037, 051 CONTACTS TYPE CONTACTS/TERMINATIONS: TYPE CONTACTS/TERMINATIONS: Pin, straight, 26 awg solder cup Socket, straight, 26 awg solder cup Pin, straight, 24 awg solder cup Socket, straight, 24 awg solder cup Pin, straight, .109" Lead Length (.018 dia) SEE NOTE 1
Pin, straight, .125" Lead Length (.018 dia) SEE NOTE 1
Pin, straight, .140" Lead Length (.018 dia) SEE NOTE 1 Socket, straight, 109" Lead Length (.018 dia) Socket, straight, .125" Lead Length (.018 dia) Socket, straight, .140" Lead Length (.018 dia) 1D 2D 2E 1E 2F Pin, straight, .150" Lead Length (.018 dia) SEE NOTE 1 22 Socket, straight, .150" Lead Length (.018 dia) Pin, straight, .156" Lead Length (.018 dia) SEE NOTE 1 2G Socket, straight, .156" Lead Length (.018 dia) Socket, straight, 172" Lead Length (.018 dia) Socket, straight, 187" Lead Length (.018 dia) Socket, straight, .250" Lead Length (.018 dia) Socket, straight, .375" Lead Length (.018 dia) Pin, straight, .172" Lead Length (.018 dia) SEE NOTE 1 2H Pin, straight, .187" Lead Length (.018 dia) SEE NOTE 1
Pin, straight, .250" Lead Length (.018 dia) SEE NOTE 1
Pin, straight, .375" Lead Length (.018 dia) SEE NOTE 1 2J 23 2K 1K Socket, straight, .500" Lead Length (.018 dia) Pin, straight, .500" Lead Length (.018 dia) SEE NOTE 1 2L Pin, straight, 1.000" Lead Length (.018 dia) SEE NOTE 1 Socket, straight, 1.000" Lead Length (.018 dia) Pin, straight, crimped wire 24 Socket, straight, .500" Lead Length (.018 dia) SEE NOTE 1 Socket, straight, 1.000" Lead Length (.018 dia) SEE NOTE 1 26 Socket, straight, crimped wire PLATING OPTIONS: PLATING OPTIONS: 50 u" Au contacts (crimp wire) 50 u" Au contacts (crimp wire) 50 μ" Au contacts (solder cup, pigtail)
50 μ" Au contacts; Sn/Pb alloy terminations ⊠ 50 µ" Au contacts (solder cup, pigtail) 50 u" Au contacts; Sn/Pb alloy terminations ⊠ 50 u" Au contacts; SAC305 terminations 50 u" Au contacts; SAC305 terminations HARDWARE STYLE OF HARDWARE: STYLE OF HARDWARE: None None Two fixed jacknut assemblies (62*) Two fixed jacknut assemblies (62*) Two turning jackscrews, allen head, Two turning jackscrews, allen head, retaining ring (81*) retaining ring (81*) Two long turning jackscrews, allen head, retaining ring (82*)
Two turning jackscrews, slot head, Two long turning jackscrews, allen head, retaining ring (82*)
Two turning jackscrews, slot head, 42 retaining ring (83*) retaining ring (83*) Two long turning jackscrews, slot head, Two long turning jackscrews, slot head, retaining ring (84*) retaining ring (84*) Two turning jackscrews, allen head, captivated** (85*) Two turning jackscrews, allen head, captivated** (85*) Keying hardware, see options below. (Body material 2, 3 and 4 only) 99 Keying hardware, see options below. (Body 99 material 2, 3 and 4 only) POLARIZATION / WIRING POLARIZATION / WIRING OΩ None 00 None For wiring codes, see page MA-3 & MA-4 XX For wiring codes, see page MA-3 & MA-4 **OPTIONS** KSXX Two turning jackscrews. See page MA-6 for keying KSXX Two turning jackscrews and interfacial sealing gasket. options See page MA-6 for keying options KPXX Two fixed jacknuts. See page MA-6 for keying KPXX Two fixed jacknuts and interfacial sealing gasket. See page MA-6 for keying options

= Captive hardware is factory installed and non-removable.

NOTE 1 = The leads on these contacts are soft copper

suitable for forming.