





Long-Ranger Computing Counter


DIMENSIONS (INCHES/MILLIMETERS)








PANEL CUTOUT SHOWING DISTANCE BETWEEN ADJACENT CUTOUTS.



TERMINAL WIRING: INDICATING MODEL



The 366C Directly Replaces 366B & 366A.

Based on a powerful built-in microcomputer, the compact 366 is the most versatile and cost-effective counter ATC has ever built. No industrial counter has ever achieved a higher level of reliability and ruggedness than the 366. It has no moving parts in its electronic logic circuits, only plug-in circuit boards which are computer-tested for reliability and assembled virtually without hand wiring. Its few mechanical components have been selected for reliable service; long life relays with heavy-duty contacts and rotary set point selector switches with extremely low wear characteristics.

CONTACT BOUNCE AND NOISE IMMUNITY: No industrial counter offers greater immunity to noise and contact bounce than the 366. Most noise encountered in typical industrial environments is blocked by such design features as full-wave bridges and a transformer power supply... so effectively that the 366 does not have to be shielded. Furthermore the 366's microcomputer employs redundant sampling logic to detect and reject any noise pulse that manages to penetrate its defenses. Through the same powerful technique, the microcomputer also detects and rejects even severe contact bounce. As a result, the 366 maintains absolute count accuracy and is virtually immune to false starts and reset, even in difficult industrial environments.

COMPUTATION: Through its internal microcomputer, the 366 keeps track of the set point throughout the count cycle. Whenever there is a change in set point, even during a cycle, it instantly recomputes the remaining count and accurately determines the number of counts before count-out. This unique capability is especially valuable in the count-down modes as it allows you to shorten or lengthen a cycle without loss of accuracy.

PROGRAMMABLE DISPLAY: The 366's three-digit cycle progress display will count UP to or DOWN from the set point, depending on the position of an internal jumper. After count-out, the display will either STOP or GO. In the UP & GO program, the display counts up to the set point and continues to count after count-out; in the DOWN & GO mode, it counts down to the set point, then begins to count up (from zero) after count-out.

WIDE RANGE: Each 366 Long-Ranger covers the overall span of 1 to 99,900 counts in three switch-selected ranges of 1 to 999, 10 to 9990 or 12 to 99,900. It can be optimized within any selected range simply by removing appropriate selector knobs (e.g. with the counter in the 1 to 999 range, you can obtain a tamper-proof span of 1 to 99 by setting the left selector at 0 and removing the knob.) To the right of the three-digit display, a counting bar (→ blinks on each time a pulse is received. At left, a marker (▼) turns on when the delayed relay is energized at count-out.

SELF-DIAGNOSTICS: The time will display "FAIL" anytime there is a problem or the knobs are in between digits.

COMPACT, PLUG-IN AND DUST-TIGHT: Packaged in a 72mm² DIN housing, the 366 occupies 40% less panel space than most other industrial counters. It is a true plug-in counter that can be replaced in seconds without disturbing housing or wiring. The 366 is also fully gasketed and 0 ring sealed to be dust and water-tight whether panel or surface-mounted.

POSITIVE RESET TIME AND PULSE LENGTH: Digitally clocked by the microcomputer, the 366's reset time is consistently of the same duration, regardless of variations in line voltage, power supply or cycle length. When the 366 operates in repeat-cycle mode, the output pulse is also digitally clocked so that both the time of occurrence and its duration are consistent from cycle to cycle.

TYPICAL INSTALLATIONS

© POWER SUPPLY
(P) PULSE INPUT
INDEPENDENT LOADS
DEPENDENT LOADS
MOMENTARY STARTING
CONTACT
SUSTAINED STARTING

SUSTAINED STARTING
CONTACT
SUSTAINED
CONTACT
CONTACT
CONTACT
CONTACT

- O LOAD DE-ENERGIZED
- X LOAD ENERGIZED
- DELAYED CONTACTS

 Contacts transfer

 contacts transfer

 in the contact of the con

All timers shown in "before start" position. Diagrams shown with power off unless otherwise marked

Maximum load current through any load carrying contact is 5


Pilot light leads are brought out to terminal block. Pilot light can be wired to show practically any desired function; unit energized, cycle running, instantaneous or delayed switch closed, etc.

ON DELAY-Reset on power failure.



INSTANTANEOUS CONTACTS Contacts are transferred when power supply is energized; transferred back, as shown when de-energized.

SUSTAINED START




MODEL NUMBER

MODEL NUMBER	366C				Р	Х
RANGE 1-999, 10-9990 or 12-99900		400				
(switch selected)						
Special		000				
VOLTAGE & FREQUENCY						
120 VAC 50-60 Hz						
240 VAC, 50-60 Hz						
24 VAC, 50 or 60 Hz						
24 VDC			N			
Special						
ARRANGEMENT						
Selectable Count Up or Count Down				30		
with Display						
Selectable Count Up & Go or				50		
Count Down & Go with Display						
FEATURES						
Basic plug-in unit					Р	
Standard unit						Х


ACCESSORIES


Surface mounting bracket kit	0353-260-27-00
Retrofit kit	0305-265-61-70


MOMENTARY START/SUSTAINED START



COUNT, PULSE AND REPEAT CYCLE







OPERATION

As soon as power is applied to terminals 1 & 2 of the counter, the instantaneous relay is energized and changes the states of its associated contacts (8-6-7 & 9-14-10). The counter then looks for terminal 15 (pulse input terminal) to receive input pulses. When the number of pulses received equals the number of counts set on the front face, the delayed relay energize and changes the states of its associated contacts (3-4-5 & 13-11-12).

The counter is reset by removing power from terminal 1 for at least 60 msec. At reset, both relays revert back to their shelf (without power) state. To the right you will find some typical applications.

SETTING SWITCHES: The three digits are set with the rotary switch knobs beneath each digit. These knobs can be rotated in either direction (CW or CCW), and they are "pull" removable if digit set security is desired. When the 366 is in the "Count Down" mode, changing one or more digits, during counting, will instantly be reflected by an equivalent change in the counter's display. In the "Count Up" mode, changing digits immediately changes the count-out set point. Setting all three digits to zero will cause instant count-out in any display mode.

THE DISPLAY: A high intensity blue fluorescent display consists of three digits and a Counting Bar with a special Count-Out symbol. The Counting Bar appears to the right of the digits and blinks once every count, regardless of range. When the delay relay is energized at count-out, a triangular Count-Out symbol appears to the left of the digits.

REMOVE THE 366C FROM ITS HOUSING TO MAKE CHANGES SHOWN BELOW.

COUNTING DISPLAY MODES: Down & Stop (30)

Up & Stop (30)

Down & Go (50)

Up & Go (50)

CHANGING THE RANGE: The 366B has three ranges:

x1 = Counts single pulses to 999

x10 = Counts every tenth pulse to 9,990

12 = Counts every 12th pulse

Each range is selected using finger force on the white plastic lever behind the front face of the counter. In two of the three possible lever positions, an indicator will appear in a range window located on the front face below and between the rotary switch knobs. When nothing appears in these windows, the counter is understood to be in the x 1 range.

TERMINALS

MODELS	Display model only for operation at 120, 240 or 24 VAC; and 24 VDC. Unit counts on break (i.e. when count input switch opens). Unit operates in on delay mode only.			
RANGE	Switch-selectable ranges of 1 to 999, 10 to 9990, and 12 to 99900.			
REPEAT ACCURACY	100% (+0 count on all ranges)			
RESET TIME	Clocked at 40 mSEC			
COUNT INPUT		AC		
	Max. count rate (symmetrical input)	1000/MIN		
	Min. pulse on time	20 mSEC		
	Min. pulse off time	30 mSEC		
		DC		
	Max. count rate (symmetrical input)	2000/MIN		
	Min. Pulse on time	15 mSEC		
	Min. Pulse off time	15 mSEC		
	Bounce Immunity	5 mSEC		
	(max. bounce open t	,		
	Pulse Contact Requirement	10 mA at line voltage		
COUNT	Single Cycle	interval or delayed		
CONTROL MODES	Repeat Cycle	pulse (occurrence and duration 50 mSEC clocked)		
-	Cycle Progress	3-digit display, 0.3 inch, high- intensity, blue programmable modes: DOWN & STOP, DOWN & GO, UP & STOP or UP & GO.		
	Count-Out	▼display; energized at count-out		
	Counting Bar	display; blinks on when count switch is closed, when pulse is received		
		ug-in design; fully gasketed,		

COUNT INPUT	Voltage Model			
	120 VAC Model	Turn On 60V 3.5 mA (nom.) Turn Off 30V 2.4 mA (nom.) 10 mA max. current at 120V		
	240 VAC Model	Turn On 120V 3.5 mA (nom.) Turn Off 60V 2.4 mA (nom.) 10 mA max. current at 240V		
	24 VAC Model	Turn On 12V 9.5mA (nom.) Turn Off 4V 3.8 mA (nom.) 30 mA max. current at 24V		
	24 VDC Model	Turn On 15 VDC 2.5 mA (nom.) Turn Off 3 VDC .5 mA (nom.) 5 mA max. current at 24V		
LOAD RELAY	Number	one instantaneous and one delayed		
	Туре	DPDT, Form C		
	Operate	Time 13 ms, max.		
	Release Time	Time 10 ms, max.		
	Contact Ratings	7A at 120, 240 or 24 VAC, 1/6 HP.		
	LIFE	100 million operations (no load)		
POWER	120V	95 to 132V, 50/60 Hz inrush-0.3A		
	2.401/	running-0.06A at 120 VAC		
	240V	190 to 264V, 50/60 Hz		
		inrush-0.15A		
	24.1/4.6	running-0.03A at 240 VAC		
	24 VAC	19.2 - 26.4 VAC, 50 or 60 Hz		
		Inrush—1 A		
	24 VDC	Running-0.25 A at 24 VAC		
	24 VDC	19.2 - 26.4 VDC, 5% ripple Running120 A at 24 VDC		
TEMPERATURE RATING	32 to 122°F (0 to 50°C)			
MOUNTING	Standard	hardware is provided for front-of-panel mounting.		
	Optional	Surface-mounting brackets with front-facing terminals		
WEIGHT	NET: AC - 1 lb., 6oz. DC - 10 oz.			
	SHIPPING: AC - 2 lbs., DC - 1 lb., 4 oz.			
	JIIII I ING. AC - 2 IDS., DC - 1 ID., 4 UZ.			

dust and water-tight in panel mounted installations. NEMA 4 when mounted per installation instructions.

16 screw terminals accessible at rear;

integral wiring diagram.