

Inductors for decoupling circuits **Wound ferrite ADL-VM** series (for automobiles)











# ADL3225VM type














## **FEATURES**

- Small size and thin form factor (mounting area 3.2 x 2.5 mm, height 2.5mm max.)
- O Achieving broadband impedance characteristics and good DC superimposition characteristics as the result of an original coiled wiring design and original structure
- O Ensuring consistent high quality and reliability as the result of a completely automated manufacturing process
- Operating temperature range: -55 to +155°C (including self-temperature rise)
- Ocompliant with AEC-Q200

#### APPLICATION

- O Inductor for use with separate signal and power lines in in-vehicle PoC (Power Over Coax)
- O Application guides: Car Infotainment

#### PART NUMBER CONSTRUCTION



#### CHARACTERISTICS SPECIFICATION TABLE

L		LMeasuring frequency	DC resistance	Rated current*		Part No.		
				Isat (mA)ty	p.	Itemp (mA	A)typ.	
(μH)	Tolerance	(kHz)	( $\Omega$ )max.	105°C	125°C	105°C	125°C	
2.2	±20%	100	0.18	875	760	995	950	ADL3225VM-2R2M-TL000
15	±20%	100	0.40	350	310	575	495	ADL3225VM-150M-TL000

<sup>\*</sup> Rated current: smaller value of either Isat or Itemp.

Isat: when based on the inductance change rate (30% below the initial L value)

Itemp.105°C: When based on the temperature increase (temperature increase of 40°C by self heating)

Itemp.125°C: When based on the temperature increase (temperature increase of 30°C by self heating)

#### Measurement equipment


Measurement item	Product No.	Manufacturer
Inductance	4294A	Keysight Technologies
DC resistance	4338A	Keysight Technologies

<sup>\*</sup> Equivalent measurement equipment may be used.




# ADL3225VM type

### **■IMPEDANCE VS. FREQUENCY CHARACTERISTICS**




### ■INDUCTANCE VS. DC BIAS CHARACTERISTICS

#### □105°C










# ADL3225VM type


#### ■SHAPE & DIMENSIONS




#### Dimensions in mm

### ■PACKAGING STYLE

#### □REEL DIMENSIONS




## ☐TAPE DIMENSIONS




Type	Α	В	K
ADL3225VM	(2.85)	(4.2)	(2.7)

## ■ RECOMMENDED LAND PATTERN



Dimensions in mm

# ■ RECOMMENDED REFLOW PROFILE



#### **□PACKAGE QUANTITY**

Package quantity	6000 pcs/reel

## ■TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range*	Storage temperature range	Individual weight
−55 to +155 °C	−55 to +155 °C	0.076 g

<sup>\*</sup> Operating temperature range includes self-temperature rise.



# REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

# **SAFETY REMINDERS**

Please pay sufficient attention to the warnings for safe designing when using this products.

# REMINDERS ○ The storage period is within 6 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH or less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate. On not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.). Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C. Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur. When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions. O Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design. Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference. Use a wrist band to discharge static electricity in your body through the grounding wire. On not expose the products to magnets or magnetic fields. O Do not use for a purpose outside of the contents regulated in the delivery specifications. The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society,

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (electric trains, ships, etc.)

set forth in the each catalog, please contact us.

(3) Medical equipment

person or property.

- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions