MOSFET – Power, Single, P-Channel, DPAK -60 V, -15.5 A

Features

- Withstands High Energy in Avalanche and Commutation Modes
- Low Gate Charge for Fast Switching
- AEC Q101 Qualified NTDV20P06L
- These Devices are Pb-Free and are RoHS Compliant

Applications

- Bridge Circuits
- Power Supplies, Power Motor Controls
- DC-DC Conversion

MAXIMUM RATINGS (T_J = 25° C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V _{DSS}	-60	V
Gate-to-Source	ce Continuous		V _{GS}	±20	V
Voltage	Non-Repetitive	$t_p \le 10 \text{ ms}$	V _{GSM}	±30	
Continuous Drain Current	Steady State	Steady State $T_C = 25^{\circ}C$		-15.5	A
Power Dissipa- tion	Steady State $T_C = 25^{\circ}C$		PD	65	W
Pulsed Drain Current	- p ie pie		I _{DM}	±50	A
$\label{eq:spectral_optimal_star} \begin{array}{l} \mbox{Operating Junction and Storage Temperature} \\ \mbox{Single Pulse Drain-to-Source Avalanche} \\ \mbox{Energy (V_{DD} = 25 V, V_{GS} = 5 V, I_{PK} = 15 A, \\ L = 2.7 \mbox{ mH, R}_G = 25 \ \Omega) \\ \mbox{Lead Temperature for Soldering Purposes} \\ \mbox{(1/8" from case for 10 s)} \end{array}$			T _J , T _{STG}	–55 to 175	°C
			E _{AS}	304	mJ
			ΤL	260	°C

THERMAL RESISTANCE RATINGS

Parameter	Symbol	Max	Unit
Junction-to-Case (Drain)	$R_{\theta JC}$	2.3	°C/W
Junction-to-Ambient - Steady State (Note 1)	$R_{\theta JA}$	80	
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	110	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


- 1. Surface-mounted on FR4 board using 1 in sq. pad size
- (Cu area = 1.127 in sq. [1 oz] including traces)
- Surface-mounted on FR4 board using the minimum recommended pad size (Cu area = 0.412 in sq.)




ON Semiconductor®

www.onsemi.com

V _{(BR)DSS}	R _{DS(on)} TYP	I _D MAX (Note 1)
-60 V	130 m Ω @ –5.0 V	–15.5 A





ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.


ELECTRICAL CHARACTERISTICS (T_J = 25° C unless otherwise noted)

Parameter	Symbol	Test Condition		Min	Тур	Max	Units
OFF CHARACTERISTICS	•	•			•		-
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V_{GS} = 0 V, I _D = -	-250 μA	-60	-74		V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /T _J				-64		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	V _{GS} = 0 V.	$T_J = 25^{\circ}C$			-1.0	μΑ
		V _{GS} = 0 V, V _{DS} = -60 V	T _J = 150°C			-10	
Gate-to-Source Leakage Current	I _{GSS}	V _{DS} = 0 V, V _{GS} =	= ±20 V			±100	nA
ON CHARACTERISTICS (Note 3)							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D = -$	-250 μA	-1.0	-1.5	-2.0	V
Gate Threshold Temperature Coefficient	V _{GS(TH)} /T _J				3.1		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	$V_{GS} = -5.0 \text{ V}, \text{ I}_{D}$	= –7.5 A		0.130	0.150	Ω
		V _{GS} = -5.0 V, I _D	= –15 A		0.143		
Forward Transconductance	9fs	V _{DS} = -10 V, I _D =	= –7.5 A		11		S
Drain-to-Source On-Voltage	V _{DS(on)}	V _{GS} = -5.0 V,	$T_J = 25^{\circ}C$			-1.2	V
		I _D = -7.5 A	T _J = 150°C			-1.9	
CHARGES AND CAPACITANCES							
Input Capacitance	C _{ISS}				740	1190	pF
Output Capacitance	C _{OSS}	V _{GS} = 0 V, f = 1 MHz,	V _{DS} = -25 V		207	300]
Reverse Transfer Capacitance	C _{RSS}				66	120	
Total Gate Charge	Q _{G(TOT)}				15	26	nC
Gate-to-Source Charge	Q _{GS}	$V_{GS} = -5.0 \text{ V}, V_{DS}$ $I_D = -18 \text{ A}$; = −48 V,		4.0		
Gate-to-Drain Charge	Q _{GD}				7.0		
SWITCHING CHARACTERISTICS (Note 4)						
Turn-On Delay Time	t _{d(ON)}				11	20	ns
Rise Time	t _r	V _{GS} = -5.0 V, V _{DC}	= −30 V,		90	180	
Turn-Off Delay Time	t _{d(OFF)}	V _{GS} = –5.0 V, V _{DD} I _D = –15 A, R _G =	= 9.1 Ω		28	50	
Fall Time	t _f				70	135	
DRAIN-SOURCE DIODE CHARACTERIS	TICS						
Forward Diode Voltage	V _{SD}	$V_{GS} = 0 \text{ V}, \text{ I}_{S} = -15 \text{ A} \frac{\text{T}_{J} = 25^{\circ}\text{C}}{\text{T}_{J} = 150^{\circ}\text{C}}$			1.5	2.5	V
					1.3		
Reverse Recovery Time	t _{RR}	V_{GS} = 0 V, d_{IS}/d_t = 100 A/µs, I _S = -12 A			60		ns
Charge Time	t _a				39]
Discharge Time	t _b				21]
Reverse Recovery Charge	Q _{RR}				0.13		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL PERFORMANCE CURVES

 $(T_J = 25^{\circ}C \text{ unless otherwise noted})$









Figure 8. Gate-to-Source and Drain-to-Source Voltage versus Total Charge










ORDERING INFORMATION

Device	Package	Shipping [†]
NTD20P06LG	DPAK (Pb-Free)	75 Units / Rail
NTD20P06LT4G		2500 / Tape & Reel
NTDV20P06LT4G		NTDV20P06LT4G (Pb-Free) 2500 / Tape & Reel
NTDV20P06LT4G-VF01	1	2500 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS



NOTES:


- 1. DIMENSIONING AND TOLERANCING PER ASME
- Dimensioning and ToleParoling Fer Asine Y14.5M, 1994.
 CONTROLLING DIMENSION: INCHES.
 THERMAL PAD CONTOUR OPTIONAL WITHIN DI-MENSIONS b3, L3 and Z.
- MENSIONS D3, L3 and Z. 4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.006 INCHES PER SIDE.
- 5. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- 6. DATUMS A AND B ARE DETERMINED AT DATUM
- PLANE H. 7 OPTIONAL MOLD FEATURE

	INC	HES	MILLIN	IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.086	0.094	2.18	2.38
A1	0.000	0.005	0.00	0.13
b	0.025	0.035	0.63	0.89
b2	0.028	0.045	0.72	1.14
b3	0.180	0.215	4.57	5.46
с	0.018	0.024	0.46	0.61
c2	0.018	0.024	0.46	0.61
D	0.235	0.245	5.97	6.22
E	0.250	0.265	6.35	6.73
е	0.090	BSC	2.29 BSC	
н	0.370	0.410	9.40	10.41
L	0.055	0.070	1.40	1.78
L1	0.114	REF	2.90 REF	
L2	0.020 BSC		0.51	BSC
L3	0.035	0.050	0.89	1.27
L4		0.040		1.01
Z	0.155		3.93	

STYLE 2:

PIN 1. GATE 2. DRAIN 3. SOURCE 4. DRAIN


SOLDERING FOOTPRINT*




*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS

IPAK





С	TES:	
	DIMENSIONING	тс

N

DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 CONTROLLING DIMENSION: INCH.

	INCHES	

	INCHES		MILLIM	IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.235	0.245	5.97	6.35
В	0.250	0.265	6.35	6.73
С	0.086	0.094	2.19	2.38
D	0.027	0.035	0.69	0.88
Е	0.018	0.023	0.46	0.58
F	0.037	0.045	0.94	1.14
G	0.090	BSC	2.29 BSC	
н	0.034	0.040	0.87	1.01
J	0.018	0.023	0.46	0.58
К	0.350	0.380	8.89	9.65
R	0.180	0.215	4.45	5.45
S	0.025	0.040	0.63	1.01
V	0.035	0.050	0.89	1.27
Z	0.155		3.93	
STYLE 2'				

PIN 1. GATE 2. DRAIN 3. SOURCE 4. DRAIN

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor dates sheets and/or application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights or others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor hardles against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors h

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421-32-700-2010

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative