<u>MOSFET</u> – Power, P-Channel, DPAK

-60 V, -12 A

This Power MOSFET is designed to withstand high energy in the avalanche and commutation modes. Designed for low-voltage, highspeed switching applications in power supplies, converters, and power motor controls. These devices are particularly well suited for bridge circuits where diode speed and commutating safe operating areas are critical and offer an additional safety margin against unexpected voltage transients.

Features

- Avalanche Energy Specified
- I_{DSS} and V_{DS(on)} Specified at Elevated Temperature
- Designed for Low–Voltage, High–Speed Switching Applications and to Withstand High Energy in the Avalanche and Commutation Modes
- NVD and SVD Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

(1) = 20 of an observation model in the data (1)			
Rating	Symbol	Value	Unit
Drain-to-Source Voltage	V _{DSS}	-60	Vdc
Gate–to–Source Voltage – Continuous – Non–repetitive (t _p ≤ 10 ms)	V _{GS} V _{GSM}	± 20 ± 25	Vdc Vpk
Drain Current – Continuous @ T _a = 25°C – Single Pulse (t _p ≤ 10 ms)	I _D I _{DM}	-12 -18	Adc Apk
Total Power Dissipation @ $T_a = 25^{\circ}C$	PD	55	W
Operating and Storage Temperature Range	T _J , T _{stg}	–55 to 175	°C
$ \begin{array}{l} \mbox{Single Pulse Drain-to-Source Avalanche} \\ \mbox{Energy - Starting } T_J = 25^\circ\mbox{C} \\ \mbox{(V}_{DD} = 25 \mbox{ Vdc, } V_{GS} = 10 \mbox{ Vdc, Peak} \\ \mbox{I}_L = 12 \mbox{ Apk, } L = 3.0 \mbox{ mH, } R_G = 25 \Omega) \end{array} $	E _{AS}	216	mJ
Thermal Resistance – Junction-to-Case – Junction-to-Ambient (Note 1) – Junction-to-Ambient (Note 2)	R _θ jc R _θ ja R _θ ja	2.73 71.4 100	°C/W
Maximum Lead Temperature for Soldering Purposes, 1/8 in. from case for 10 seconds	ΤL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


1. When surface mounted to an FR4 board using 1 in pad size (Cu area = 1.127 in²).

 When surface mounted to an FR4 board using the minimum recommended pad size (Cu area = 0.412 in²).



ON Semiconductor®

www.onsemi.com



optional. In cases where the Assembly Location is stamped in the package, the front side assembly code may be blank.

ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.


ELECTRICAL CHARACTERISTICS (T_J = 25° C unless otherwise noted)


Characteristic			Min	Тур	Max	Unit
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage (Note 3) (V _{GS} = 0 Vdc, I _D = -0.25 mA) (Positive Temperature Coefficient)			-60 -	67		Vdc mV/°C
$\label{eq:constraint} \begin{array}{l} \mbox{Zero Gate Voltage Drain Current} \\ (V_{GS} = 0 \mbox{ Vdc}, V_{DS} = -60 \mbox{ Vdc}, T \\ (V_{GS} = 0 \mbox{ Vdc}, V_{DS} = -60 \mbox{ Vdc}, T \end{array}$		I _{DSS}			-10 -100	μAdc
Gate-Body Leakage Current (V _{GS}	$_{\rm s}=\pm$ 20 Vdc, V _{DS} = 0 Vdc)	I _{GSS}	-	-	-100	nAdc
ON CHARACTERISTICS (Note 3)				1	I	
Gate Threshold Voltage $(V_{DS} = V_{GS}, I_D = -250 \ \mu Adc)$ (Negative Temperature Coefficie	ent)	V _{GS(th)}	-2.0 -	-2.8 4.5	-4.0	Vdc mV/°C
Static Drain–Source On–State Resistance ($V_{GS} = -10 \text{ Vdc}, I_D = -6.0 \text{ Adc}$)			_	0.155	0.180	Ω
Drain-to-Source On-Voltage ($V_{GS} = -10$ Vdc, $I_D = -12$ Adc) ($V_{GS} = -10$ Vdc, $I_D = -6.0$ Adc, $T_J = 150^{\circ}$ C)				-1.86 -	-2.6 -2.0	Vdc
Forward Transconductance (V _{DS} =	gFS		8.0	-	Mhos	
DYNAMIC CHARACTERISTICS			•	1	I.	
Input Capacitance		C _{iss}	-	500	750	pF
Output Capacitance	(V _{DS} = -25 Vdc, V _{GS} = 0 Vdc, F = 1.0 MHz)	C _{oss}	-	150	250	
Reverse Transfer Capacitance	· ····································	C _{rss}	-	50	100	
SWITCHING CHARACTERISTICS	(Notes 3 and 4)	·				-
Turn-On Delay Time		t _{d(on)}	-	10	20	ns
Rise Time	(V _{DD} = −30 Vdc, I _D = −12 A,	t _r	-	45	85	
Turn-Off Delay Time	$V_{GS} = -10 \text{ V}, \text{ R}_{G} = 9.1 \Omega$	t _{d(off)}	-	26	40	
Fall Time		t _f	-	48	90	
Gate Charge		QT	-	15	30	nC
	(V _{DS} = −48 Vdc, V _{GS} = −10 Vdc, I _D = −12 A)	Q _{GS}	-	4.0	-	
		Q _{GD}	-	7.0	-]
DRAIN-SOURCE DIODE CHARA	CTERISTICS (Note 3)	·				
Diode Forward On–Voltage ($I_S = 12 \text{ Adc}, V_{GS} = 0 \text{ V}$) ($I_S = 12 \text{ Adc}, V_{GS} = 0 \text{ V}, T_J = 150^{\circ}\text{C}$)		V _{SD}		-1.6 -1.3	-2.5	Vdc
Reverse Recovery Time (I _S = 12 A, dI _S /dt = 100 A/ μ s ,V _{GS} = 0 V)		t _{rr}	-	50		ns
		t _a	-	40	-	1
		t _b	-	10	-	1
Reverse Recovery Stored Charge		Q _{RR}	-	0.10	-	μC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Indicates Pulse Test: Pulse Width \leq 300 μ s, Duty Cycle \leq 2%. 4. Switching characteristics are independent of operating junction temperature.

TYPICAL PERFORMANCE CURVES (T_J = 25°C unless otherwise noted)









Figure 11. Maximum Rated Forward Biased Safe Operating Area



di/dt

ls






Figure 13. Thermal Response

ORDERING INFORMATION

Device	Package	Shipping [†]
NTD2955G	DPAK (Pb-Free)	75 Units / Rail
NTD2955-1G	IPAK (Pb-Free)	75 Units / Rail
NTD2955T4G	DPAK (Pb-Free)	2500 / Tape & Reel
NVD2955T4G*	DPAK (Pb-Free)	2500 / Tape & Reel
SVD2955T4G*	DPAK (Pb-Free)	2500 / Tape & Reel


+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

*NVD and SVD Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.

PACKAGE DIMENSIONS

DPAK (SINGLE GAUGE) CASE 369C

ISSUE F




- NOTES: 1. DIMENSIONING AND TOLERANCING PER ASME
- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
 CONTROLLING DIMENSION: INCHES.
 THERMAL PAD CONTOUR OPTIONAL WITHIN DI-MENSIONS b3, L3 and Z.
 DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.006 INCHES PER SIDE.
 DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
 DATUMS A AND B ARE DETERMINED AT DATUM PLANE H.
- PLANE H

7. OPTIONAL	MOLD	FEATURE.


	INCHES		MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.086	0.094	2.18	2.38	
A1	0.000	0.005	0.00	0.13	
b	0.025	0.035	0.63	0.89	
b2	0.028	0.045	0.72	1.14	
b3	0.180	0.215	4.57	5.46	
С	0.018	0.024	0.46	0.61	
c2	0.018	0.024	0.46	0.61	
D	0.235	0.245	5.97	6.22	
Е	0.250	0.265	6.35	6.73	
е	0.090	0.090 BSC		29 BSC	
н	0.370	0.410	9.40	10.41	
L	0.055	0.070	1.40	1.78	
L1	0.114 REF		2.90 REF		
L2	0.020 BSC		0.51 BSC		
L3	0.035	0.050	0.89	1.27	
L4		0.040		1.01	
Z	0.155		3.93		

STYLE 2: PIN 1. GATE 2. DRAIN 3. SOURCE 4. DRAIN



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS



IPAK CASE 369D ISSUE C

NOTES:

z

1. DIMENSIONING AND TOLERANCING PER

ANSI Y14.5M, 1982. 2. CONTROLLING DIMENSION: INCH.

	INCHES		MILLIN	IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.235	0.245	5.97	6.35
В	0.250	0.265	6.35	6.73
С	0.086	0.094	2.19	2.38
D	0.027	0.035	0.69	0.88
Е	0.018	0.023	0.46	0.58
F	0.037	0.045	0.94	1.14
G	0.090 BSC		2.29 BSC	
н	0.034	0.040	0.87	1.01
J	0.018	0.023	0.46	0.58
К	0.350	0.380	8.89	9.65
R	0.180	0.215	4.45	5.45
S	0.025	0.040	0.63	1.01
V	0.035	0.050	0.89	1.27
Z	0.155		3.93	

STYLE 2: PIN 1. GATE 2. DRAIN

3. SOURCE 4. DRAIN

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor dates sheets and/or application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights or others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor hardles against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors h

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative