

#### **Features**

- ESD Protection for 1 line with Bi-directional
- Provide ESD protection for the protected line to IEC 61000-4-2 (ESD) ±30kV (air), ±30kV (contact)
   IEC 61000-4-4 (EFT) 80A (5/50ns)
   IEC 61000-4-5 (Lightning) 42A (8/20μs)
- For low operating voltage applications: 3.3V
- 0402 small DFN package saves board space
- Protect one I/O line or power line
- Fast turn-on and Low clamping voltage
- Solid-state silicon-avalanche and active circuit triggering technology
- Green Part

# **Applications**

- Power Line Protection
- Audio Protection
- Mobile Phones
- Control Signal Line Protection
- Hand Held Portable Applications

# **Description**


AZ5883-01F is a design which includes one bi-directional surge rated clamping cell to protect one power line, or one control line, or one low speed data line in an electronic systems. The AZ5883-01F has been specifically designed to sensitive components which protect connected to power and control lines from over-voltage damage and latch-up caused by Electrostatic Discharging (ESD), Electrical Fast **Transients** Lightning, and Cable (EFT), Discharge Event (CDE).

AZ5883-01F is a unique design which includes proprietary clamping cell in a single package. During transient conditions, the proprietary clamping cell prevents over-voltage on the power line or control/data lines, protecting any

downstream components.

AZ5883-01F may be used to meet the ESD immunity requirements of IEC 61000-4-2, Level 4 (±15kV air, ±8kV contact discharge).

# Circuit Diagram / Pin Configuration



## **SPECIFICATIONS**

| ABSOLUTE MAXIMUM RATINGS (T <sub>A</sub> = 25°C, unless otherwise specified) |                            |               |            |  |  |
|--|----------------------------|---------------|------------|--|--|
| PARAMETER  | SYMBOL                     | RATING        | UNITS      |  |  |
| Peak Pulse Current (tp=8/20μs)   | I <sub>PP-1</sub> (Note 1) | 42            | А          |  |  |
|  | I <sub>PP-2</sub> (Note 2) | 33            |            |  |  |
| Operating Supply Voltage   | $V_{DC}$                   | ±3.6          | V          |  |  |
| ESD per IEC 61000-4-2 (Air)  | \/                         | ±30           | kV         |  |  |
| ESD per IEC 61000-4-2 (Contact)  | V <sub>ESD</sub>           | ±30           |            |  |  |
| Lead Soldering Temperature   | T <sub>SOL</sub>           | 260 (10 sec.) | $^{\circ}$ |  |  |
| Operating Temperature  | T <sub>OP</sub>            | -55 to +125   | $^{\circ}$ |  |  |
| Storage Temperature  | T <sub>STO</sub>           | -55 to +150   | $^{\circ}$ |  |  |

| ELECTRICAL CHARACTERISTICS         |                       |   |      |      |     |       |
|------------------------------------|-----------------------|---|------|------|-----|-------|
| PARAMETER                          | SYMBOL                | CONDITIONS  | MINI | TYP  | MAX | UNITS |
| Reverse Stand-Off<br>Voltage       | $V_{RWM}$             | T=25 ℃.   | -3.3 |      | 3.3 | V     |
| Reverse Leakage<br>Current         | I <sub>Leak</sub>     | V <sub>RWM</sub> =±3.3V,T=25 °C.                                    |      |      | 0.5 | μА    |
| Reverse<br>Breakdown Voltage       | $V_{BV}$              | I <sub>BV</sub> = 1mA, T=25 °C.                                     | 4.5  |      | 6.8 | V     |
| Surge Clamping<br>Voltage (Note 1) | $V_{\text{CL-surge}}$ | I <sub>PP</sub> = 5A, tp=8/20μs, T=25 °C.                           |      | 4.5  |     | V     |
|                                    |                       | I <sub>PP</sub> = 42A, tp=8/20μs, T=25 °C.                          |      | 9    |     |       |
| ESD Clamping<br>Voltage (Note 3)   | $V_{clamp}$           | IEC 61000-4-2 +8kV (I <sub>TLP</sub> = 16A), contact mode, T=25 °C. |      | 5    |     | V     |
| ESD Dynamic<br>Turn-on Resistance  | $R_{dynamic}$         | IEC 61000-4-2 0~+8kV, contact mode, T=25 °C.                        |      | 0.04 |     | Ω     |
| Channel Input Capacitance          | $C_{IN}$              | $V_R = 0V$ , $f = 1MHz$ , $T=25$ °C.                                |      | 70   | 85  | pF    |

Note 1: The Peak Pulse Current measured conditions:  $tp = 8/20\mu s$ , 20hm source impedance.


Note 2: The Peak Pulse Current measured conditions:  $tp = 8/20\mu s$ , 42ohm source impedance.


Note 3: ESD Clamping Voltage was measured by Transmission Line Pulsing (TLP) System.


TLP conditions:  $Z_0$ = 50 $\Omega$ ,  $t_p$ = 100ns,  $t_r$ = 1ns.



# **Typical Characteristics**









# **Applications Information**

The AZ5883-01F is designed to protect one line against System ESD/EFT/Lightning pulses by clamping it to an acceptable reference. It provides bi-directional protection.

The usage of the AZ5883-01F is shown in Fig. 1. Protected line, such as data line, control line, or power line, is connected at pin 1. The pin 2 is connected to a ground plane on the board. In order to minimize parasitic inductance in the board traces, all path lengths connected to the pins of AZ5883-01F should be kept as short as possible.

In order to obtain enough suppression of ESD induced transient, good circuit board is critical. Thus, the following guidelines are recommended:

- Minimize the path length between the protected lines and the AZ5883-01F.
- Place the AZ5883-01F near the input terminals or connectors to restrict transient coupling.
- The ESD current return path to ground should be kept as short as possible.
- Use ground planes whenever possible.
- NEVER route critical signals near board edges and near the lines which the ESD transient easily injects to.






Fig. 1



#### **Mechanical Details**


# DFN1006P2E PACKAGE DIAGRAMS





| Symbol | Millimeters |      |      | Inches |        |       |
|--------|-------------|------|------|--------|--------|-------|
| Symbol | MIN         | NOM  | MAX  | MIN    | NOM    | MAX   |
| Α      | 0.95        | 1.00 | 1.05 | 0.037  | 0.039  | 0.041 |
| В      | 0.55        | 0.60 | 0.65 | 0.022  | 0.024  | 0.026 |
| С      | 0.45        | 0.50 | 0.55 | 0.018  | 0.020  | 0.022 |
| C1     | 0.00        | 0.02 | 0.05 | 0.000  | 0.001  | 0.002 |
| E      | 0.20        | 0.25 | 0.30 | 0.008  | 0.010  | 0.012 |
| F      | 0.45        | 0.50 | 0.55 | 0.018  | 0.020  | 0.022 |
| G      | 0.65 BSC    |      |      | 0.     | 026 BS | C     |

#### LAND LAYOUT




(Unit: mm)

#### Notes:

This LAND LAYOUT is for reference purposes only. Please consult your manufacturing partners to ensure your company's PCB design guidelines are met.

## **MARKING CODE**



**Top View** 

| Part Number                     | Marking Code |  |
|---------------------------------|--------------|--|
| AZ5883-01F.R7GR<br>(Green Part) | m            |  |

Note: Green means Pb-free, RoHS, and Halogen free compliant.



**Ordering Information** 

| PN#             | Material | Type | Reel size | MOQ         | MOQ/internal box    | MOQ/carton              |
|-----------------|----------|------|-----------|-------------|---------------------|-------------------------|
| AZ5883-01F.R7GR | Green    | T/R  | 7 inch    | 12,000/reel | 4 reels =48,000/box | 6 boxes =288,000/carton |

**Revision History** 

| Revision            | Modification Description |
|---------------------|--------------------------|
| Revision 2017/04/25 | Formal Release.          |
|                     |                          |
|                     |                          |
|                     |                          |
|                     |                          |
|                     |                          |
|                     |                          |