

Features

- ESD Protect for 1 Line with Bi-directional
- Provide ESD protection for the protected line to IEC 61000-4-2 (ESD) ±16kV (air/contact)
 Cable Discharge Event (CDE)
- 0402 small DFN package saves board space
- Protect one I/O line or one power line
- Fast turn-on and Low clamping voltage
- For low operating voltage applications: 3.3V maximum
- Solid-state silicon-avalanche and active circuit triggering technology
- Green part
- AEC-Q101 qualified

Applications

- Mobile Phones
- Hand Held Portable Applications
- Computer Interfaces Protection
- Microprocessors Protection
- Serial and Parallel Ports Protection
- Control Signal Lines Protection
- Power lines on PCB Protection
- Latchup Protection


Description

AZ9523-01F is a design which includes one Bi-directional surge rated clamping cell to protect one power line, or one control line, or one low speed data line in an electronic systems. The AZ9523-01F has been specifically designed to protect sensitive components which are connected to power and control lines from over-voltage damage and latch-up caused by Electrostatic Discharging (ESD), and Cable Discharge Event (CDE).

AZ9523-01F is a unique design which includes proprietary clamping cell in a single package. During transient conditions, the proprietary clamping cell prevents over-voltage on the power line or control/data lines, protecting any downstream components.

AZ9523-01F may be used to meet the ESD immunity requirements of IEC 61000-4-2, Level 4 (±15kV air, ±8kV contact discharge)

Circuit Diagram / Pin Configuration



DFN1006P2X (Bottom View) (1.0mm x 0.6mm x 0.45mm)



SPECIFICATIONS

| ABSOLUTE MAXIMUM RATINGS | | | | |
|---------------------------------|------------------|---------------|-------|--|
| PARAMETER | SYMBOL | RATING | UNITS | |
| Operating Supply Voltage | V_{DC} | ±3.6 | V | |
| ESD per IEC 61000-4-2 (Air) | V_{ESD} | ±16 | kV | |
| ESD per IEC 61000-4-2 (Contact) | | ±16 | | |
| Lead Soldering Temperature | T _{SOL} | 260 (10 sec.) | °C | |
| Operating Temperature | T _{OP} | -55 to +125 | °C | |
| Storage Temperature | T _{STO} | -55 to +150 | °C | |


| ELECTRICAL CHARACTERISTICS | | | | | | |
|--------------------------------------|----------------------|--|------|-----|-----|-------|
| PARAMETER | SYMBOL | CONDITIONS | MINI | TYP | MAX | UNITS |
| Reverse Stand-Off Voltage | V_{RWM} | T=25 °C | -3.3 | | 3.3 | V |
| Leakage Current | I _{Leak} | $V_{RWM} = \pm 3.3 \text{V}, T=25 ^{\circ}\text{C}$ | | | 1.0 | μΑ |
| Breakdown Voltage | V_{BV} | I _{BV} = 1mA, T=25 °C | 4 | | 6.8 | V |
| ESD Clamping Voltage (Note 1) | V_{ESD_CL} | IEC 61000-4-2 +8kV (I _{TLP} = 16A), Contact mode, T=25 °C, pin-1 to pin-2 | | 7 | | V |
| ESD Dynamic Turn-on Resistance | R _{dynamic} | IEC 61000-4-2 0~+8kV, T= 25 °C, Contact mode, pin-1 to pin-2 | | 0.1 | | Ω |
| Channel Input Capacitance | C _{IN} | V _R = 0V, f = 1MHz, T=25 °C | | 15 | 18 | pF |


Note 1: ESD Clamping Voltage was measured by Transmission Line Pulsing (TLP) System.

TLP conditions: Z_0 = 50 Ω , t_p = 100ns, t_r = 2ns.



Typical Characteristics





3



Applications Information

The AZ9523-01F is designed to protect one line against System ESD/CDE pulses by clamping them to an acceptable reference. It provides bi-directional protection.

The usage of the AZ9523-01F is shown in Fig. 1. Protected line, such as data line, control line, or power line, is connected at pin 1. The pin 2 is connected to a ground plane on the board. In order to minimize parasitic inductance in the board traces, all path lengths connected to the pins of AZ9523-01F should be kept as short as possible.

In order to obtain enough suppression of ESD induced transient, good circuit board is critical. Thus, the following guidelines are recommended:

- Minimize the path length between the protected lines and the AZ9523-01F.
- Place the AZ9523-01F near the input terminals or connectors to restrict transient coupling.
- The ESD current return path to ground should be kept as short as possible.
- Use ground planes whenever possible.
- NEVER route critical signals near board edges and near the lines which the ESD transient easily injects to






Fig. 1 ESD protection scheme by using AZ9523-01F.




Mechanical Details

DFN1006P2X PACKAGE DIAGRAMS








PACKAGE DIMENSIONS

| Symbol | Millin | neters | Inches | | |
|--------|--------|--------|--------|-------|--|
| | min | max | min | max | |
| Α | 0.95 | 1.05 | 0.037 | 0.041 | |
| В | 0.55 | 0.65 | 0.022 | 0.026 | |
| С | 0.41 | 0.55 | 0.016 | 0.022 | |
| D | 0.45 | | 0.0 | 0.018 | |
| E | 0.20 | 0.30 | 0.008 | 0.012 | |
| F | 0.45 | 0.55 | 0.018 | 0.022 | |


LAND LAYOUT



Notes:

This LAND LAYOUT is for reference purposes only. Please consult your manufacturing partners to ensure your company's PCB design guidelines are met.

MARKING CODE



Top View

| Part Number | Marking Code | | |
|--------------|--------------|--|--|
| AZ9523-01F | 4 | | |
| (Green Part) | 4 | | |

Note. Green means Pb-free, RoHS, and Halogen free compliant.



Ordering Information

| PN# | Material | Type | Reel size | MOQ | MOQ/internal box | MOQ/carton |
|-----------------|----------|------|-----------|-------------|-------------------|----------------------|
| AZ9523-01F.R7GR | Green | T/R | 7 inch | 12,000/reel | 4 reel=48,000/box | 6 box=288,000/carton |

Revision History

| Revision | Modification Description | | | |
|---------------------|--------------------------|--|--|--|
| Revision 2015/02/04 | Preliminary release. | | | |
| Revision 2015/05/27 | Formal release. | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |