

Dwg. Number	Customer P/N	Smart P/N	Length(L) in 'INCH'
IE-00274-01	-	IB047SMSM4.0IN	4 +0.16/-0
IE-00274-02	-	IB047SMSM6.0IN	6 +0.24/-0
IE-00274-03	-	IB047SMSM8.0IN	8 +0.32/-0
IE-00274-04	-	IB047SMSM10.0IN	10 +0.40/-0
IE-00274-05	-	IB047SMSM12.0IN	12 +0.48/-0

1.0 Scope

This drawing documents the construction and performance of INSTABEND 047 cable assemblies manufactured by Times Microwave systems.

2.0 Cable Information

- 2.1 Cable to be INSTABEND 047
- 2.2 Jacket color to be Blue
- 2.3 Jacket material to be FEP
- 2.4 Nominal cable impedance to be 50 ohms
- 2.5 Cable diameter to be 0.061inch [1.55mm] (Nominal).

3.0 Connector Information:

- 3.1 Forward Connector:
 - Type SMA (M) Connector (47396) Connector Body – Stainless Steel, Passivated Center Contact – Beryllium Copper, Gold Plated
- 3.2 After Connector: Type SMA (M) Connector (47396) Connector Body – Stainless Steel, Passivated Center Contact – Beryllium Copper, Gold Plated

Unless otherwise spec- ified, dimensions are in INCH. Tolerances are applicable when spec- ified.				TIMES MICROWAVE SYSTEMS					
	Drawn	SVP	05/14/22		www.		ww.timesmi	.timesmicrowave.com	
These drawings and specifications contain proprietary information	Checked			INSTABEND 047 CABLE ASSEMBLY					
which is the property of	Approved								
Times Microwave	, ppioved			Size	CAGE (CAGE CODE		Drawing No.:	
Systems.				A	6899	99	IE-00274-XX		
				Scale:	NA	Rev. ((A)	Sheet: 1 of 3	

	THE REVISION STATUS OF ALL SHEETS OF THIS DRAWING IS THE SAME AS SHEET 1							
REV	DESCRIPTION	DATE	BY					
А	INITIAL RELEASE	05/14/22	SVP					

4.0 Electrical Performance

Dwg Number	Max. Insertion Loss in (dB)	Max. VSWR		
Dwg. Number	@ 10MHz – 27000 MHz	10MHz – 27000 MHz		
IE-00274-01	1.22	1.25		
IE-00274-02	1.66	1.25		
IE-00274-03	2.10	1.25		
IE-00274-04	2.54	1.25		
IE-00274-05	2.98	1.25		

5.0 Mechanical Performance

5.1 Overall Length to be specified length.

5.2 Minimum Bend radius is 0.750inch [19.05mm].

6.0 Environmental Performance

- 6.1 Installation Temperature Range (-65°C to +125°C)
- 6.2 Storage Temperature Range (-65°C to +125°C)
- 6.3 Operating Temperature Range (-65°C to +125°C)

7.0 Marking Details

- 7.1 Markers are to be black text on White Color Marker Sleeve.
- 7.2 Marker Configuration to be:

		,						
	Dwg. Num			ker 1				
	IE-00274-		Times Microw IB047SM \$\$\$					
	IE-00274-		Times Microwave Systems IB047SMSM6.0IN \$\$\$\$\$					
	IE-00274-		IB047SM	wave Systems /ISM8.0IN \$\$\$				
	IE-00274-	04	IB047SM \$\$\$	vave Systems SM10.0IN \$\$\$				
	IE-00274-		Times Microw IB047SM \$\$\$					
Unless otherwise spec- ified, dimensions are in INCH. Tolerances are	Aŗ	oprova	als			TIMES	MICROW	AVE SYSTEMS
applicable when spec- ified.	Drawn	SVP	05/14/22			W	ww.timesmi	crowave.com
These drawings and specifications contain proprietary information	Checked				INSTABEND 047 CABLE ASSEMBLY			
which is the property of	Approved						-	
Times Microwave	, pprovou			Size	CAGE CODE		Drawing No.:	
Systems.				A	6899	99	IE	-00274-XX
				Scale:	NA	Rev. ((A)	Sheet: 2 of 3

THE REVISION STATUS OF ALL SHEETS OF THIS DRAWING IS THE SAME AS SHEET 1						
REV	DESCRIPTION	DATE	BY			
А	INITIAL RELEASE	05/14/22	SVP			
	7.2. ###### E digit Covid Number for this presific Configuration	-				

7.3 \$\$\$\$ = 5-digit Serial Number for this specific Configuration.7.4 Register to be Maintained for Serial Number.

8.0 NOTES

1. Unless Otherwise Specified: Tolerance will be

Linear Dimension	Tolerance
INCH	INCH
<20	±0.4
20-79	±0.6
>79	±0.8

**Tolerances are not accumulative.

Unless otherwise spec- ified, dimensions are in INCH. Tolerances are applicable when spec- ified. These drawings and specifications contain proprietary information				TIMES MICROWAVE SYSTEMS				VAVE SYSTEMS	
	Drawn	SVP	05/14/22			www.timesmicrowave.com			
	Checked			INSTABEND 047 CABLE ASSEMBLY				E ASSEMBLY	
which is the property of	Approved								
Times Microwave	Лррготец			Size CAGE CO		ODE Drawing No.:		j No.:	
Systems.				A	A 689		IE	E-00274-XX	
				1	Scale: NA				
				Scale:			(A)	Sheet: 3 of 3	