

Multilayer Band Pass Filter

For 1880-2025MHz


DEA Series 1.6x0.8mm [EIA 0603] TYPE

P/N: **DEA161953BT-2303B1-H**

DEA161953BT-2303B1-H

SHAPES AND DIMENSIONS

[Top View] [Bottom View]



Dimensions (mm)

		<u>, , </u>								
L	W	Т	а	b	С	d	е	f	g	h
1.60	0.80	0.80	0.55	0.60	0.25	0.23	0.40	0.12	0.125	0.21
+/-0.10	+/-0.10	Max	+/-0.10	+/-0.10	+/-0.10	+/-0.10	+/-0.10	+/-0.10	+/-0.10	+/-0.10

Terminal functions

1011111	1 Offilia fariotiono						
(1)	Input Port						
(2)	GND						
(3)	Output Port						
(4)	GND						

DC Cut

No. There is NOT a DC Cut between the IN & OUT & GND.

TERMINATION FINISH

Material	
Ag	

DEA161953BT-2303B1-H

ELECTRICAL CHARACTERISTICS

(Measurement)

Parameter	Frequency (MHz)			TDK Spec		
Farameter				Min.	Тур.	Max.
Insertion Loss (dB)	1805	to	1880	-	2.10	-
	1880	to	2025	•	1.34	1.80
Insertion Loss (dB)	1880	to	2025	-	-	2.20
(-40 to +85 °C)						
VSWR (Input Port)	1880	to	2025	-	1.37	2.0
(Output Port)	1880	to	2025	•	1.36	2.0
Attenuation (dB)	1545	to	1610	20	25.4	-
	2400	to	2500	18	31.5	-
	5150	to	5850	25	40.4	-
Characteristic Impedance (ohm)				50	(Nomi	nal)

 $Ta = +25 + /-5 ^{\circ}C$

MAXIMUM RATINGS


Parameter	TDK Spec	Conditions		
Operating temperature (°C)		–40 to +85 °C		
Storage temperature (°C)		-40 to +85 °C		
Power Handling (W) *1	Frequency (MHz)			
	1805 to 2025	1	CW	
Human Body Model: HBM	@Each Port (V)	+/-1000	100pF / 1500ohm	
Machine Model : MM	@Each Port (V)	+/-150	200pF / 0ohm	
Charged Device Model: CDM	@Each Port (V)	+/-500	Humidity: 60%RH max	

*1: Refer to 3GPP TS 38.101-1 V15.2.0



DEA161953BT-2303B1-H


FREQUENCY CHARACTERISTICS






DEA161953BT-2303B1-H

RECOMMENDED LAND PATTERN



EVALUATION BOARD



unit: mm


- * Line width should be designed to match 50 ohm characteristic impedance depending on PCB material and thickness.
- ** The position of the throuh hole which have possibility of influence to the prerformance are indicated by dimension line.

ENVIRONMENT INFORMATION

RoHS Statement RoHS Compliance

DEA161953BT-2303B1-H

RECOMMENDED REFLOW PROFILE



Soldering Preheating Critical zone (T3 to T4) **Peak** Time Temp. Time Temp. Temp. **Time** T3 **t2 T4** t3 * **t1** 150°C 200°C 60 to 120sec 217°C 60 to 120sec 240 to 260°C 30 sec Max

* t3 : Time within 5°C of actual peak temperature The maximum number of reflow is 3.


Note: Lead free solder is recommended.


Recommended solder is Sn-3.0Ag-0.5Cu. (M705 by Senju Metal Industry)

DEA161953BT-2303B1-H

PACKAGING STYLE

Reel Dimensions





Dimensions (mm)

I	Α	В	С	D	Е	F	G	Н	J	K	t
	0.97	1.8	8.0	3.5	1.75	4.0	2.0	4.0	1.5	1.0	0.25
	+/-0.05	+/-0.05	+0.3/-0.1	+/-0.05	+/-0.1	+/-0.1	+/-0.05	+/-0.1	+0.1/-0	MAX	+/-0.05

STANDARD PACKAGE QUANTITY
(pieces/reel)
4,000



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

↑ REMINDERS

The products listed on this specification sheet are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property. Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this specification sheet.

- 1. Aerospace/Aviation equipment
- 2. Transportation equipment (cars, electric trains, ships, etc.)
- 3. Medical equipment
- 4. Power-generation control equipment
- 5. Atomic energy-related equipment
- 6. Seabed equipment
- 7. Transportation control equipment
- 8. Public information-processing equipment
- 9. Military equipment
- 10. Electric heating apparatus, burning equipment
- 11. Disaster prevention/crime prevention equipment
- 12. Safety equipment
- 13. Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/equipment or providing backup circuits, etc., to ensure higher safety.