


# **DUALSLIM USB-C Female-Male FEEDTHROUGH CONNECTOR**

Can be front or rear mounted in the panel



**VARIANTS** 

Part No.
CP30711
CP30711X
CP30711X1

DUALSLIM USB-C F-M Black plastic frame, CSK holes

DUALSLIM USB-C F-M Black plastic frame, Ø2.5 PLAIN holes

DUALSLIM USB-C F-M Black plastic frame, Ø3.2 PLAIN holes

## Feedthrough Features

- Fits standard rectangular cutout.
- Front or rear mounting through the panel.
- Various hole mounting options.
- No soldering or punch termination. Use standard cable for each connector style.
- Low rear profilé.

#### <u>General:</u>

Please note: Functionality is affected by cable quality, length and cable wiring configuration.

#### Matarial:

- 1. Insert: ABS UL94 HB
- 2. Plastic Frame: Polyamide UL94 V-2

### **USB-C Specification:**

Maximum Rated Current - 3A
Maximum Working Voltage - 30V
Withstanding Voltage - 100V for 1 minute.
Contact Resistance - 40 Milli-ohms Max.
Insulation Resistance - 100 Mega-ohms Min.
Insulator Flammability Rating - UL-94V0
Insertion Life - 10,000 Cycles.

For further information, contact sales@cliffuk.co.uk

# **Cliff Electronic Components Limited**,

76 Holmethorpe Avenue, Holmethorpe Ind. Estate, Redhill, Surrey RH1 2PF U.K.

Tel: +44 (0)1737 771375 Fax: +44 (0)1737 766012





www.cliffuk.co.uk

© CLIFF 11/2020 ISS.1