



RFHCM Series – 1012(0405)- RoHS Compliance

MULTILAYER CERAMIC COMMON MODE FILTER Halogens Free Product

P/N: RFHCM1012GD900B05T

*Contents in this sheet are subject to change without prior notice.



FEATURES and Application

- 1. Powerful components with composite co-fired material to solve EMI problem for high speed differential signal transmission line as USB, and LVDS, without distortion to high speed signal transmission.
- 2. MIPI, MHL serial interface in mobile device.

CONSTRUCTION



DIMENSIONS

Figure	Symbol	Dimension (mm)
	L	1.25 ± 0.10
	W	1.00 ± 0.10
	т	0.50 ± 0.10
	Р	0.55 ± 0.10
	C1	0.30 ± 0.10
	C2	0.20 ± 0.15



ELECTRICAL CHARACTERISTICS

RFHCM1012GD900B05T	Specification			
Common Mode Impedance	90 Ω ± 25% @ 100MHz			
DC Resistance	3.0 Ω max.			
Rated Current	100 mA max.			
Rated Voltage	10 V			
Insulation Resistance	100 MΩ min.			
Test Instruments	 Agilent E4991A RF IMPEDANCE / MATERIAL ANALYZER HP4338 MILLIOHMMETER Agilent E5071C ENA SERIES NETWORK ANALYZER Keithley 2410 1100V SOURCE METER 			
Operating & Storage Condition (Component) Operation Temperature Range: -40 ~ +85 ℃ Storage Temperature Range: -40 ~ +85 ℃				
Storage Condition before Soldering (Included packaging material) Storage Temperature Range: +5 ~ +40 ℃ Humidity: 30 to 70% relative humidity				
Typical Transmission Chart				
Impedance vs Frequency Characteristic: Insertion Loss vs Frequency Characteristic:				
1000 Common Mode 100 100 100 Different	tial Mode			
10 100 1,000	10,000 10 100 1,000 10,000 Frequency (MHz)			
Figure				





RELIABILITY TEST

Test item	Test condition	Criteria		
Temperature Cycle	A. Temperature : -40 ~ +85℃ B. Cycle : 100 cycles C. Dwell time : 30minutes Measurement : at ambient temperature 24 hrs after test completion	A. No mechanical damage B.Impedance value should be within ± : % of the initial value		
Operational Life	A. Temperature : 85° C ± 5°C B. Test time : 1000 hrs C. Apply current : full rated current Measurement : at ambient temperature 24 hrs after test completion	 A. No mechanical damage B.Impedance value should be within ± 20 % of the initial value 		
Biased Humidity	A. Temperature : $40 \pm 2^{\circ}$ C B. Humidity : $90 \sim 95 \%$ RH C. Test time : 1000 hrs D. Apply current : full rated current Measurement : at ambient temperature 24 hrs after test completion	 A. No mechanical damage B. Impedance value should be within ± 20 % of the initial value 		
Resistance to Solder Heat	A. Solder temperature : $260 \pm 5^{\circ}$ C B. Flux : Rosin C. DIP time : 10 ± 1 sec	 A. More than 95 % of terminal electrode should be covered with new solder B. No mechanical damage C.Impedance value should be within ± 20 % of the initial value 		
Steam Aging Test	A. Temperature : $93 \pm 2^{\circ}$ C B. Test time : 4 hrs C. Solder temperature : $235 \pm 5^{\circ}$ C D. Flux : Rosin E. DIP time : 5 ± 1 sec	More than 95 % of terminal electrode should be covered with new solder		

SOLDERING CONDITION

Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2,



Fig 2. Infrared soldering profile

ORDERING CODE

RF	НСМ	1012	G	D	900	В	05	Т
Walsin	Product Code	Dimension	Material	Product	Impedance	Internal	Dimension	Packing
RF device	HCM :	code (L*W)	Code	identification	Value	Code	Code (T)	T: Reeled
	Common Mode	1012 =		number	Ex:		05=0.50mm	
	Filter	Width 10,			900=90 ohm			
		Length 12,						

Minimum Ordering Quantity: 4000 pcs per reel.

PACKAGING

Type : Paper Carrier



Unit : mm

Symbol	Size	Symbol	Size
A	1.20±0.05	Po	4.00±0.10
В	1.45±0.05	P1	4.00±0.10
W	8.00±0.10	P2	2.00±0.05
E	1.75±0.05	Do	1.55±0.05
F	3.50±0.05	т	0.60±0.03

Reel dimensions



Taping Quantity:4000 pieces per 7" reel

CAUTION OF HANDLING

Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Medical equipment
- (5) Disaster prevention / crime prevention equipment
- (6) Traffic signal equipment
- (7) Transportation equipment (vehicles, trains, ships, etc.)
- (8) Applications of similar complexity and /or reliability requirements to the applications listed in the above.

Storage condition

- (1) Products should be used in 6 months from the day of WALSIN outgoing inspection.
- (2) Storage environment condition.
 - Products should be storage in the warehouse on the following conditions.
 - Temperature : +5 to +40°C
 - Humidity : 30 to 70% relative humidity
 - Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
 - Products should be storage on the palette for the prevention of the influence from humidity, dust and son on.
 - Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
 - Products should be storage under the airtight packaged condition.