# Cree<sup>®</sup> 5-mm Red/Amber Round LED C503B-RCS/RCN-030(30 degree minimum) C503B-ACS/ACN-030(30 degree minimum)

# **PRODUCT DESCRIPTION**

CREE 🔶

Round LEDs offer superior light output for excellent readability in sunlight and dependable performance. They provide extremely stable light output over long periods of time.

These lamps are made with an advanced optical-grade epoxy offering superior high-temperature and highmoisture-resistance performance in outdoor signal and sign applications.

# FEATURES

- Size (mm): 5
- Color and Typical Dominant Wavelength:Red (624nm) Wavelength:Amber (591nm)
- Luminous Intensity (mcd) C503B-RCS/RCN-030: (4180 - 8200) C503B-ACS/ACN-030: (5860 - 12000)
- Viewing angle: C503B-RCS/RCN-030: 30 degree minimum C503B-ACS/ACN-030: 30 degree minimum
- Lead Free
- RoHS Compliant

# APPLICATIONS

- Electronic Signs & Signals (ESS)
- Motorway Signs
- Variable Message Sign (VMS)
- Advertising signs
- Petrol Signs
- Amusement
- Roadway Signs

# ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^{\circ}C$ )

Items	Symbol	Absolute Maximum Rating	Unit		
Forward Current	I <sub>F</sub>	50 Note1	mA		
Peak Forward Current Note2	$I_{_{\rm FP}}$	200	mA		
Reverse Voltage	V <sub>R</sub>	5	V		
Power Dissipation	P <sub>D</sub>	130	mW		
Operation Temperature	T <sub>opr</sub>	-40 ~ +100	°C		
Storage Temperature	T <sub>stg</sub>	-40 ~ +100	°C		
Lead Soldering Temperature	T <sub>sol</sub>	Max. 260°C for 3 sec. max. (3 mm from the base of the epoxy bulb)			
Electrostatic Discharge Classification (MIL-STD-883E)	ESD	Class 2			

#### Note:

- 1. For long term performance the drive currents between 10mA and 30mA are recommended. Please contact CREE
- sales representative for more information on recommended drive conditions.
- 2. Pulse width  $\leq$ 0.1 msec, duty  $\leq$ 1/10.

# **TYPICAL ELECTRICAL & OPTICAL CHARACTERISTICS (T<sub>A</sub> = 25^{\circ}C)**

Characteristics	Color	Symbol	Condition	Unit	Minimum	Typical	Maximum
Forward Voltage	Red/Amber	V <sub>F</sub>	$I_{F} = 20 \text{ mA}$	V		2.1	2.6
Reverse Current	Red/Amber	I <sub>R</sub>	$V_{R} = 5 V$	μA			100
Dominant Wayalangth	Red	$\lambda_{\rm D}$	$I_{F} = 20 \text{ mA}$	nm	618	624	630
Dominant Wavelength	Amber	$\lambda_{\rm D}$	I <sub>F</sub> = 20 mA	nm	584	591	596
	C503B-RCS/RCN-030	$I_v$	$I_F = 20 \text{ mA}$	mcd	4180	6600	
Luminous Intensity	C503B-ACS/ACN-030	I <sub>v</sub>	I <sub>F</sub> = 20 mA	mcd	5860	6800	
50% Power Angle	C503B-RCS/RCN-030	201/2	I <sub>r</sub> = 20 mA	dog	30		
50% Fower Angle	C503B-ACS/ACN-030	2072	$I_F = 20 \text{ mA}$	deg	30		

Note: Continuous reverse voltage can cause LED damage.

# **INTENSITY BIN LIMIT (I**<sub>F</sub> = 20 mA)

C503B-RCS/RCN-030 (	(30	dearee	min)	)
C303D 1(C3/1(C11 030)		acgree		,

В	in Code	Min. (mcd)	Max. (mcd)	Bin Code	Min. (mcd)	Max. (mcd)	Bin Code	Min. (mcd)	Max. (mcd)
x	X0	4180	Xa 4180 5020						
^	XU	4100	5000	Xb	5020	5860			
				Ya	5860	7030	YA	5860	6500
Y	YO	5860	8200			5800 7050		6500	7200
				Yb	7030	8200	YC	7200	8200

#### C503B-ACS/ACN-030 (30 degree min)

В	in Code	Min. (mcd)	Max. (mcd)	Bin Code	Min. (mcd)	lin. (mcd) Max. (mcd)		Min. (mcd)	Max. (mcd)
				Ya	5860	7030	YA	5860	6500
Y	Y0	5860	8200				YB	6500	7200
				Yb	7030	8200	YC	7200	8200
7	70	0200	12000	Za	8200	10100			
Z	ZO	8200	12000	Zb	10100	12000			

 $\bullet$  Tolerance of measurement of luminous intensity is  $\pm 15\%$ 

# COLOR BIN LIMIT $(I_F = 20 \text{ mA})$

#### C503B-RCS/RCN-030 (30 degree min)

Bin Code	Min.(nm)	Max.(nm)
RA	618	630

#### C503B-ACS/ACN-030 (30 degree min)

Bin Code	Min.(nm)	Max.(nm)
A2	584	587
A3	587	590
A4	590	593
A5	593	596

• Tolerance of measurement of dominant wavelength is  $\pm 1$  nm

# **ORDER CODE TABLE\***

#### Red (30 degree min)

		Minuter	Luminous Intensity (mcd)			Dominant Wavelength				
Color	Kit Number	Viewing Angle	Min.	Max.	Color Bin	Min. (nm)	Color Bin	Max. (nm)	Package	Standoff
Red	C503B-RCS-CXaYCAA1-030	30	4180	8200	RA	618	RA	630	Bulk	Yes
Red	C503B-RCS-CXaYAAA1-030	30	4180	6500	RA	618	RA	630	Bulk	Yes
Red	C503B-RCS-CYAYBAA1-030	30	5860	6500	RA	618	RA	630	Bulk	Yes
Red	C503B-RCN-CXaYCAA1-030	30	4180	8200	RA	618	RA	630	Bulk	No
Red	C503B-RCN-CXaYAAA1-030	30	4180	6500	RA	618	RA	630	Bulk	No
Red	C503B-RCN-CYAYBAA1-030	30	5860	6500	RA	618	RA	630	Bulk	No
Red	C503B-RCS-CXaYCAA2-030	30	4180	8200	RA	618	RA	630	Ammo	Yes
Red	C503B-RCS-CXaYAAA2-030	30	4180	6500	RA	618	RA	630	Ammo	Yes
Red	C503B-RCS-CYAYBAA2-030	30	5860	6500	RA	618	RA	630	Ammo	Yes
Red	C503B-RCN-CXaYCAA2-030	30	4180	8200	RA	618	RA	630	Ammo	No
Red	C503B-RCN-CXaYAAA2-030	30	4180	6500	RA	618	RA	630	Ammo	No
Red	C503B-RCN-CYAYBAA2-030	30	5860	6500	RA	618	RA	630	Ammo	No

# **ORDER CODE TABLE\***

#### Amber (30 degree min)

			Luminous Intensity (mcd)		Dominant Wavelength					
Color	Kit Number	Viewing Angle	Min.	Max.	Color Bin	Min. (nm)	Color Bin	Max. (nm)	Package	Standoff
Amber	C503B-ACS-CY0Z0251-030	30	5860	12000	A2	584	A5	596	Bulk	Yes
Amber	C503B-ACS-CY0Z0341-030	30	5860	12000	A3	587	A4	593	Bulk	Yes
Amber	C503B-ACN-CY0Z0251-030	30	5860	12000	A2	584	A5	596	Bulk	No
Amber	C503B-ACN-CY0Z0341-030	30	5860	12000	A3	587	A4	593	Bulk	No
Amber	C503B-ACS-CY0Z0252-030	30	5860	12000	A2	584	A5	596	Ammo	Yes
Amber	C503B-ACS-CY0Z0342-030	30	5860	12000	A3	587	A4	593	Ammo	Yes
Amber	C503B-ACN-CY0Z0252-030	30	5860	12000	A2	584	A5	596	Ammo	No
Amber	C503B-ACN-CY0Z0342-030	30	5860	12000	A3	587	A4	593	Ammo	No
Amber	C503B-ACS-CYAZa251-030	30	5860	10100	A2	584	A5	596	Bulk	Yes
Amber	C503B-ACS-CYBZa251-030	30	6500	10100	A2	584	A5	596	Bulk	Yes
Amber	C503B-ACS-CYAZa341-030	30	5860	10100	A3	587	A4	593	Bulk	Yes
Amber	C503B-ACS-CYBZa341-030	30	6500	10100	A3	587	A4	593	Bulk	Yes
Amber	C503B-ACN-CYAZa251-030	30	5860	10100	A2	584	A5	596	Bulk	No
Amber	C503B-ACN-CYBZa251-030	30	6500	10100	A2	584	A5	596	Bulk	No
Amber	C503B-ACN-CYAZa341-030	30	5860	10100	A3	587	A4	593	Bulk	No
Amber	C503B-ACN-CYBZa341-030	30	6500	10100	A3	587	A4	593	Bulk	No
Amber	C503B-ACS-CYAZa252-030	30	5860	10100	A2	584	A5	596	Ammo	Yes
Amber	C503B-ACS-CYBZa252-030	30	6500	10100	A2	584	A5	596	Ammo	Yes
Amber	C503B-ACS-CYAZa342-030	30	5860	10100	A3	587	A4	593	Ammo	Yes
Amber	C503B-ACS-CYBZa342-030	30	6500	10100	A3	587	A4	593	Ammo	Yes
Amber	C503B-ACN-CYAZa252-030	30	5860	10100	A2	584	A5	596	Ammo	No
Amber	C503B-ACN-CYBZa252-030	30	6500	10100	A2	584	A5	596	Ammo	No
Amber	C503B-ACN-CYAZa342-030	30	5860	10100	A3	587	A4	593	Ammo	No
Amber	C503B-ACN-CYBZa342-030	30	6500	10100	A3	587	A4	593	Ammo	No

Notes:

1. The above kit numbers represent order codes that include multiple intensity-bin and color-bin codes. Only one intensity-bin code and one color-bin code will be shipped on each bulk. Single intensity-bin code and single color-bin codes will not be orderable.

2. Please refer to the "Cree LED Lamp Reliability Test Standards" document <sup>#1</sup> for reliability test conditions.


3. Please refer to the "Cree LED Lamp Soldering & Handling" document <sup>#2</sup> for information about how to use this LED product safely.


#1: Refer to http://www.cree.com/led-components/media/documents/LED\_Lamp\_Reliability\_Test\_Standard.pdf


#2: Refer to http://www.cree.com/led-components/media/documents/sh-HB.pdf




#### GRAPHS









(RELATIVE LUMINOUS INTENSITY)

5.0

Angle 60° -30° 30° 90° FIG.6 FAR FIELD PATTERN

The above data are collected from statistical figures that do not necessarily correspond to the actual parameters of each single LED. Hence, these data will be changed without further notice.




#### **MECHANICAL DIMENSIONS**


All dimensions are in mm. Tolerance is  $\pm 0.25$  mm unless otherwise noted.

An epoxy meniscus may extend about 1.5 mm down the leads.


Burr around bottom of epoxy may be 0.5 mm max.

#### C503B-RCS-030/C503B-ACS-030:





C503B-RCN-030/C503B-ACN-030:



# NOTES

#### **RoHS** Compliance

The levels of RoHS-restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application in accordance with EU Directive 2011/65/EC (RoHS2), as implemented by EU member states on January 2, 2013 and amended on March 31, 2015 by EU Directive 2015/863/EU.

RoHS Declarations for this product can be obtained from your Cree representative or from the Product Ecology section of the Cree website.

#### Vision Advisory Claim


Users should be cautioned not to stare at the light of this LED product. The bright light can damage the eye.



# **KIT NUMBER SYSTEM**

All dimensions in mm.Cree LED lamps are tested and sorted into performance bins. A bin is specified by ranges of color, forward voltage, and brightness. Sorted LEDs are packaged for shipping in various convenient options. Please refer to the "Cree LED Lamp Packaging Standard" document for more information about shipping and packaging options.

Cree LEDs are sold by order codes in combinations of bins called kits. Order codes are configured in the following manner:






# **REFLOW SOLDERING**

The LED soldering specification is shown below(suitable for both leaded solder & lead-free solder):

Manual Solder	ing	Solder Dipping			
Soldering iron	35 W max	Preheat	110 °C max		
Tomporatura	300 °C max	Preheat time	60 seconds max		
Temperature	Sou oc max	Solder-bath temperature	260 °C Max		
Soldering time	3 seconds max	Dipping time	5 seconds max		
Position	Not less than 3 mm from the base of the package.	Position	Not less than 3 mm from the base of the package.		

• Manual soldering onto the PCB is not recommended because soldering time is uncontrollable.

• The recommended wave soldering is as below:



- Do not apply any stress to the LED package, particularly when heated.
- Only bottom preheat is suggested & should not preheat on top in order to reduce thermal stress experienced by the LEDs.
- The LEDs must not be re used once they have been extracted from PCB.
- After soldering the LEDs, the package should be protected from mechanical shock or vibration until the LEDs have reached 40 °C or below.
- Precautions must be taken as mechanical stress on the LEDs may be caused by PCB warpage or from the clinching and cutting of the LED leads.
- When it is necessary to clam the LEDs during soldering, it is important to ensure no mechanical stress is exerted on the LEDs.
- Cut the LED lead at normal room temperature. Lead cutting at high temperature may cause failure of the LEDs.

Refer to "http://www.cree.com/led-components/media/documents/sh-HB.pdf" for soldering & handling details.



# PACKAGING

#### **Features:**

- The LEDs are packed in cardboard boxes after packaging in normal or anti-electrostatic bags.
- Cardboard boxes will be used to protect the LEDs from mechanical shock during transportation.
- The boxes are not water resistant, and they must be kept away from water and moisture.
- The Bulk Pack types of packaging.
- Max 500 pcs per bulk and Max 2500 pcs per ammo.

# **Bulk Pack Packaging Type:**

# Ammo Pack Packaging Type:

