


www.vishay.com

Vishay Semiconductors

# Schottky Rectifier, 2 x 15 A






PRODUCT SUMMARY	
Package	TO-220AB
I <sub>F(AV)</sub>	2 x 15 A
V <sub>R</sub>	35 V, 45 V
V <sub>F</sub> at I <sub>F</sub>	See Electrical table
I <sub>RM</sub> max.	40 mA at 125 °C
T <sub>J</sub> max.	150 °C
Diode variation	Common cathode
E <sub>AS</sub>	16 mJ

#### **FEATURES**

- 150 °C T<sub>J</sub> operation
- Low forward voltage drop
- High frequency operation





- term reliability
- Compliant to RoHS Directive 2002/95/EC
- Designed and qualified according to JEDEC-JESD47
- Halogen-free according to IEC 61249-2-21 definition (-N3 only)

#### **DESCRIPTION**

This center tap Schottky rectifier has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 150 °C junction temperature. Typical applications are in switching power supplies, converters, freewheeling diodes, and reverse battery protection.

MAJOR RATING	GS AND CHARACTERISTICS		
SYMBOL	CHARACTERISTICS	VALUES	UNITS
I <sub>F(AV)</sub>	Rectangular waveform (per device)	30	А
V <sub>RRM</sub>		35/45	V
I <sub>FRM</sub>	T <sub>C</sub> = 130 °C (per leg)	30	Δ.
I <sub>FSM</sub>	t <sub>p</sub> = 5 μs sine	1060	A
V <sub>F</sub>	30 A <sub>pk</sub> , T <sub>J</sub> = 125 °C	0.73	V
TJ	Range	- 65 to 150	°C

VOLTAGE RATING	GS					
PARAMETER	SYMBOL	VS-MBR2535CTPbF	VS-MBR2535CT-N3	VS-MBR2545CTPbF	VS-MBR2545CT-N3	UNITS
Maximum DC reverse voltage	V <sub>R</sub>	35	35	45	45	V
Maximum working peak reverse voltage	V <sub>RWM</sub>	33	33	45	45	V

ABSOLUTE MAXIMUM RATINGS						
PARAMETER	SYMBOL	TEST (	CONDITIONS	VALUES	UNITS	
Maximum average per leg		$I_{F(AV)}$ $T_C = 130$ °C, rated $V_R$		15		
forward current per device	IF(AV)	TC = 130 C, rated VR		30		
Peak repetitive forward current per leg	I <sub>FRM</sub>	Rated V <sub>R</sub> , square wave, 20	Rated V <sub>R</sub> , square wave, 20 kHz, T <sub>C</sub> = 130 °C			
Non-repetitive peak surge current	I <sub>ESM</sub>	5 μs sine or 3 μs rect. pulse	Following any rated load condition and with rated V <sub>RRM</sub> applied	1060	Α	
, ,	. 6	Surge applied at rated load conditions halfwave, single phase, 60 Hz		150		
Non-repetitive avalanche energy per leg	E <sub>AS</sub>	$T_J = 25  ^{\circ}\text{C},  I_{AS} = 2  \text{A},  L = 8  \text{mH}$		16	mJ	
Repetitive avalanche current per leg	I <sub>AR</sub>	Current decaying linearly to Frequency limited by T <sub>J</sub> ma		2	Α	

Revision: 30-Aug-11 Document Number: 94291



www.vishay.com

# Vishay Semiconductors

ELECTRICAL SPECIFICATIONS							
PARAMETER	SYMBOL	TEST COND	DITIONS	VALUES	UNITS		
Maximum forward voltage drop	V <sub>FM</sub> <sup>(1)</sup>	30 A	T <sub>J</sub> = 25 °C	0.82	V		
Maximum forward voltage drop	V-M \ /	30 A	T <sub>J</sub> = 125 °C	0.73	V		
Maximum instantaneous roverse current	I <sub>RM</sub> <sup>(1)</sup>	T <sub>J</sub> = 25 °C	Rated DC voltage	0.2	mA		
Maximum instantaneous reverse current	'RM`'	T <sub>J</sub> = 125 °C	haled DC vollage	40			
Threshold voltage	V <sub>F(TO)</sub>	$T_{.1} = T_{.1}$ maximum	0.355	V			
Forward slope resistance	r <sub>t</sub>	rj = rj maximum	12.3	mΩ			
Maximum junction capacitance	C <sub>T</sub>	$V_R = 5 V_{DC}$ (test signal range 100 kHz to 1 MHz) 25 °C		700	pF		
Typical series inductance	L <sub>S</sub>	Measured from top of terminal to mounting plane		8.0	nΗ		
Maximum voltage rate of change	dV/dt	Rated V <sub>R</sub>		10 000	V/µs		

#### Note

 $<sup>^{(1)}~</sup>$  Pulse width < 300  $\mu s,~duty~cycle < 2~\%$ 

THERMAL - MECHANICAL SPECIFICATIONS							
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS			
Maximum junction temperature range	TJ		- 65 to 150	°C			
Maximum storage temperature range	T <sub>Stg</sub>		- 65 to 175	C			
Maximum thermal resistance, junction to case per leg	R <sub>thJC</sub>	DC operation	1.5	°C/W			
Typical thermal resistance, case to heatsink	R <sub>thCS</sub>	Mounting surface, smooth and greased	0.50	O/ <b>VV</b>			
Approximate weight			2	g			
Approximate weight			0.07	OZ.			
Mounting torque minimu	ım	Non-lubricated threads	6 (5)	kgf · cm			
maximu	ım	Non-lubricated tilleads	12 (10)	(lbf · in)			
Marking device		Casa style TO 220AB	MBR2	535CT			
ivial Killy device		Case style TO-220AB	MBR2	545CT			

Vishay Semiconductors

www.vishay.com




Fig. 1 - Maximum Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)




Fig. 4 - Maximum Thermal Impedance ZthJC Characteristics (Per Leg)




Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)




Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)


#### Note

 $\begin{array}{ll} \text{(1)} & \text{Formula used: } T_C = T_J - (Pd + Pd_{REV}) \ x \ R_{thJC}; \\ Pd = \text{Forward power loss} = I_{F(AV)} \ x \ V_{FM} \ at \ (I_{F(AV)}/D) \ (\text{see fig. 6}); \\ Pd_{REV} = \text{Inverse power loss} = V_{R1} \ x \ I_R \ (1 - D); \ I_R \ at \ V_{R1} = Rated \ V_R \end{array}$ 

Vishay Semiconductors

### ORDERING INFORMATION TABLE





- Vishay Semiconductors product

2 - Schottky MBR series

Current rating (30 A)

35 = 35 V 45 = 45 V

5 - CT = Essential part number

Environmental digit

• PbF = Lead (Pb)-free and RoHS compliant

• -N3 = Halogen-free, RoHS compliant, and totally lead (Pb)-free

ORDERING INFO	RMATION (Example)		
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION
VS-MBR2535CTPbF	50	1000	Antistatic plastic tube
VS-MBR2535CT-N3	50	1000	Antistatic plastic tube
VS-MBR2545CTPbF	50	1000	Antistatic plastic tube
VS-MBR2545CT-N3	50	1000	Antistatic plastic tube


	LINKS TO RELAT	ED DOCUMENTS
Dimensions		www.vishay.com/doc?95222
Part marking information	TO-220AB PbF	www.vishay.com/doc?95225
	TO-220AB -N3	www.vishay.com/doc?95028



## Vishay Semiconductors

## **TO-220AB**

#### **DIMENSIONS** in millimeters and inches



#### **Diodes**

- 1. Anode/open 2. - Cathode
- 3. Anode

Conforms to JEDEC outline TO-220AB

MILLIMETERS

MILLIM	IETERS	INC	INCHES		
MIN.	MAX.	MIN.	MAX.	NOTES	
4.25	4.65	0.167	0.183		
1.14	1.40	0.045	0.055		
2.56	2.92	0.101	0.115		
0.69	1.01	0.027	0.040		
0.38	0.97	0.015	0.038	4	
1.20	1.73	0.047	0.068		
1.14	1.73	0.045	0.068	4	
0.36	0.61	0.014	0.024		
0.36	0.56	0.014	0.022	4	
14.85	15.25	0.585	0.600	3	
8.38	9.02	0.330	0.355		
11.68	12.88	0.460	0.507	6	
	MIN. 4.25 1.14 2.56 0.69 0.38 1.20 1.14 0.36 0.36 14.85 8.38	4.25     4.65       1.14     1.40       2.56     2.92       0.69     1.01       0.38     0.97       1.20     1.73       1.14     1.73       0.36     0.61       0.36     0.56       14.85     15.25       8.38     9.02	MIN.         MAX.         MIN.           4.25         4.65         0.167           1.14         1.40         0.045           2.56         2.92         0.101           0.69         1.01         0.027           0.38         0.97         0.015           1.20         1.73         0.047           1.14         1.73         0.045           0.36         0.61         0.014           0.36         0.56         0.014           14.85         15.25         0.585           8.38         9.02         0.330	MIN.         MAX.         MIN.         MAX.           4.25         4.65         0.167         0.183           1.14         1.40         0.045         0.055           2.56         2.92         0.101         0.115           0.69         1.01         0.027         0.040           0.38         0.97         0.015         0.038           1.20         1.73         0.047         0.068           1.14         1.73         0.045         0.068           0.36         0.61         0.014         0.024           0.36         0.56         0.014         0.022           14.85         15.25         0.585         0.600           8.38         9.02         0.330         0.355	

SYMBOL	IVIILLIIV	IEIENO	INCHES		NOTES
STIVIBOL	MIN.	MAX.	MIN.	MAX.	NOTES
E	10.11	10.51	0.398	0.414	3, 6
E1	6.86	8.89	0.270	0.350	6
E2	-	0.76	-	0.030	7
е	2.41	2.67	0.095	0.105	
e1	4.88	5.28	0.192	0.208	
H1	6.09	6.48	0.240	0.255	6, 7
L	13.52	14.02	0.532	0.552	
L1	3.32	3.82	0.131	0.150	2
ØΡ	3.54	3.73	0.139	0.147	
Q	2.60	3.00	0.102	0.118	
θ	90° t	o 93°	90° t	o 93°	

INCHES

- (1) Dimensioning and tolerancing as per ASME Y14.5M-1994
- (2) Lead dimension and finish uncontrolled in L1
- (3) Dimension D, D1 and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Dimension b1, b3 and c1 apply to base metal only
- (5) Controlling dimensions: inches
- Thermal pad contour optional within dimensions E, H1, D2 and
- $^{(7)}$  Dimensions E2 x H1 define a zone where stamping and singulation irregularities are allowed
- Outline conforms to JEDEC TO-220, except A2 (maximum) and D2 (minimum) where dimensions are derived from the actual package outline

Lead tip



## **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000