## **SPECIFICATIONS**


(RoHS Compliant)

 Model Number:
 CLE3L2
 Version: 02

 Part Number:
 19020190A
 Aug 07, 2018



#### **Mechanical Drawing:**



#### **Motor:**

 $\begin{array}{lll} \mbox{Nominal Voltage} & = 230 \mbox{ VAC} \\ \mbox{Frequency} & = 50/60 \mbox{ Hz} \\ \mbox{Nominal Running Current} & = 0.24 \ / \ 0.25 \mbox{ amps} \\ \mbox{Max. Locked Rotor Current} & = 0.355 \mbox{ amps} \\ \mbox{Running Power} & = 60/60 \mbox{ watts} \\ \mbox{Average Speed} & = 1400/1650 \mbox{ RPM} \end{array}$ 

Bearings = Ball

Air Flow = 455/550 CFM Acoustic: = 45.4/49.2 dBA

#### **Construction:**

Venturi: Aluminum, Black

Propeller: Plastic, Black, UL 94V-0

#### Life Expectancy:

This fan is designed for continuous duty life of 46,000

hours at 70°C.

#### **Additional Features:**

Permanent Split Capacitor

**Automatic Restart Thermal Protector** 

Class B Insulation

Operating Temperature: -10°C to 70°C Storage Temperature: -40°C to 85°C

#### **Termination:**

24" Lead wires, 18 AWG, UL 1015

### **Agency Approvals:**

UL, CUL, CE

# **PQ** Curve:

