

HDC MPN 6.0 M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold

Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com





Make your connections fit for the future With the advanced solutions from RockStar® ModuPlug

Industrial applications are becoming increasingly complex. The demands being made of the connectivity used are growing at the same time. Functionality in the smallest of installation spaces, safe installation and a fast retrofitting process are just some of the product properties being called for. Not only does our RockStar® ModuPlug modular plug-in connector system meet current market requirements; it has been specially designed with the future in mind too. Using the individual modules, you combine all the necessary functions for power, signal and data transmission in a single interface. Thanks to the new variety of module sizes, you can fit more applications than ever before in one plug-in connector. The modules reduce the amount of space required and cut costs when compared with fixed-pole inserts and other modular plug-in connector systems. The sophisticated frames and modules can be installed with extreme ease and integrated into HDC enclosures with the IP65 and IP68 protection classes. You can even use the RockStar® ModuPlug to supplement existing applications without any need to make system adjustments. As an experienced Industrial Connectivity partner, Weidmüller offers ultra-modern connectivity with maximum reliability. So you can create customised solutions for future-proof connections with RockStar® too.

General ordering data

HDC MPN 6.0 M		
<u>2637350000</u>		
Pneumatic contact		
4050118654615		
10 pc(s).		
	2637350000 Pneumatic contact 4050118654615	

Creation date June 15, 2020 9:47:37 PM CEST



HDC MPN 6.0 M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold

Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com

Technical data

Dimensions and weights					
Net weight	1.371 g				
Temperatures					
Limit temperature	-40 °C 80 °C				
Pneumatic contact					
Thousand Contact					
Operating pressure	≤8 bar	Inner hose diameter	6 mm		
Contact with valve	No				
Classifications					
ETIMA C. O.	F0000040	ETIMA 7.0	50000040		
ETIM 6.0 eClass 9.0	EC002943 27-44-02-92	ETIM 7.0 eClass 9.1	EC002943 27-44-02-92		
eClass 10.0	27-44-02-92	eciass 9.1	27-44-02-92		
Approvals					
ROHS	Conform				
Downloads					
Engineering Data	STEP				