

Label - MM-EML (EX24)R C1 TR/BK - 1116133

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Label, Roll, transparent/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 22 mm

Product Description

The MM-EML... polyester self-adhesive labels are available as continuous media for equipment marking.

Your advantages

- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- The self-adhesive material in continuous format is particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application
- The material is cUL certified
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing



Key Commercial Data

Packing unit	1 pc
GTIN	4 063151 040888
GTIN	4063151040888
Weight per Piece (excluding packing)	80.000 g
Custom tariff number	96121010
Country of origin	China

Technical data

Dimensions

Length (b)	8 m
Width (a)	24 mm



Label - MM-EML (EX24)R C1 TR/BK - 1116133

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C 150 °C
I Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Color	transparent/black
Components	free from silicone, halogen, and cadmium
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	adhesive

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

	ı
eCl@ss 9.0	27400629
00.600 0.0	

Approvals

Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized



http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

MH48542