


NOTES: UNLESS OTHERWISE SPECIFIED

- 1. ALL DIMENSIONS FOR REFERENCE ONLY.
- 2. OUTPUT SHAFT DIRECTION IS REVERSIBLE.
- 3. MOTOR IS NOT DESIGNED FOR STALL.







PART #	VOLTS	SPEED	TORQUE	CURRENT
DCM-1021-24	24	20 RPM	65 OZ-IN	0.20 AMPS
DCM-1021-12	12	10 RPM	65 OZ-IN	0.15 AMPS

I/WE CERTIFY THAT SAMPLES OF THIS MOTOR HAVE BEEN FULLY TESTED BY THE UNDERSIGNED AND THAT ALL SPECIFICATIONS HAVE BEEN REVIEWED FOR PRODUCTION. MULTIPRODUCTS COMPANY, INC. IS NOT RESPONSIBLE FOR MOTORS THAT FAIL IN THE FIELD DUE TO INSUFFICIENT TESTING OF THE SAMPLE MOTORS. I/WE AGREE TO PROVIDE MULTIPRODUCTS COMPANY. INC. WITH CURRENT DRAWINGS AND IN-HOUSE TEST PROCEDURES AS THEY BECOME AVAILABLE. ANY CHANGES THAT I/WE MAY MAKE WHICH OCCUR AFTER THE DATE SHOWN ARE SUBJECT TO REVIEW AND MAY AFFECT UNIT PRICE AND/OR DELIVERY DATES.

SIGNATURE PRINT NAME IN ORDER TO BEGIN PRODUCTION, MULTIPRODUCTS COMPANY, INC. MUST HAVE SIGNED APPROVAL.

Γ	Α	ADDED DCM-1021-24, REDRAWN		
)	REV.	DESCRIPTION	DATE	ECO#

TOLERANCES X.XX: ±.010 X.XXX: ±.005

FRACTION: ±1/64 ANGLE: ±2°

UNLESS OTHERWISE SPECIFIED

MULTI PRODUCTS

Company, Inc.

PART NAME/DESCRIPTION:

DC GEARHEAD MOTOR

	DRAWN BY: DAB	DATE: 4/10/2013	SCALE: 1:1	MATERIAL: -
	CHK'D BY: RP	DATE: 4/10/2013	PART NUMBER:	MOD-DCM-1021
)	APPR'D BY: -	DATE:	10100-0010-1021	