

Description: 1005 5GNR-n77 Band Pass Filter

PART NUMBER: BPF1005LRPPR3750L

Features:

Compact size: 1.0x0.5x0.38mm

RoHS compliant

Applications:

WWAN

• 5GNR

For n77 Band

ELECTRICAL SPECIFICATIONS

Item	Frequency Range(MHz)	Min.	Тур.	Max.
Insertion Loss (dB)	3300~4200	-	1.60	1.80
Insertion Loss (dB) at -40~85°C	3300~4200	-	-	2.30
Return Loss (dB)	3300~3800	15	21.0	-
	600~1610	40	42.6	-
	1710~1785	38	48.0	-
	1780~1860	48	54.0	-
	1805~2200	30	39.5	-
	2300~2620	25	36.1	-
Attonuction (dP)	2620~2690	20	33.8	-
Attenuation (dB)	5150~5850	20	22.5	-
	5850~6600	20	22.7	-
	6600~7600	25	27.1	-
	7600~8400	20	36.6	-
	9900~12600	10	26.8	-
	13200~18000	10 (Ref.)	15.0	-

Operating Temperature Range: -40~85°C

Power Capacity: 3W max.

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION



This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:





Description: 1005 5GNR-n77 Band Pass Filter

PART NUMBER: BPF1005LRPPR3750L

MECHANICAL DIMENSION

Outline





Termination


Terminal name	Function
P1	NC
P2	GND
P3	NC
P4	Output
P5	GND
P6	Input


(6)	(5)	(4)
(1)	(2)	(3)

Mechanical

	Dimension
L (mm)	1.00±0.05
W (mm)	0.50 ± 0.05
T (mm)	0.38(Max.)
a (mm)	0.18 ± 0.05
b (mm)	0.125 ± 0.05
c (mm)	0.18±0.05
d (mm)	0.15±0.05
e (mm)	0.36 ± 0.05
D1-D2	0 ± 0.04
D3-D4	0 ± 0.04

Reference design of EVB





Unit: mm


Line width should be designed to match 50Ω characteristic impedance, depending on PCB material and thickness.



Description: 1005 5GNR-n77 Band Pass Filter


PART NUMBER: BPF1005LRPPR3750L

MEASURING DIAGRAM



Test Instrument: Agilent E5071A Network Analyzer.

ELECTRICAL PERFORMANCES



Frequency Characteristics



Description: 1005 5GNR-n77 Band Pass Filter

PART NUMBER: BPF1005LRPPR3750L

		REVISION HISTORY	
Revision	Date	Description	
Version 1	Jun. 15, 2022	- New issue	