
Bansbach easylift

		SPECIFICATIONS				
		Model		Rated Torque	Damping Direction	Max Rotation Speed
		FRN-C2-R301		(30±8.0)X10 ⁻³ Nm (300±80gfcm)	Clockwise	50 RPM
Max Cycle Rate	Operating Temperature		Weight	t Body & Cap Material	Rotating S Materia	
10 cycles/min.	0 ~ 50°C		3.2g	Polycarbonate	e Polyacet	al Silicone Oil

Note 1) Rated torque measured at a rotation speed of 20rpm at 23°C Note 2) Torque can be customized by changing the oil viscosity

There are dampers that generate torque in both directions and one-way torque in the clockwise direction or counter clockwise direction when the rotating axle is viewed from the top





- Speed characteristics: A rotary damper's torque varies according to the rotation speed. In general, as shown in the graph to the left, the torque increases as the rotation speed increases, and the torque decreases as the rotation speed decreases. In addition, please note that the starting torque slightly differs from the rated torque.
- Temperature characteristics: A rotary damper's torque varies according to the ambient temperature. In addition, as shown in the graph to the left, the torque decreases as the ambient temperature increases, and the torque increases as the ambient temperature decreases. This is because the viscosity of the silicone oil inside the damper varies according to the temperature. When the temperature returns to normal, the torque will return to normal as well.