

# **Single Port Vertical Mount RJ45**

ARV11-4447I


- 10/100/1000 Gigabit Base-T for Ethernet Applications
- RJ45 Jack cavity conforms to FCC rules and regulations part 68, SUB Part F
- Industrial Temp: -40°C to ± 85°C
- DC Resistance: 1.2Ω MAX
- Available in other circuit designs
- Other LED pattens available




Electrical Specifications @ 25°C										
OCL(µH Min) @100KHz, 0.1V	Turns Ratio @100KHz	Insertion Loss (dB Max)	Return Loss (dB Min)			Cross Talk (dB Min)	CMR (dB Min)	Hi-Pot VDC		
With 8mA DC Bias		1-100MHz	1-30MHz	30-50MHz	60-80MHz	80-100MHz	1-100MHz	1-100 MHz	2250	
350	1CT:1CT	-1.2	-16	-12	-10	-8	-30	-30		

All specifications subject to change without notice

## **MECHANICAL**






#### Dimensions: (mm)

Α	В	C	D
16.10	16.87	23.15	2.80






### **SCHEMATICS**



### **PCB LAYOUT**



### **NOTES**

1. Connector Material:

Housing: PA66 Black UL94 V-0

Shield: Brass Shield Plating: Nickel

Contact: Phosphor Bronze

Contact Plating: Selective Gold, 30 Micro Inchs MIN in contact area

- Pin not electrically connected maybe omitted see electrical drawing for omitted Pins
- 3. RJ45 cavities conform to FCC rules and regulations part 6B
- 4. The part is recommended for IR soldering process peak soldering temperature is 260°C Max, 10 Secs Max