



No. of PIN/ROW	Dimension Information						
	A	B	C	D	E	F	G
2x06	8.37	6.35	9.37	10.77	11.87	12.60	10.10
2x08	10.91	8.89	11.91	13.31	14.41	15.14	12.64
2x10	13.45	11.43	14.45	15.85	16.95	17.68	15.18
2x13	17.26	15.24	18.26	19.66	20.76	21.49	18.99
2x16	21.07	19.05	22.07	23.47	24.57	25.30	22.80
2x20	26.15	24.13	27.15	28.55	29.65	30.38	27.88
2x23	29.96	27.94	30.96	32.36	33.46	34.19	31.69
2x25	32.50	30.48	33.50	34.90	36.00	36.73	34.23
2x34	43.93	41.91	44.93	46.33	47.43	48.16	45.66
2x40	51.55	49.53	52.55	53.95	55.05	55.78	53.28

REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
A	NEW	INTERIM INITIAL RELEASE.	2021.09.28	廖昌紅
B	△	Correction Of Cavity No. Position	2022.01.06	廖昌紅

Specifications
 Current Rating:1.70Amp/PIN.
 Insulation Resistance:10000MΩMin.
 Dielectric Withstanding Voltage:500VAC
 Contact Resistance:25mΩMax.
 Operating Temperature:-55°C to +125°C
 Materials
 Contact Material:Phosphor Bronze
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 LCP or the equivalent material
 ☆All materials must meet GREENCONN hazardous substances control standards.
 "★": Critical Characteristics.
 indicates product characteristics, functionalities, and manufacturing processes regarding to customer's specifications
 "☆": Safety Features
 indicates product characteristics, functionalities, and manufacturing processes complying to legal regulations stated by local government

Pin No.	Dim.H
≤25Pin	0.12
>25Pin	0.15



Ordering Information

C BEC224- XX XX B 001 C 1 A X

No. of Pins per Row: 06,08,10,13,16, 20,23,25,34,40
 Standard Plating: 79=5u"Au/80~160u"Matte Tin, 05=1u"Au/80~160u"Matte Tin
 Selective Plating: 02=Gold Flash
 Color: 1=Black
 Standard Packing: F=Cap+Tape&Reel, C=Tube, E=Cap+Tube
 Selective Packing: X

Greenconn
 Website: www.greenconn.com
 E-mail: sales@greenconn.com

REV. B	UNIT. mm	SCALE. 3:1	PAGE. 1/1
--------	----------	------------	-----------

GENERAL TOLERANCE	
X.*±5.0°	X.±0.30
.X'±3.0°	.X±0.25
.XX'±2.0°	.XX±0.15
.XXX'±1.0°	.XXX±0.10

DESIGNED: 廖昌紅 DATE: 2022.01.06
 CHECKED: 木子 日期: 2022.1.7
 APPROVED: 日期: 2022.01.07

DWG. NO. CBEC224-CB001
 PART NO. CBEC224-XXXXB001C1AX

TITLE. 1.27 BOARD TO BOARD FEMALE DUAL ROW SMT TYPE CONNECTOR