


KEY (SIGNAL PRESS-FIT)		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
19	8.00	4.30

KEY (POWER PRESS-FIT)		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
P01	6.50	4.30
P02	7.25	4.30
P03	8.00	4.30
P16	5.00	4.30
P17	5.75	4.30



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE

SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCj www.fciconnect.com	
ltr	ecr no.	dr	date	linear	0.X ±0.3	COPY		projection	title MONOBLOCK HEADER ASSEMBLY PRESS-FIT, 4 ROW, 6 MOD
H					0.XX ±0.13	MM			
					0.XXX ±.051	3:2			
				angles	0° ±2°	scale		product family METRAL code	
				dr	T.BRUNGARD 06/05/00	A		size	
				engr	M.STRAWSER 5/31/00	70463		213	
				chr	M.STRAWSER 06/05/00			sheet	
				appd	M.STRAWSER 06/05/00			2	
sheet index	revision sheet								




This document is the property of and embodies
 CONFIDENTIAL and PROPRIETARY information of FCj.
 No part of the information shown on this
 document may be used in any way or disclosed
 to others without the written consent of FCj.
 Copyright FCj.

METRAL P/N	ROW	PM					SM					SM					SM					SM					PM														
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36				
70463-X005 SEE NOTE 8 LEAD FREE OPTION	D	P01		P01			3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01		P01		
	C	P01		P01			3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01		P01		
	B	P01		P01			3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01		P01		
	A	P01		P01			3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01		P01		

METRAL P/N	ROW	PM					SM					SM					SM					SM					PM														
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36				
70463-X006 SEE NOTE 8 LEAD FREE OPTION	D	P17		P17			2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P17		P17		
	C	P17		P17			2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P17		P17		
	B	P02		P02			4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	P02		P02		
	A	P17		P17			2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P17		P17		

METRAL P/N	ROW	PM					SM					SM					SM					SM					PM														
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36				
70463-X007 SEE NOTE 8 LEAD FREE OPTION	D	P01		P01			3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01		P01		
	C	P02		P02			4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	P02		P02		
	B	P03		P03			19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03		P03		
	A	P03		P03			19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03		P03		

METRAL P/N	ROW	PM					SM					SM					SM					SM					PM														
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36				
70463-X008 SEE NOTE 8 LEAD FREE OPTION	D	P01		P01			3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01		P01		
	C	P01		P01			3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01		P01		
	B	P03		P03			19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03		P03		
	A	P01		P01			3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01		P01		

mat'l code				--		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ±0.3		COPY		 projection	title	
H					0.XX ±0.13		MM			MONOBLOCK HEADER ASSEMBLY	
					0.XXX ±.051		3:2			PRESS-FIT, 4 ROW, 6 MOD	
				angles	0° ±2°		 MM		product family		
				dr	T.BRUNGARD	06/05/00	scale		METRAL		
				engr	M.STRAWSER	5/31/00	A		code		
				chr	M.STRAWSER	06/05/00	70463		213		
				appd	M.STRAWSER	06/05/00	4		sheet		
sheet index		revision sheet								4	





This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

METRAL P/N	ROW	PM						SM						SM						SM						SM						PM							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36		
70463-X009 SEE NOTE 8 LEAD FREE OPTION	D	P17		P17		2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P17		P17	
	C	P17		P17		2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P17		P17	
	B	P17		P17		2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P17		P17	
	A	P17		P17		2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P17		P17	

METRAL P/N	ROW	PM						SM						SM						SM						SM						PM							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36		
70463-X010 SEE NOTE 8 LEAD FREE OPTION	D	P02		P02		4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	P02		P02	
	C	P02		P02		4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	P02		P02	
	B	P02		P02		4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	P02		P02	
	A	P02		P02		4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	P02		P02	

METRAL P/N	ROW	PM						SM						SM						SM						SM						PM							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36		
70463-X011 SEE NOTE 8 LEAD FREE OPTION	D	P03		P03		19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03		P03	
	C	P03		P03		19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03		P03	
	B	P03		P03		19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03		P03	
	A	P03		P03		19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03		P03	

METRAL P/N	ROW	SM						SM						SM						SM						SM						PM							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36		
70463-X012 SEE NOTE 8 LEAD FREE OPTION	D	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	P16		P16	
	C	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	P16		P16	
	B	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	P16		P16	
	A	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	P16		P16	

mat'l code				--				tolerances unless otherwise specified				CUSTOMER				 www.fciconnect.com					
ltr	ecn no.	dr	date	linear				0.X ±0.3				COPY				title					
H				linear				0.XX ±0.13				projection				MONOBLOCK HEADER ASSEMBLY					
				angles				0.XXX ±.051								PRESS-FIT, 4 ROW, 6 MOD					
				dr				T.BRUNGARD		06/05/00		MM				product family		METRAL		code	
				engr				M.STRAWSER		5/31/00		← MM →				size		dwg no		213	
				chr				M.STRAWSER		06/05/00		scale				A		70463		sheet	
				appd				M.STRAWSER		06/05/00		3:2						5			
sheet index		revision sheet																			



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

This document is the property of and embodies
 CONFIDENTIAL and PROPRIETARY information of FCI.
 No part of the information shown on this
 document may be used in any way or disclosed
 to others without the written consent of FCI.
 Copyright FCI.



A

B

1 | 2

3 |

4

METRAL P/N	ROW	SM						SM						SM						SM						SM						PM											
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36						
70463-X013 SEE NOTE 8 LEAD FREE OPTION	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	PI6						PI6					
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	PI6						PI6					
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	PI6						PI6					
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01						P01					



METRAL P/N	ROW	SM						SM						SM						SM						SM						PM											
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36						
70463-X014 SEE NOTE 8 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01						P01					
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	PI7						PI7					
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	PI7						PI7					
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01						P01					

METRAL P/N	ROW	SM						SM						SM						SM						SM						PM											
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36						
70463-X015 SEE NOTE 8 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01						P01					
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01						P01					
	B	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01						P01					
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01						P01					

METRAL P/N	ROW	SM						SM						SM						SM						SM						PM											
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36						
70463-X016 SEE NOTE 8 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	PI7						PI7					
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	PI7						PI7					
	B	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	P02						P02					
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	PI7						PI7					

A

B

mat'l code				--	tolerances unless otherwise specified				CUSTOMER			 www.fciconnect.com			
ltr	ecn no.	dr	date	linear	0.X ±0.3				COPY			title MONOBLOCK HEADER ASSEMBLY PRESS-FIT, 4 ROW, 6 MOD			
H					0.XX ±0.13				projection						
					0.XXX ±.051										
				angles	0° ±2°				MM ← MM → scale 3:2			product family		METRAL	code
				dr	T.BRUNGARD	06/05/00						size		dwg no	213
				engr	M.STRAWSER	5/31/00			A		70463	sheet	6		
				chr	M.STRAWSER	06/05/00									
				appd	M.STRAWSER	06/05/00									
sheet index	revision sheet												cage code 22526		4

1 | 2

Pro/E





3 |

METRAL P/N	ROW	SM						SM						SM						SM						SM						PM					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36
70463-X017 SEE NOTE 8 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01	P01	
	C	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	P02	P02	
	B	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03	P03	
	A	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03	P03	

METRAL P/N	ROW	SM						SM						SM						SM						PM									
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34
70463-X018 SEE NOTE 8 LEAD FREE OPTION	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01	P01
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01	P01
	B	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03	P03
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	P01	P01

METRAL P/N	ROW	SM						SM						SM						SM						PM									
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34
70463-X019 SEE NOTE 8 LEAD FREE OPTION	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P17	P17
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P17	P17
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P17	P17
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P17	P17

METRAL P/N	ROW	SM						SM						SM						SM						PM									
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34
70463-X020 SEE NOTE 8 LEAD FREE OPTION	D	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	P02	P02	
	C	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	P02	P02	
	B	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	P02	P02	
	A	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	P02	P02	

mat'l code				tolerances unless otherwise specified				CUSTOMER				 www.fciconnect.com						
ltr	ecn no.	dr	date	linear	0.X ±0.3				COPY				title					
H					0.XX ±0.13				projection				MONOBLOCK HEADER ASSEMBLY PRESS-FIT, 4 ROW, 6 MOD					
					angles	0.XXX ±.051								product family				
				0° ±2°								METRAL						
				dr	T.BRUNGARD	06/05/00							size		dwg no		code	
				engr	M.STRAWSER	5/31/00			A				70463		213			
				chr	M.STRAWSER	06/05/00									sheet			
				appd	M.STRAWSER	06/05/00									7			
sheet index		revision sheet																





This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

METRAL P/N	ROW	SM						SM						SM						SM						SM						PM					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36
70463-X021 SEE NOTE 8 LEAD FREE OPTION	D	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03	P03
	C	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03	P03
	B	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03	P03
	A	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	P03	P03

METRAL P/N	ROW	SM						SM						SM						SM						PM											
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36
70463-X022 SEE NOTE 8 LEAD FREE OPTION	D	2	-	2	2	-	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P01	P01	
	C	2	-	-	-	-	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P02	P02
	B	-	-	-	-	2	-	2	2	2	2	2	2	2	2	2	2	2	2	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P03	P03	
	A	2	2	-	-	2	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P03	P03

METRAL P/N	ROW	PM						SM						SM						SM						SM						PM					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36
70463-X023 SEE NOTE 8 LEAD FREE OPTION	D	P01						2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P01	P01	
	C	P01						2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P01	P01
	B	P01						2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P01	P01
	A	P01						2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P01	P01

METRAL P/N	ROW	PM						SM						SM						SM						SM						PM					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36
70463-X024 SEE NOTE 8 LEAD FREE OPTION	D	P02						2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P02	P02	
	C	P03						2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P03	P03
	B	P01						2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P01	P01
	A	P03						2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	P03	P03

mat'l code				--				tolerances unless otherwise specified				CUSTOMER								www.fciconnect.com							
ltr	ecr no.	dr	date	linear				0.X ±0.3				COPY				title				MONOBLOCK HEADER ASSEMBLY							
H				angles				0.XX ±0.13				projection				PRESS-FIT, 4 ROW, 6 MOD											
				dr				0.XXX ±.051								product family				METRAL							
				enrg				0° ±2°				MM				code				213							
				chr				T.BRUNGARD 06/05/00				scale				size				dwg no							
				appd				M.STRAWSER 5/31/00				3:2				A				70463							
								M.STRAWSER 06/05/00												sheet							
sheet index				revision sheet																							



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

METRAL P/N	ROW	PM						SM						SM						SM						SM						PM					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36
70463-X025 SEE NOTE 8 LEAD FREE OPTION	D	P01			P01		I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	
	C	P01			P01		I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	
	B	P01			P01		I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	
	A	P01			P01		I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	I	

METRAL P/N	ROW	SM						SM						GM						SM						SM						SM									
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36				
70463-X026 SEE NOTE 8 LEAD FREE OPTION	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	-	2	2
	C	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	-	2	2
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	-	2	2
	A	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	4	4	-	19	19

METRAL P/N	ROW	GM						PM						PM						SM						SM						GM					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36
70463-X027 SEE NOTE 8 LEAD FREE OPTION	D							P01	P01	---						---						-															
	C							P01	P01	P01	P01	2	2	2	2	2	2	2	2	2	2	2	2														
	B							P01	P01	P01	P01	-	-	-	-	-	-	-	2	2	2	2	2	2													
	A							P01	P01	P01	P01	2	2	2	2	2	2	2	2	2	2	2	2	2													

A

A



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

B

B

mat'l code				--				tolerances unless otherwise specified				CUSTOMER							
ltr	ecn no.	dr	date	linear				0.X ± 0.3				COPY				www.fciconnect.com			
H				angles				0.XX ± 0.13				projection				title			
				dr				0.XXX ± .051								MONOBLOCK HEADER ASSEMBLY			
				enr				0° ± 2°				MM				PRESS-FIT, 4 ROW, 6 MOD			
				chr				T.BRUNGARD 06/05/00				product family				METRAL			
				appd				M.STRAWSER 5/31/00				size				dwg no			
				sheet				M.STRAWSER 06/05/00				scale				213			
				index				3:2				A				70463			
				revision												9			
				sheet															