
3

Crimping tool for D-SUB Contacts



- Automatic lock guarantees quality crimp
- Unlocking option in the event of a incorrect operation
- With stop for exact positioning of the contacts



Technical specifications

<u>Discription:</u> Crimping tool for D-SUB Contacts

Type: Wire size Awg 28-20

Crimp profile 1: min. AWG 28 max. AWG 24

<u>Crimp profile 2:</u> min. AWG 22 max. AWG 20

	SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
<u></u>				SCALE 1:1	MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-m			molex			
F	= 0				CURRENT REVISIO	DN					
	₽ = 0				DRWN: DRAWN BY	mteubel	07-12-2021	.			
	<u></u>				APPR: APPR BY	fvetter	10-12-2021				
	= 0	2			INITIAL REVISION			PRODUCT CUSTOMER DRAWING			
	⊘ = 0	1			DRWN: DRAWN BY	mteubel 07-12- fvetter 10-12-		MATERIAL NUMBER		REVISION	
	⊠ = 0	REV. CHNO.		NO.			10-12-2021	731120337		1	
	= 0	REPLACEMENT FOR:			THIRD ANGLE PROJECTION	DRAWING	-	DOCUMENT NUMBER	CUSTOMER	SHEET	
	▽= 0				$\bigcirc \oplus$	A4-SIZE		F1089 D	GENERAL MARKET	1 OF 1	

С

D

Е