3971D-HR



High Rejection Low-Profile Permanent Mount GPS Antenna



The 3971D-HR, low-profile permanent mount GPS antenna provides 28 dB gain and superior out-of-band rejection performance and is the optimum choice for GPS Tracking and Timing applications with high RF fields. It features a precision tuned custom ceramic patch element for maximum signal reception, 15KV ESD circuit protection, a multi-stage LNA circuit and dual high rejection SAW filters. This enables the 3971D-HR to provide a reliable and clear GPS signal while minimizing loss-of-lock, even when conditions are less than ideal. Available in an all-plastic, non-corrosive conical package for vehicle mounting or fixed installations.



3971D-HR

34" thru-hole or bracket mount*

Features

• Weather proof, all-plastic, non-corrosive, low-profile enclosure

FLECTRICAL SPECIFICATIONS - GNSS ANTENNA

- ¾ inch thru-hole or bracket mount
- High out-of-band rejection for stand-alone or mobile applications where interference is a concern and performance is critical

TNC jack

- Innovative dual SAW filter design
- Voltage range: 2.7 to 5.5 V

3971D-HR

• Low current draw: 8 mA @ 3.3 VDC

STANDARD CONFIGURATION							
Model	Connector	Mount					

ELECTRICAL OF LOW FORTHOR	to altoo Alti ElittiA		
Frequency Range	LNA Gain	Element Gain	Polarization
1575.42 ± 10 MHz	28 dB	3 dBic @ 90° -2 dBic @ 20°	Right hand circular

ELECTRICAL SPECIFICATION	AL SPECIFICATIONS - GNSS ANTENNA, continued				
Out of Band Rejection	Current Draw	DC Voltage	Noise Figure		
> 50 dBc @ ± 40 MHz	8 mA @ 3.3 VDC	2.7-5.5 VDC	3.1 dB (typical)		

MECHANICAL & ENVIRONMENTAL SPECIFICATIONS								
Dimensions	Weight	Housing Material	Temperature Range	ESD Circuit Protection	Ingress Protection			
2.36" Dia x .83" H (60 x 21 mm)	0.11 lbs (50 g)	PC	-40°C to +85°C operating	15 KV	IP67**			

^{*} Order MMK1925 bracket for compatible mounting.