

AO6401

30V P-Channel MOSFET


General Description


The AO6401 uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as 2.5V. This device is suitable for use as a load switch or in PWM applications.


Product Summary


 $\begin{array}{lll} V_{DS} & -30V \\ I_{D} \; (at \; V_{GS} \!\!=\! \!\! -10V) & -5A \\ R_{DS(ON)} \; (at \; V_{GS} \!\!=\! \!\! -10V) & < 47m\Omega \\ R_{DS(ON)} \; (at \; V_{GS} \!\!=\! \!\! -4.5V) & < 64m\Omega \\ R_{DS(ON)} \; (at \; V_{GS} \!\!=\! \!\!\! -2.5V) & < 85m\Omega \end{array}$











Absolute Maximum Ratings T_A=25℃ unless otherwise noted

, 10001010 1110711110111	A TO CHILD HOLD THE CONTROL OF THE C						
Parameter		Symbol	Maximum	Units			
Drain-Source Voltage)	V _{DS}	-30	V			
Gate-Source Voltage		V _{GS}	±12	V			
Continuous Drain	T _A =25℃		-5				
Current	T _A =70℃	'D	-4	A			
Pulsed Drain Current	Ċ	I _{DM}	-28				
	T _A =25℃	В	2	W			
Power Dissipation ^B	T _A =70℃	P _D	1.3	VV			
Junction and Storage	Temperature Range	T _J , T _{STG}	-55 to 150	C			

Thermal Characteristics						
Parameter	Symbol	Тур	Max	Units		
Maximum Junction-to-Ambient A	t ≤ 10s	D	47.5	62.5	€/W	
Maximum Junction-to-Ambient AD	Steady-State	$R_{\theta JA}$	74	110	€/W	
Maximum Junction-to-Lead	Steady-State	$R_{\theta JL}$	37	50	€\M	



Electrical Characteristics (T_J=25℃ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Тур	Max	Units
STATIC F	PARAMETERS					
BV _{DSS}	Drain-Source Breakdown Voltage	I _D =-250μA, V _{GS} =0V	-30			V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =-30V, V _{GS} =0V			-1	μΑ
l	Gate-Body leakage current	$V_{DS}=0V, V_{GS}=\pm 12V$			-5 ±100	nA
I _{GSS}	Gate Threshold Voltage	$V_{DS} = V_{GS} I_{D} = -250 \mu A$	-0.5	-0.9	-1.3	V
V _{GS(th)}	On state drain current	$V_{DS} = V_{GS} I_D = 250\mu A$ $V_{GS} = -10V, V_{DS} = -5V$	-0.5	-0.9	-1.3	A
I _{D(ON)}	On state drain current		-20	20	47	А
		V_{GS} =-10V, I_{D} =-5A T_{J} =125°C		39 60	47 74	mΩ
R _{DS(ON)}	Static Drain-Source On-Resistance	V_{GS} =-4.5V, I_{D} =-4A		45	64	mΩ
		V_{GS} =-2.5V, I_{D} =-1A		59	85	mΩ
g _{FS}	Forward Transconductance	V_{DS} =-5V, I_{D} =-5A		18		S
V _{SD}	Diode Forward Voltage	I _S =-1A,V _{GS} =0V		-0.7	-1	V
I _S	Maximum Body-Diode Continuous Cui				-2.5	Α
	PARAMETERS					
C _{iss}	Input Capacitance			645	780	pF
C _{oss}	Output Capacitance	V _{GS} =0V, V _{DS} =-15V, f=1MHz		80		pF
C _{rss}	Reverse Transfer Capacitance	7		55	80	pF
R_g	Gate resistance	V _{GS} =0V, V _{DS} =0V, f=1MHz	4	7.8	12	Ω
SWITCHI	NG PARAMETERS					
Q _g (10V)	Total Gate Charge			14	17	nC
Q _g (4.5V)	Total Gate Charge	V _{GS} =-10V, V _{DS} =-15V, I _D =-5A		7	8.5	nC
Q_{gs}	Gate Source Charge	V _{GS} =-10V, V _{DS} =-13V, I _D =-3A		1.5		nC
Q_{gd}	Gate Drain Charge	7		2.5		nC
t _{D(on)}	Turn-On DelayTime			6.5		ns
t _r	Turn-On Rise Time	V_{GS} =-10V, V_{DS} =-15V, R_L =3 Ω ,		3.5		ns
t _{D(off)}	Turn-Off DelayTime	$R_{GEN}=3\Omega$		41		ns
t _f	Turn-Off Fall Time	7		9		ns
t _{rr}	Body Diode Reverse Recovery Time	I _F =-5A, dI/dt=100A/μs		11	13.5	ns
Q_{rr}	Body Diode Reverse Recovery Charge	e I _F =-5A, dl/dt=100A/μs		3.5		nC

A. The value of $R_{\theta JA}$ is measured with the device mounted on 1in² FR-4 board with 2oz. Copper, in a still air environment with T_A =25° C. The value in any given application depends on the user's specific board design.

B. The power dissipation P_D is based on P_D is based on the user's specific board design.

C. Repetitive rating, pulse width limited by junction temperature P_D is based on low frequency and duty cycles to keep

THIS PRODUCT HAS BEEN DESIGNED AND QUALIFIED FOR THE CONSUMER MARKET. APPLICATIONS OR USES AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS ARE NOT AUTHORIZED. AOS DOES NOT ASSUME ANY LIABILITY ARISING OUT OF SUCH APPLICATIONS OR USES OF ITS PRODUCTS. AOS RESERVES THE RIGHT TO IMPROVE PRODUCT DESIGN, FUNCTIONS AND RELIABILITY WITHOUT NOTICE.

initial $T_J = 25^{\circ}$ C.


D. The $R_{\theta JA}$ is the sum of the thermal impedence from junction to lead $R_{\theta JL}$ and lead to ambient.

E. The static characteristics in Figures 1 to 6 are obtained using <300µs pulses, duty cycle 0.5% max.

F. These curves are based on the junction-to-ambient thermal impedence which is measured with the device mounted on 1in^2 FR-4 board with 2oz. Copper, assuming a maximum junction temperature of $T_{J(MAX)}=150^\circ$ C. The SOA curve provides a single pulse rating.




TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS





TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS



Operating Area (Note F)

Figure 10: Single Pulse Power Rating Junction-to-Ambient (Note F)






Figure 11: Normalized Maximum Transient Thermal Impedance (Note F)





Gate Charge Test Circuit & Waveform







Resistive Switching Test Circuit & Waveforms







Unclamped Inductive Switching (UIS) Test Circuit & Waveforms





Diode Recovery Test Circuit & Waveforms








Document No.	PD-00119
Version	Е
Title	AO6401 Marking Description

TSOP-6 PACKAGE MARKING DESCRIPTION



Green product

NOTE:

P - Package and product type

N - Last digital of product number

W - Year and week code

A - Assembly location code


L&T - Assembly lot code

PART NO.	DESCRIPTION	CODE (PN)
AO6401	Green product	D1
AO6401L	Green product	D1




Document No.	PO-00002
Version	rev H

TSOP6 PACKAGE OUTLINE



RECOMMENDED LAND PATTERN



UN	IT:	mm


	DIMENS	SIONS IN MILLI	METERS	DIM	DIMENSIONS IN INCHES		
SYMBOLS	MIN	NOM	MAX	MIN	NOM	MAX	
A	0.80		1.25	0.031		0.049	
A1	0.00		0.15	0.000		0.006	
A2	0.70	1.10	1.20	0.028	0.043	0.047	
b	0.30	0.40	0.50	0.012	0.016	0.020	
С	0.08	0.13	0.20	0.003	0.005	0.008	
D	2.70	2.90	3.10	0.106	0.114	0.122	
Е	2.50	2.80	3.10	0.098	0.110	0.122	
E1	1.50	1.60	1.70	0.059	0.063	0.067	
e		0.95 BSC.		0.037BSC.			
el	1.90 BSC.				0.075 BSC.		
L	0.30		0.60	0.012		0.024	
θ1	0°		8°	0°		8°	

NOTE

- 1. PACKAGE BODY SIZES EXCLUDE MOLD FLASH AND GATE BURRS. MOLD FLASH AT THE NON-LEAD SIDES SHOULD BE LESS THAN 5 MILS EACH.
- 2. DIMENSION "L" IS MEASURED IN GAUGE PLANE.
- 3. TOLERANCE ± 0.100 mm(4 mil) UNLESS OTHERWISE SPECIFIED.
- 4. FOLLOWED FROM JEDEC MÓ-178C & MO-193C.
- 5. CONTROLLING DIMENSIONS IS MILLIMETER. CONVERTED INCH DIMENSIONS ARE NOT NECESSARILY EXACT.





TSOP-6 Tape and Reel Data



UNIT: MM

PACKAGE	A0	В0	K0	D0	D1	E	E1	E5	P0	P1	P2	Т
SDT-23	3.15	3.27	1.34	1.10	1.50	8.00	1.75	3.50	4.00	4.00	2.00	0.25
(8 mm)	±0.10	±0.10	±0.10	±0.01	+0.10	±0.20	±0.10	±0.05	±0.10	±0.10	±0.10	±0.05







AOS Semiconductor Product Reliability Report

AO6401/AO6401L, rev B

Plastic Encapsulated Device

ALPHA & OMEGA Semiconductor, Inc

495 Mercury Drive Sunnyvale, CA 94085 U.S.

Tel: (408) 830-9742 <u>www.aosmd.com</u>

Aug 4, 2006



This AOS product reliability report summarizes the qualification result for AO6401. Accelerated environmental tests are performed on a specific sample size, and then followed by electrical test at end point. Review of final electrical test result confirms that AO6401 passes AOS quality and reliability requirements. The released product will be categorized by the process family and be monitored on a quarterly basis for continuously improving the product quality.

Table of Contents:

- I. Product Description
- II. Package and Die information
- III. Environmental Stress Test Summary and Result
- IV. Reliability Evaluation
- V. Quality Assurance Information

I. Product Description:

The AO6401 uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as 2.5V. This device is suitable for use as a load switch or in PWM applications. Standard Product AO6401 is Pb-free (meets ROHS & Sony 259 specifications). AO6401L is a Green Product ordering option. AO6401 and AO6401L are electrically identical.

Absolute Maximum Ratings T _A =25°C unless otherwise noted						
Parameter	Parameter		Symbol M		Maximum	Units
Drain-Source Voltage		V _{DS}	-30	V		
Gate-Source Voltage		V_{GS}	±12	V		
Continuous Drain	T _A =25°C		-5			
Current	T _A =70°C	I _D	-4.2	Α		
Pulsed Drain Current	Pulsed Drain Current		-30			
	T _A =25°C	P _D	2	l w		
Power Dissipation	T _A =70°C	L D	1.44	VV		
Junction and Storage Temperature						
Range		T_{J}, T_{STG}	-55 to 150	°C		

Thermal Characteristics								
Parameter		Symbol	Тур	Max	Units			
Maximum Junction-to- Ambient	T ≤ 10s	В	47.5	62.5	°C/W			
Maximum Junction-to- Ambient	Steady- State	$R_{ hetaJA}$	74	110	°C/W			
Maximum Junction-to-Lead	Steady- State	$R_{ hetaJL}$	37	50	°C/W			



II. Die / Package Information:

Package Type

AO6401 AO6401L (Green Compound)

Process Standard sub-micron Standard sub-micron

low voltage P channel process low voltage P channel process

6 leads TSOP 6 leads TSOP

Lead Frame Copper with Ag spot Copper with Ag spot

Die AttachAg epoxyAg epoxyBond wireAu 2milsAu 2mils

Mold Material Epoxy resin with silica filler Epoxy resin with silica filler

Filler % (Spherical/Flake)90/10100/0Flammability RatingUL-94 V-0UL-94 V-0Backside MetallizationTi / Ni / AgTi / Ni / AgMoisture LevelUp to Level 1 *Up to Level 1*

Note * based on info provided by assembler and mold compound supplier

III. Result of Reliability Stress for AO6401 (Standard) & AO6401L (Green)

Test Item	Test Condition	Time Point	Lot Attribution	Total Sample size	Number of Failures
Solder Reflow Precondition	Standard: 1hr PCT+3 cycle reflow@260°c Green: 168hr 85°c /85%RH +3 cycle reflow@260°c	0hr	Standard: 16 lots Green: 7 lots	3575pcs	0
НТСВ	Temp = 150°c , Vgs=100% of Vgsmax	168 / 500 hrs 1000 hrs	5 lots (Note A*)	410pcs 77+5 pcs / lot	0
HTRB	Temp = 150°c , Vds=80% of Vdsmax	168 / 500 hrs 1000 hrs	5 lots (Note A*)	410pcs 77+5 pcs / lot	0
HAST	130 +/- 2°c , 85%RH, 33.3 psi, Vgs = 80% of Vgs max	100 hrs	Standard: 16 lots Green: 6 lots (Note B**)	1210pcs 50+5 pcs / lot	0
Pressure Pot	121°c , 29.7 psi, 100%RH	96 hrs	Standard: 14 lots Green: 7 lots (Note B**)	1155pcs 50+5 pcs / lot	0
Temperature Cycle	-65 to 150°c , air to air	250 / 500 cycles	Standard: 15 lots Green: 7 lots (Note B**)	1210pcs 50+5 pcs / lot	0



III. Result of Reliability Stress for AO6401 (Standard) & AO6401L (Green) Continues

Continuos	1				•
DPA	Internal Vision	NA	5	5	0
	Cross-section		5	5	
	X-ray		5	5	
CSAM		NA	5	5	0
Bond Integrity	Room Temp 150°c bake	0hr 250hr	40 40	40 wires 40 wires	0
	150°c bake	500hr	40	40 wires	
Solderability	230°c	5 sec	15	15 leads	0
Die shear	150°c	0hr	10	10	0

Note A: The HTGB and HTRB reliability data presents total of available AO6401 and AO6401L burn-in data up to the published date.

Note B: The pressure pot, temperature cycle and HAST reliability data for AO6401 and AO6401L comes from the AOS generic package qualification data.

IV. Reliability Evaluation

FIT rate (per billion): 9.3 MTTF = 12274 years

In general, 500 hrs of HTGB, 150 deg C accelerated stress testing is equivalent to 15 years of lifetime at 55 deg C operating conditions (by applying the Arrhenius equation with an activation energy of 0.7eV and 60% of upper confidence level on the failure rate calculation). AOS reliability group also routinely monitors the product reliability up to 1000 hr at and performs the necessary failure analysis on the units failed for reliability test(s).

The presentation of FIT rate for the individual product reliability is restricted by the actual burn-in sample size of the selected product (AO6401). Failure Rate Determination is based on JEDEC Standard JESD 85. FIT means one failure per billion hours.

Failure Rate =
$$\text{Chi}^2 \times 10^9 \text{/} 2[(\text{N}) \text{ (H) (Af)}]$$

= $1.83 \times 10^9 \text{/} 2[(2 \times 164) (168) (258) + (2 \times 164) (500) (258) + (164) (1000) (258)]$
= 9.3
MTTF = $10^9 \text{/ FIT} = 1.07 \times 10^8 \text{hrs} = 12274 \text{ years}$

Chi² = Chi Squared Distribution, determined by the number of failures and confidence interval **N** = Total Number of units from HTRB and HTGB tests

H = Duration of HTRB/HTGB testing

Af = Acceleration Factor from Test to Use Conditions (Ea = 0.7eV and Tuse = 55°C)

Acceleration Factor [Af] = Exp [Ea/k (1/Tj u - 1/Tj s)]

Acceleration Factor ratio list:

	55 deg C	70 deg C	85 deg C	100 deg C	115 deg C	130 deg C	150 deg C
Af	258	87	32	13	5.64	2.59	1

Tj s = Stressed junction temperature in degree (Kelvin), K = C+273.16

Tj u =The use junction temperature in degree (Kelvin), K = C+273.16

 \mathbf{k} = Boltzmann's constant, 8.617164 X 10⁻⁵eV / K



V. Quality Assurance Information

Acceptable Quality Level for outgoing inspection: **0.1%** for electrical and visual. Guaranteed Outgoing Defect Rate: **< 25 ppm** Quality Sample Plan: conform to **Mil-Std-105D**