

Designated client product

This product will be discontinued its production in the near term.

And it is provided for customers currently in use only, with a time limit.

It can not be available for your new project. Please select other new or existing products.

For more information, please contact our sales office in your region.

New Japan Radio Co.,Ltd.

www.njr.com

NJM4741M



GENERAL PURPOSE QUAD OPERATIONAL AMPLIFIER

■ GENERAL DESCRIPTION


The NJM4741 consists of four independent high-gain operational amplifiers that are designed for high slew rate, wide band, and good noise characteristics.

■ FEATURES

 Operating Voltage 	(±4V~±20V)
Wide Band	(3.5MHz typ.)
Slew Rate	(1.6V/µs typ.)
 Low Input Noise Voltage 	(9nV/√Hz typ.)
 Low Distortion 	(0.0005% typ.)
 Package Outline 	DIP14,DMP14

■ PIN CONFIGURATION

Bipolar Technology




NJM4741M

1.A OUTPUT
2.A –INPUT
3.A +INPUT
4.V[†]
5.B +INPUT
6.B –INPUT
7.B OUTPUT
8.C OUTPUT
9.C –INPUT
10.C +INPUT
11. V
12.D +INPUT
14.D OUTPUT


PIN FUNCTION

■ PACKAGE OUTLINE



NJM4741D

■ EQUIVALENT CIRCUIT (1/4 Shown)



■ ABSOLUTE MAXIMUM RATINGS

(Ta=25°C)

PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	V ⁺ √	± 20	V
Differential Input Voltage	V _{ID}	± 30	V
Input Voltage	V _{IC}	± 15 (note)	V
Power Dissipation	P _D	(DIP14) 500 (DMP14) 300	mW
Operating Temperature Range	Topr	-40~+85	°C
Storage Temperature Range	T _{stg}	-40~+125	°C

(note) When the supply voltage is less than ± 15 V, the absolute maximum input voltage is equal to the supply voltage.

■ ELECTRICAL CHARACTERISTICS


 $(Ta=25^{\circ}C,V^{\dagger}/V=\pm 15V)$

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Input Offset Voltage	V _{IO}	R _S ≤100Ω	-	1.0	5.0	mV
Input Offset Current	I _{IO}		-	5	50	nA
Input Bias Current	I_{B}		-	60	300	nA
Large Signal Voltage Gain	Av	R _L ≥2kΩ,V _O =±10V	88	110	-	dB
Operating Current	Icc		-	5	7	mA
Common Mode Rejection Ratio	CMR		80	120	-	dB
Supply Voltage Rejection Ratio	SVR		80	120	-	dB
Maximum Output Voltage 1	V_{OM1}	R _L ≥10kΩ	± 12	± 13.7	-	V
Maximum Output Voltage 2	V_{OM2}	R _L ≥2kΩ	± 10	± 12.5	-	V
Input Common Mode Voltage Range	V _{ICM}		± 12	± 14	-	V
Slew Rate	SR	A _v =1	-	1.6	-	V/µs
Equivalent Input Noise Voltage	e _n	f=1kHz	-	9	-	nV/√Hz
Channel Separation	CS	f=10kHz,Input Referred	-	108	-	dB


⁽ note) The application that leads to the extreme difference of power dissipation between channels may cause the mutual interference by the temperature gradient on the chip.

■ TYPICAL CHARACTERISTICS


Voltage Gain, Phase vs. Frequency




Voltage Gain vs. Frequency




Maximum Output Voltage Swing vs. Frequency




Maximum Output Voltage Swing vs. Load Resistance



Equivalent Input Noise Voltage vs. Frequency




Pulse Response




■ TYPICAL CHARACTERISTICS


Maximum Outout Voltage Swing vs. Temperature




Input Offset Voltage vs. Temperature




Input Bias Current vs. Temperature




Operating Current vs. Operating Voltage



Maximum Output Voltage Swing vs. Operating Voltage




Slew Rate, Unity Gain Bandwidth vs. Operating Voltage



■ TYPICAL CHARACTERISTICS

Operating Current vs. Temperature



[CAUTION]
The specifications on this databook are only given for information, without any guarantee as regards either mistakes or omissions. The application circuits in this databook are described only to show representative usages of the product and not intended for the guarantee or permission of any right including the industrial rights.