FlexiForce[™] Standard Model ESS102

The ESS102 is a standard force sensor ideal for conditions with high temperature and humidity. This sensor is made from Tekscan's Enhanced Stability Series (ESS) pressure sensitive ink. This allows better performance in a wider range of operating and storage conditions. The ESS102 can be used with our test & measurement, prototyping, and embedding electronics, including the FlexiForce Sensor Characterization Kit, FlexiForce Prototyping Kit, FlexiForce Quickstart Board, and the ELF™ System*. You can also use your own electronics, or multimeter.

Thickness 0.203 mm (0.008 in.)

THICKNESS	0.203 11111 (0.000 11.)
Length	38.1 mm (1.5 in.)**
Width	7.6 mm (0.30 in.)
Sensing Area	3.8 mm (0.15 in.) diameter
Connector	2-pin Male Square Pin
Substrate	Polyester
Pin Spacing	2.54 mm (0.1 in.)

Benefits

6 mm (.25 in.

Actual size of sensor

7.6 mm

(.30 in.)

ESS102

38.1 mm (1.5 in.)

Sensing

Area

- Operates in temperatures up to 85°C approximately 185°F) and with a relative humidity up to 95%
- Thin and flexible
- Easy to use, ideal for prototyping and integrating
- Available off-the-shelf



* Sensor will require an adapter/extender to connect to the ELF System. Contact your Tekscan representative for assistance.

**Length does not include pins. Please add approximately 6 mm (0.25 in.) for pin length for a total length of approximately 32 mm (1.25 in).

	Typical Performance	Evaluation Conditions
Linearity (Error)	$< \pm 8.6\%$ of full scale	Line drawn from 0 to 50% load
Repeatability	< ±2.5%	Conditioned sensor, 80% of full force applied
Hysteresis	< 5.5% of full scale	Conditioned sensor, 80% of full force applied
Drift	< 3.8% per logarithmic time scale	Constant load of 111 N (25 lb)
Response Time	< 5µsec	Impact load, output recorded on oscilloscope
Operating Temperature	-40°C - 85°C (-40°F - 185°F)	Convection and conduction heat sources
Durability	\geq 3 million actuations	Perpendicular load, room temperature, 22 N (5 lb)
Temperature Sensitivity	0.36%/°C (± 0.2%/°F)	Conductive heating

***All data above was collected utilizing an Op Amp Circuit (shown on the next page). If your application cannot allow an Op Amp Circuit, visit www.tekscan.com/flexiforce-integration-guides, or contact a FlexiForce Applications Engineer.




Standard Force Ranges as Tested with Circuit Shown

[†]**This sensor can measure up to 44 N (10 lb).** The force range can be extended by reducing the drive voltage, V_{τ} , or the resistance value of the feedback resistor, R_{F} . Conversely, the sensitivity can be increased for measurement of lower forces by increasing V_{τ} or R_{F} .

4.4 N (0 - 1 lb) ⁺

Sensor output is a function of many variables, including interface materials. Therefore, Tekscan recommends the user calibrate each sensor for the application. The graph on the right is an illustration of how a sensor can be used to measure varying force ranges by changing the feedback resistor (**Figure 1** should not be used as a calibration chart).

Test Conditions: Input Voltage- 0.45V; Load Applied - 1lb; Measured Current- 79uA



Recommended Circuit

PURCHASE TODAY ONLINE AT WWW.TEKSCAN.COM/STORE



©Tekscan Inc., 2021. All rights reserved. Tekscan, the Tekscan logo, and FlexiForce are trademarks or registered trademarks of Tekscan, Inc.