

Multilayer Band Pass Filter
For LTE

DEA Series 2.0x1.25mm [EIA 0805] TYPE


P/N: **DEA203550BT-2224A4-H**




DEA203550BT-2224A4-H

SHAPES AND DIMENSIONS

[Top View]



[Bottom View]



Dimensions (mm)

| L | W T a b | | | | С | d | |
|---------|---------|------|---------|---------|---------|---------|--|
| 2.00 | 1.25 | 0.65 | 0.275 | 0.25 | 0.60 | 0.95 | |
| +/-0.15 | +/-0.10 | Max | +/-0.10 | +/-0.10 | +/-0.10 | +/-0.15 | |

Terminal functions

| (1) | Input Port | | | | |
|-----|------------|--|--|--|--|
| (2) | GND | | | | |
| (3) | GND | | | | |

| (4) | Output Port |
|-----|-------------|
| (5) | GND |
| (6) | GND |

TERMINATION FINISH

| Material |
|----------|
| Ag |



DEA203550BT-2224A4-H

ELECTRICAL CHARACTERISTICS

(Measurement)

| Parameter | Eroguo | nev | /MU-/ | TI | DK Spec | | |
|--------------------------------|-----------|-----|----------|------|---------|------|--|
| Farameter | Frequency | | (IVITIZ) | Min. | Тур. | Max. | |
| Insertion Loss (dB) | 3300 | to | 3400 | - | 1.04 | 1.25 | |
| | 3400 | to | 3800 | • | 0.94 | 1.15 | |
| Insertion Loss (dB) | 3300 | to | 3400 | - | - | 1.45 | |
| (-40 to +90 °C) | 3400 | to | 3800 | • | - | 1.25 | |
| Return Loss (dB) | 3300 | to | 3400 | 10 | 22.3 | - | |
| | 3400 | to | 3800 | 10 | 21.9 | - | |
| Attenuation (dB) | 500 | to | 2170 | 40 | 44.1 | - | |
| (-40 to +90 °C) | 880 | to | 960 | 40 | 45.9 | - | |
| | 1710 | to | 1785 | 40 | 44.1 | - | |
| | 2300 | to | 2700 | 32 | 34.9 | - | |
| | | | 2800 | 7 | 42.7 | - | |
| | 2700 | to | 3150 | - | 1.5 | - | |
| | 4100 | to | 4300 | - | 4.1 | - | |
| | | | 4400 | 7 | 17.3 | - | |
| | 4800 | to | 4900 | 25 | 35.6 | - | |
| | 4900 | to | 5150 | 30 | 42.0 | - | |
| | 5150 | to | 5850 | 35 | 41.5 | - | |
| | 6250 | to | 6550 | 35 | 42.8 | - | |
| | 6800 | to | 7200 | 35 | 46.4 | _ | |
| | 7200 | to | 9000 | 35 | 50.0 | _ | |
| | 10200 | to | 10800 | 35 | 45.0 | - | |
| Characteristic Impedance (ohm) | | | | 50 | (Nomi | nal) | |

Ta = +25+/-5°C

MAXIMUM RATINGS

| Parameter | | TDK S | Spec | Conditions | | |
|----------------------------|----------------|----------|--------|-------------------------------|--|--|
| Farameter | | Min. | Max. | Conditions | | |
| Operating temperature (°C) | | –40 to - | +90 °C | | | |
| Storage temperature (°C) | | –40 to | +90 °C | | | |
| Power Handling (W) *1 | | - | 2 | CW | | |
| Human Body Model : HBM | @Each Port (V) | -1000 | 1000 | 100pF / 1500ohm | | |
| Machine Model : MM | @Each Port (V) | -150 150 | | 200pF / 0ohm | | |
| Charged Device Model : CDM | @Each Port (V) | -500 | 500 | Relative humidity : 60%RH max | | |


*1 : Refer to 3GPP TS 38.101-1 V15.2.0



DEA203550BT-2224A4-H

FREQUENCY CHARACTERISTICS









DEA203550BT-2224A4-H

FREQUENCY CHARACTERISTICS








DEA203550BT-2224A4-H

RECOMMENDED LAND PATTERN



Unit: mm


ENVIRONMENT INFORMATION

RoHS Statement
RoHS Compliance



DEA203550BT-2224A4-H

RECOMMENDED REFLOW PROFILE



Soldering **Preheating** Critical zone (T3 to T4) Peak Temp. Temp. **Time Time** Temp. **Time T3 T4 t1 t2** t3 * 150°C 200°C 60 to 120sec 217°C 60 to 120sec 240 to 260°C 30 sec Max

* t3 : Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

Note: Lead free solder is recommended.

Recommended solder is Sn-3.0Ag-0.5Cu. (M705 by Senju Metal Industry)

■ GENERAL TECHNICAL INFORMATION


https://product.tdk.com/en/system/files?file=dam/doc/product/rf/rf/diplexer/general tech info/rf general-technical-info 02 en.pdf




DEA203550BT-2224A4-H

PACKAGING STYLE

Reel Dimensions







Dimensions (mm)

| Α | В | С | D | E | F | G | Н | J | K | t |
|---------|---------|-----------|---------|--------|--------|---------|--------|---------|-----|---------|
| 1.45 | 2.2 | 8.0 | 3.5 | 1.75 | 4.0 | 2.0 | 4.0 | 1.5 | 0.8 | 0.25 |
| +/-0.05 | +/-0.05 | +0.3/-0.1 | +/-0.05 | +/-0.1 | +/-0.1 | +/-0.05 | +/-0.1 | +0.1/-0 | MAX | +/-0.05 |

STANDARD PACKAGE QUANTITY (pieces/reel) 2,000



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

⚠ REMINDERS

The products listed on this specification sheet are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property. Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this specification sheet.

- 1. Aerospace/Aviation equipment
- 2. Transportation equipment (cars, electric trains, ships, etc.)
- 3. Medical equipment
- 4. Power-generation control equipment
- 5. Atomic energy-related equipment
- 6. Seabed equipment
- 7. Transportation control equipment
- 8. Public information-processing equipment
- 9. Military equipment
- 10. Electric heating apparatus, burning equipment
- 11. Disaster prevention/crime prevention equipment
- 12. Safety equipment
- 13. Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/equipment or providing backup circuits, etc., to ensure higher safety.