



DGD2103

HALF-BRIDGE GATE DRIVER IN SO-8

Description

The DGD2103 is a high-voltage, high-speed gate driver capable of driving N-channel MOSFETs and IGBTs in a half-bridge configuration. High-voltage processing techniques enable the DGD2103's high side to switch to 600V in a bootstrap operation.

The DGD2103 logic inputs are compatible with standard TTL and CMOS levels (down to 3.3V) to interface easily with controlling devices. The driver output features high pulse current buffers designed for minimum driver cross conduction. DGD2103 has a fixed internal deadtime of 520ns (typical).

The DGD2103 is offered in the SO-8 (Type TH) package and operates over an extended -40°C to +125°C temperature range.

Applications


- **DC-DC** Converters
- **DC-AC Inverters**
- **AC-DC Power Supplies**
- Motor Controls
- **Class D Power Amplifiers**

Features

- Floating High-Side Driver in Bootstrap Operation to 600V
- Drives Two N-Channel MOSFETs or IGBTs in a Half-Bridge Configuration
- 290mA Source / 600mA Sink Output Current Capability
- **Outputs Tolerant to Negative Transients**
- Internal Dead Time of 520ns to Protect MOSFETs
- Wide Low Side Gate Driver Supply Voltage: 10V to 20V
- Logic Input (HIN and LIN*) 3.3V Capability
- Schmitt Triggered Logic Inputs
- Undervoltage Lockout for V_{CC} (Logic and Low Side Supply)
- Extended Temperature Range: -40°C to +125°C
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)

Mechanical Data

- Case: SO-8 (Type TH)
- Case Material: Molded Plastic. "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads.
- Solderable per MIL-STD-202, Method 208 @3
- Weight: 0.075 grams (Approximate)



Ordering Information (Note 4)

Product	Marking	Reel Size (inches)	Tape Width (mm)	Quantity per Reel
DGD2103S8-13	DGD2103	13	12	2,500

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. Notes:

See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

Marking Information




= Manufacturer's marking DGD2103 = Product Type Marking Code YΥ = Year (ex: 16 = 2016) ww

= Week (01 to 53)



Pin Diagrams




Top View: SO-8 (Type TH)

Pin Descriptions

Pin Number	Pin Name	Function
1	Vcc	Logic and Low Side Supply
2	HIN	Logic Input for High-Side Gate Driver Output in Phase with HO
3	LIN*	Logic input for Low-Side Gate Driver Output out of Phase with LO
4	COM	Low-Side and Logic Return
5	LO	Low-Side Gate Drive Output
6	Vs	High-Side Floating Supply Return
7	HÔ	High-Side Gate Drive Output
8	VB	High-Side Floating Supply

Functional Block Diagram





DGD2103

Absolute Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
High-Side Floating Supply Voltage	VB	-0.3 to +624	V	
High-Side Floating Supply Offset Voltage	Vs	V _B -24 to V _B +0.3	V	
High-Side Floating Output Voltage	V _{HO}	V _S -0.3 to V _B +0.3	V	
Offset Supply Voltage Transient	dV _S / dt	50	V/ns	
Low-Side Fixed Supply Voltage	V _{CC}	-0.3 to +24	V	
Low-Side Output Voltage	V _{LO}	-0.3 to V _{CC} +0.3	V	
Logic Input Voltage (HIN and LIN*)	V _{IN}	-0.3 to V _{CC} +0.3	V	

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power Dissipation Linear Derating Factor (Note 5)	PD	0.625	W
Thermal Resistance, Junction to Ambient (Note 5)	R _{0JA}	200	°C/W
Operating Temperature	TJ	+150	
Lead Temperature (Soldering, 10s)	TL	+300	°C
Storage Temperature Range	T _{STG}	-55 to +150	

Note: 5. When mounted on a standard JEDEC 2-layer FR-4 board.

Recommended Operating Conditions

Parameter	Symbol	Min	Мах	Unit
High-Side Floating Supply Absolute Voltage	VB	Vs + 10	V _S + 20	V
High-Side Floating Supply Offset Voltage	Vs	(Note 6)	600	V
High-Side Floating Output Voltage	V _{но}	Vs	VB	V
Low-Side Supply Voltage	Vcc	10	20	V
Low-Side Output Voltage	VLO	0	V _{CC}	V
Logic Input Voltage (HIN & LIN*)	V _{IN}	0	5	V
Ambient Temperature	TA	-40	+125	O°

Note: 6. Logic operation for V_S of -5V to +600V. Logic state held for V_S of -5V to -V_{BS}.





DGD2103

DC Electrical Characteristics (V_{BIAS} (V_{CC} , V_{BS}) = 15V, $@T_A$ = +25°C, unless otherwise specified.) (Note 7)

Parameter	Symbol	Min	Тур	Max	Unit	Condition
Logic "1" (HIN) & Logic "0" (LIN*) Input Voltage	VIH	2.5	-	-	V	$V_{CC} = 10V$ to 20V
Logic "0" (HIN) & Logic "1" (LIN*) Input Voltage	V _{IL}	-	-	0.8	V	$V_{CC} = 10V \text{ to } 20V$
High Level Output Voltage, V _{BIAS} - V _O	Vон	-	0.05	0.2	V	$I_0 = 2mA$
Low Level Output Voltage, V _O	V _{OL}	-	0.02	0.1	V	$I_0 = 2mA$
Offset Supply Leakage Current	I _{LK}	-	-	50	μA	$V_{B} = V_{S} = 600V$
Quiescent V _{BS} Supply Current	I _{BSQ}	-	60	100	μA	$V_{IN} = 0V \text{ or } 5V$
Quiescent V _{CC} Supply Current	ICCQ	-	350	500	μA	$V_{IN} = 0V \text{ or } 5V$
Logic "1" Input Bias Current	I _{IN+}	-	3	10	μA	$HIN = 5V, LIN^* = 0V$
Logic "0" Input Bias Current	I _{IN-}	-	-	5	μA	$HIN = 0V, LIN^* = 5V$
V _{CC} Supply Undervoltage Positive Going Threshold	V _{CCUV+}	8.0	8.9	9.8	V	-
V _{CC} Supply Undervoltage Negative Going Threshold	Vccuv-	7.4	8.2	9.0	V	-
Output High Short Circuit Pulsed Current	I _{O+}	130	290		mA	V _O = 0V, PW ≤ 10µs
Output Low Short Circuit Pulsed Current	I ₀₋	270	600	-	mA	V _O = 15V, PW ≤ 10µs

Note: 7. The V_{IN} and I_{IN} parameters are applicable to the two logic pins: HIN and LIN*. The V_O and I_O parameters are applicable to the respective output pins: HO and LO.

AC Electrical Characteristics (V_{BIAS} (V_{CC}, V_{BS}) = 15V, C_L = 1000pF, @T_A = +25°C, unless otherwise specified.)


Parameter	Symbol	Min	Тур	Max	Unit	Condition
Turn-On Propagation Delay	ton		680	820	ns	$V_S = 0V$
Turn-Off Propagation Delay	toff	-	150	220	ns	$V_{\rm S} = 600 V$
Delay Matching, HO & LO Turn-On/Turn-Off	t _{DM}	-		60	ns	-
Turn-On Rise Time	t _R	-	70	170	ns	$V_{\rm S} = 0V$
Turn-Off Fall Time	tF	-	35	90	ns	$V_{\rm S} = 0V$
Deadtime: tpt LO-HO & tpt HO-LO	tрт	400	520	650	ns	-





DGD2103

Timing Waveforms





Typical Performance Characteristics (@T_A = +25°C, unless otherwise specified.)




Figure 4. Turn-on Propagation Delay vs. Supply Voltage





Figure 6. Turn-off Propagation Delay vs. Supply Voltage






Figure 5. Turn-on Propagation Delay vs. Temperature




Figure 7. Turn-off Propagation Delay vs. Temperature





Figure 9. Rise Time vs. Temperature




Typical Performance Characteristics (Cont.)





800

Typical Performance Characteristics (Cont.)






Figure 16. Output Source Current vs. Supply Voltage




Figure 18. Output Sink Current vs. Supply Voltage




Figure 20. Logic 1 Input Voltage vs. Supply Voltage

Figure 17. Output Source Current vs. Temperature




Figure 19. Output Sink Current vs. Temperature






Figure 21. Logic 1 Input Voltage vs. Temperature



Typical Performance Characteristics (Cont.)












Figure 26. VCC UVLO vs. Temperature




Figure 23. Logic 0 Input Voltage vs. Temperature




Figure 25. Deadtime vs. Temperature





Figure 27. Offset Supply Leakage Current vs. Temperature



DGD2103

Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.



Note : For high-voltage applications, the appropriate industry sector guidelines should be considered with regards to creepage and clearance distances between device Terminals and PCB tracking.



DGD2103

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2017, Diodes Incorporated

www.diodes.com

DGD2103 Document Number DS38278 Rev. 5 - 3