HDC MPN 1.6 SOF



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com





Make your connections fit for the future With the advanced solutions from RockStar® ModuPlug

Industrial applications are becoming increasingly complex. The demands being made of the connectivity used are growing at the same time. Functionality in the smallest of installation spaces, safe installation and a fast retrofitting process are just some of the product properties being called for. Not only does our RockStar® ModuPlug modular plug-in connector system meet current market requirements; it has been specially designed with the future in mind too. Using the individual modules, you combine all the necessary functions for power, signal and data transmission in a single interface. Thanks to the new variety of module sizes, you can fit more applications than ever before in one plug-in connector. The modules reduce the amount of space required and cut costs when compared with fixed-pole inserts and other modular plug-in connector systems. The sophisticated frames and modules can be installed with extreme ease and integrated into HDC enclosures with the IP65 and IP68 protection classes. You can even use the RockStar® ModuPlug to supplement existing applications without any need to make system adjustments. As an experienced Industrial Connectivity partner, Weidmüller offers ultra-modern connectivity with maximum reliability. So you can create customised solutions for future-proof connections with RockStar® too.

General ordering data

Туре	HDC MPN 1.6 SOF		
Order No.	<u>2637490000</u>		
Version	Pneumatic contact		
GTIN (EAN)	4050118654738		
Qty.	10 pc(s).		

HDC MPN 1.6 SOF

Technical data



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com

Dimensions and weig	hts		
Net weight	0.653 g		
Temperatures			
Limit temperature	-40 °C 80 °C		
Pneumatic contact			
Operating pressure	≤8 bar	Inner hose diameter	1.6 mm
Contact with valve	Yes		1.0 1111
Classifications			
ETIM 6.0 eClass 9.0	EC002943 27-44-02-92	ETIM 7.0 eClass 9.1	EC002943 27-44-02-92
eClass 9.0 eClass 10.0	27-44-02-92		27-44-02-92
Approvals			
ROHS	Conform		
Downloads			
Engineering Data	STEP		