

Multilayer Ceramic Chip Capacitor


Part Number: 2220Y2K00104KXTWS3

Description: 2220 2000Vdc 100nF ±10% X7R (2R1)

A range of X7R MLC capacitors to suit a variety of applications. In a wide selection of chip sizes, rated voltages and terminations, including FlexiCap[™], the world's first commercially available flexible termination.

WS2 and WS3 parts use StackiCap™ patented construction technology.

Suffix code PXX or PX mandates the use of precious metal electrode (PME) materials. This may incur additional costs.



Mechanical Specification		
Size Code	2220	
Length (L1) in mm (")	5.8 ± 0.4 (0.225 ± 0.016)	
Width (W) in mm (")	5.0 ± 0.40 (0.197 ± 0.016)	
Thickness (T) in mm (")	4.5 Max (0.177 Max)	
Minimum Termination Band (L2,L3) in mm (")	0.25 (0.010)	
Maximum Termination Band (L2,L3) in mm (")	1.00 (0.040)	
Termination Material	FlexiCap [™] Polymer termination, Nickel barrier, Sn Plated Solder (RoHS compliant)	
Solderability	IEC-60068-2-58	
Packaging	7" Reel Horizontal Orientation, 500 per reel	
Conformal Coating	Considered essential and was used for internal qualification testing	

		-	
Rated Voltage		2000Vdc	
Nominal Capacitance Value		100nF	
Capacitance Tolerance		±10%	
Tangent of Loss Angle (Tan δ)		≤0.025	
Capacitance and Tan δ Test Conditions		1.0Vrms @ 1kHz	
Voltage Proof		2400Vdc	
(Voltage applied for 5 secs max. @ 50mA max. charge current)			
Min Insulation Resistance (IR)		5.00GOhm @ 100Vdc	
Dielectric Classification		X7R (2R1)	
Rated Temperature Range		-55°C / +125°C	
Maximum Capacitance Change over Temperature Range		No DC Voltage	±15%
		Rated DC Voltage -	
Climatic Category (IEC)		55/125/56	
Ageing Characteristic		<2% per decade (nominal capacitance is 1000 hour value)	
	1		
Knowles Precision Devices - Sales	This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at http://www.knowlescapacitors.com or by contacting us.		
Europe: KPD-Europe-sales@knowles.com			
Asia: KPD-Asia-sales@knowles.com	© The information contained on this drawing is Data is correct to the best of our knowledge, errors and confidential and may not be copied in whole or part in omissions excepted.		
USA: KPD-NA-sales@knowles.com	any form or disclosed to a t	or party without the consent omer mentioned within this	Data: Wadnasday, Dasamber 07, 2022
www.knowlescapacitors.com	specification.		Date: Wednesday, December 07, 2022 20221207 195340471UTC



Multilayer Ceramic Chip Capacitor

Part Number: 2220Y2K00104KXTWS3	Description: 2220 2000Vdc 100nF ±10% X7R (2R1)
Env	ironmental
RoHS Compliant to 2011/65/EC as amended by 2015/863/	EU Compliant
REACH Compliant	224 compliant
California Proposition 65	No exposure risk
Воа	ard Layout
Knowles' conventional 2-terminal chip capacitors of generally be mounted using pad designs in accordance w international specification IPC-7351, Generic Requireme for Surface Mount Design and Land Pattern Standards, there are some other factors that have been shown to redu mechanical stress, such as reducing the pad width to be than the chip width. In addition, the position of the chip on board should be considered. Some high voltage parts may require modifications to board layout and/or the addition of a conformal coating prevent flashover. Refer to application note AN0043 further information.	$\begin{array}{c} C & 5.30 \text{mm} & 0.209^{\text{m}} \\ \hline Y & 1.50 \text{mm} & 0.059^{\text{m}} \\ \hline X & 5.40 \text{mm} & 0.213^{\text{m}} \\ \hline \end{array}$
Pa	ackaging
Tape packaging information for tape-and-reel parts: Tape and reel packing of surface mounting chip capacitors automatic placement are in accordance with IEC60286-3.	for Product identifying label Plastic carrier tape Top tape 8 or 12mm 178mm (7") or nominal 330mm (13") dia. reel
S	oldering
Reflow solder in accordance with IPC-A-610. Recommender reflow profile as laid down in IPC/JEDEC J-STD-020. Wave soldering is also possible, but care must be taken for case sizes 1210 and larger and component thickness >1.0mm. Trials are encouraged. Hand soldering is not recommended and can lead to component damage through thermal shock. PdAg terminations are primarily intended for conductive ep attachment - they may be suitable for soldering but trials are	Tp TL Max Min ts Preheat area
recommended. Application notes with mounting and handling guidance are	Time
Compex DLI Johanson MFC	
Europe: KPD-Europe-sales@knowles.com Asia: KPD-Asia-sales@knowles.com USA: KPD-NA-sales@knowles.com	or a standard item and is confirmed valid on the date generated, the latest published date for and is available at http://www.knowlescapacitors.com or by contacting us. contained on this drawing is not be copied in whole or part in to a third party without the consent customer mentioned within this Data is correct to the best of our knowledge, errors and omissions excepted. Date: Wednesday, December 07, 202. 20221207 195340471UTC