



SPECIFICATIONS

Model	Rated Torque	Max Rotation Speed	Max Cycle Rate
FRT-E2-300	(3.0±0.8)X10 ⁻³ Nm (30±8gfcm)	50 RPM	10 cycles/ min.


Operating	Weight	Body & Cap	Rotating Shaft	Oil
Temperature		Material	Material	Type
0 ~ 50°C	0.32g	Polycarbonate	Polyacetal	Silicone Oil

Note 1) Rated torque measured at a rotation speed of 20rpm at 23°C

Note 2) Models with gears bear G1 or G2 at the end

Note 3) Torque can be customized by changing the oil viscosity

DAMPING CHARACTERISTICS



- **Speed characteristics:** A rotary damper's torque varies according to the rotation speed. In general, as shown in the graph to the left, the torque increases as the rotation speed increases, and the torque decreases as the rotation speed decreases. In addition, please note that the starting torque slightly differs from the rated torque.
- Temperature characteristics: A rotary damper's torque varies according to the ambient temperature. In addition, as shown in the graph to the left, the torque decreases as the ambient temperature increases, and the torque increases as the ambient temperature decreases. This is because the viscosity of the silicone oil inside the damper varies according to the temperature. When the temperature returns to normal, the torque will return to normal as well.