

HS2A thru HS2M

High Efficient Surface Mount Rectifiers Reverse Voltage 50 to 1000 Volts Forward Current 1.5 Amperes

Features


- Glass passivated junction chip.
- ◆ For surface mounted application
- ◆ Low forward voltage drop
- Low profile package
- ◆ Built-in stain relief, ideal for automatic placement
- Fast switching for high efficiency
- ♦ High temperature soldering:
- 250°C/10 seconds at terminals
- Plastic material used carries Underwriters Laboratory Classification 94V-O

Mechanical Data

- ◆ Cases: Molded plastic
- ◆ Terminals: Solder plated
- Polarity: Indicated by cathode band
 Weight: 0.003 ounce, 0.093 gram



DO-214AA (SMB)



Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified Single phase, half wave, 60Hz, resistive or inductive load For capacitive load, derate current by 20%

Parameter	Symbols	HS2A	HS2B	HS2D	HS2F	HS2G	HS2J	HS2K	HS2M	Units
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	300	400	600	800	1000	Volts
Maximum RMS voltage	V _{RMS}	35	70	140	210	280	420	560	700	Volts
Maximum DC blocking voltage	V _{pc}	50	100	200	300	400	600	800	1000	Volts
Maximum average forward rectified current See Fig.2	l _(AV)	1.5							Amps	
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	FsM	50.0							Amps	
Maximum instantaneous forward voltage @ 1.5A	V _F	1.0 1.3 1.7						Volts		
Maximum DC reverse current @ T _A =25°C at rated DC blocking voltage @ T _A =100°C	l _R	5.0 100							uA uA	
Maximum reverse recovery time (Note 1)	ţ,	50 75							nS	
Typical junction capacitance (Note 2)	C	50 30							pF	
Operating junction temperature range	,T,	-55 to +150								°C
Storage temperature range	T _{stg}	-55 to +150							°C	


Notes:

- 1. Reverse Recovery Test Conditions: I_F=0.5A, I_R=1.0A, I_{RR}=0.25A
- 2 Measured at 1 MHz and Applied Reverse Voltage of 4.0 V D.C.



RATINGS AND CHARACTERISTIC CURVES


100 NONINDUCTIVE 500 YOYINDUCTIVE (*) 50Vdc (approx) (-) PULSE GENERATOR (NOTE 2) NON (OSCILLOSCOPE NOTES 1. Rise Time-7ns max. Input Impedance-1 megetim 22pf 2 Rise Time-10ns max. Sourse Impedance-50 ohms.



DERATING CURVE 3 3.0 FORWARD CURRENT 2.5 21 1 ! 1 (50 75 100 125 150 175 75 LEAD TEMPERATURE (C)

FIG.2- MAXIMUM FORWARD CURRENT

FIG.3- TYPICAL REVERSE CHARACTERISTICS






FIG.5- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT

