

## CDS series

- Low impedance, 105°C 2000 hours High CV
- Applicable to SMT process
- AEC-Q200 Compliant
- RoHS Compliant



## SPECIFICATIONS

Items	Characteristics						
Capacitance Tolerance	$\pm 20\%$ (120Hz , 20°C)						
Operating Temperature Range	-55°C ~ + 105°C						
Rated Voltage Range	6.3 ~ 50VDC						
Capacitance Range	10 ~ 2200μF						
Leakage Current	$I \leq 0.01CV$ or $3(\mu A)$ , which is greater. (After 2 minutes application of DC rated voltage at 20°C)						
Dissipation Factor (tan δ)	Measurement Frequency:120Hz. Temperature: 20°C						
	Rated Voltage(V)	6.3	10	16	25	35	50
	tanδ ( Max)	0.26	0.19	0.16	0.14	0.12	0.10
Low Temperature Stability	Measurement Frequency:120Hz						
	Rated Voltage(V)	6.3	10	16	25	35	50
Impedance Ratio(Max)	Z(-25°C) / Z(20°C)	4	3	2	2	2	2
	Z(-40°C) / Z(20°C)	8	5	4	3	3	3
Load Life	2000 hours with application of rated voltage at 105°C						
	Capacitance Change	within $\pm 30\%$ of Initial Value					
	tan δ	200% or less of Initial Specified Value					
	Leakage Current	Initial Specified Value or less					
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1000 hours 105°C without voltage applied. Before the measurement, the capacitance shall be preconditioned by applying voltage according to them 4.1 of JIS C5101-4.						
	Capacitance Change	Within $\pm 30\%$ of Initial Value					
	tan δ	200% or less of Initial Specified Value					
	Leakage Current	Initial Specified Value or less					
Resistance to Soldering Heat	The capacitors shall be kept on the hot plate maintained at 250°C for 30 seconds. After removing from the hot plate and restored at room temperature, they meet the characteristics requirements listed at right.				Capacitance Change	Within $\pm 10\%$ of Initial Value	
					tan δ	Initial Specified Value	
					Leakage Current	Initial Specified Value or less	
Standards	JIS C 5101-4-1 (IEC 60384)						

## Frequency Coefficient of Permissible Ripple Current

Frequency (Hz)	$120 \leq F < 1K$	$1K \leq F < 10K$	$10K \leq F < 100K$	$100K \leq F$
$\leq 470$	0.65	0.85	0.95	1.00
$> 470$	0.70	0.90	0.95	1.00

The endurance of capacitors is reduced with internal heating produced by ripple current at the rate of halving the lifetime with every 5°C rise. When long life performance is required in actual use, The rms ripple current has to be reduced.



# Aluminum Electrolytic Capacitors

**Su'scon**


## DIMENSIONS(mm)

### ■ Chip Type

Fig.1  $\Phi D=4\sim10mm$



### ■ Land / Pad pattern



Size	$\Phi D$	L	W	H	C	R	P	Vmax
4*6	4.0	6.0±0.3	4.3	4.3	5.1	0.5~0.8	1.0	0.3
5*6	5.0	6.0±0.3	5.3	53	5.9	0.5~0.8	1.5	0.3
6.3*6	6.3	6.0±0.3	6.6	6.6	7.2	0.5~0.8	2.1	0.3
6.3*7.7	6.3	7.7±0.3	6.6	6.6	7.2	0.5~0.8	2.1	0.3
8*10	8.0	10±0.5	8.4	8.4	9.0	0.7~1.1	3.2	0.3
10*10	10.0	10±0.5	10.3	10.3	11.0	0.7~1.3	4.5	0.3

DxL	A	B	C
$\Phi 4$	1	2.6	1.6
$\Phi 5$	1.4	3	1.6
$\Phi 6.3$	1.9	3.5	1.6
$\Phi 8$	3	3.5	2.5
$\Phi 10$	4	4	2.5
$\Phi 12.5$	4.3	5.8	2.5
$\Phi 16$	6.6	6.5	5
$\Phi 18$	6.6	7.7	5
$\Phi 8(G)$	2.5	4.5	4.7
$\Phi 10(G)$	3.8	4.8	4.7
$\Phi 12.5(G)$	3.8	6.1	6.9
$\Phi 16(G)$	5	8	9.5
$\Phi 18(G)$	5	8.6	9.5

"(G)" "Anti-vibration Structure"

## Electric Characteristics

Su'scon P/N	Cap. (uF)	Cap. Tol. (%)	Rate Volt. (V-DC)	Surge Volt. (V-DC)	Oper. Temp. (°C)	Nominal Case Size $D*L$ (mm)	Leakage Current Max (uA)	D.F. MAX (%)	R.C 100KHz (mA rms)	IMP 100KHz at 25°C(Ω)Max	Load Life (hours)
CDS016M101D06PE50V00A	100	±20	16	18.4	105	5*6	16	16	240	0.400	2000
CDS016M221E06PE50V00A	220	±20	16	18.4	105	6.3*6	35	16	300	0.300	2000
CDS025M220C06PE50V00A	22	±20	25	28.8	105	4*6	5.5	14	160	1.00	2000
CDS035M220C06PE50V00A	22	±20	35	40.3	105	4*6	7.7	12	160	1.00	2000

## REMARKS:

1. Dissipation Factor Test: at 20°C, 120 Hz
2. Capacitance Test: at 20°C, 120 Hz
3. Ripple Current Test: at 105°C, 100K Hz
4. Leakage Current: Initial specified value or less;
5. When have characteristic requested: Load life & shelf life test and etc., judgment standard reference to our catalogue.
6. Remarks: Su'scon Part Number with suffix code "A" is specially offered for automotive project, which meets AEC-Q200 standard.

## **US Contact Information**

Tony Yang

Lumimax Optoelectronic Technology

Tel: +1 510 241 9686

Mobile: +1 510 364 7157

Email: tony.yang@lumimaxusa.com

### **DONG GUAN KUAN KUN ELECTRONIC CO., LTD**

**YIN HE INDUSTRIAL ZONE, QING XI TOWN,      TEL: +86-769- 87318000  
DONG GUAN CITY, GUAN DONG CHINA (P.R.O.C)      FAX: +86-769- 87318008**