

CGL series

- Low impedance, 125°C 2000~3000 hours long life
- Applicable to SMT process
- AEC-Q200 Compliant
- RoHS Compliant



SPECIFICATIONS

Items	Characteristics				
Capacitance Tolerance	$\pm 20\%$ (120Hz , 20°C)				
Operating Temperature Range	-40°C ~ + 125°C				
Rated Voltage Range	16 ~ 50VDC				
Capacitance Range	33 ~ 330μF				
Leakage Current	$I \leq 0.01CV$ or $3(\mu A)$, which is greater. (After 2 minutes application of DC rated voltage at 20°C)				
Dissipation Factor (tan δ)	Measurement Frequency:120Hz. Temperature: 20°C Rated Voltage(V) 16 25 35 50 tanδ (Max) 0.23 0.18 0.16 0.14				
Low Temperature Stability	Measurement Frequency:120Hz				
Impedance Ratio(Max)	Rated Voltage(V) 16 25 35 50 Z(-25°C) / Z(20°C) 3 3 2 2 Z(-40°C) / Z(20°C) 4 4 3 3				
Load Life	5000 hours with application of rated voltage at 125°C Capacitance Change within $\pm 30\%$ of Initial Value tan δ 300% or less of Initial Specified Value Leakage Current Initial Specified Value or less				
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1000 hours 125°C without voltage applied. Before the measurement, the capacitance shall be preconditioned by applying voltage according to them 4.1 of JIS C5101-4. Capacitance Change Within $\pm 30\%$ of Initial Value tan δ 300% or less of Initial Specified Value Leakage Current Initial Specified Value or less				
Resistance to Soldering Heat	The capacitors shall be kept on the hot plate maintained at 250°C for 30 seconds. After removing from the hot plate and restored at room temperature, they meet the characteristics requirements listed at right.			Capacitance Change	Within $\pm 10\%$ of Initial Value
				tan δ	Initial Specified Value
				Leakage Current	Initial Specified Value or less
Standards	JIS C 5101-4-1 (IEC 60384)				

Frequency Coefficient of Permissible Ripple Current

Frequency (Hz) Capacitance (μF)	120 ≤ F < 1K	1K ≤ F < 10K	10K ≤ F < 100K	100K ≤ F
33 ~ 330	0.40	0.75	0.90	1.00


The endurance of capacitors is reduced with internal heating produced by ripple current at the rate of halving the lifetime with every 5°C rise. When long life performance is required in actual use, The rms ripple current has to be reduced.

Aluminum Electrolytic Capacitors


Su'scon

DIMENSIONS(mm)

■ Chip Type



■ Land / Pad pattern



ΦD	8*10	10*10
A	2.9	3.2
B	8.3	10.3
C	8.3	10.3
E	3.1	4.5
L	10	10
H	0.8~1.1	0.8~1.1

DxL	A	B	C
Φ4	1	2.6	1.6
Φ5	1.4	3	1.6
Φ6.3	1.9	3.5	1.6
Φ8	3	3.5	2.5
Φ10	4	4	2.5
Φ12.5	4.3	5.8	2.5
Φ16	6.6	6.5	5
Φ18	6.6	7.7	5
Φ8(G)	2.5	4.5	4.7
Φ10(G)	3.8	4.8	4.7
Φ12.5(G)	3.8	6.1	6.9
Φ16(G)	5	8	9.5
Φ18(G)	5	8.6	9.5

"(G)" "Anti-vibration Structure"

Electric Characteristics

Su'scon P/N	Cap. (uF)	Cap. Tol. (%)	Rate Volt. (V-DC)	Surge Volt. (V-DC)	Oper. Temp. (°C)	Nominal Case Size D*L(mm)	Leakage Current Max (uA)	D.F. MAX (%)	R.C 100KHz (mA rms)	IMP 100KHz at 25°C(Ω)Max	Load Life (hours)
CGL025M101F10PE50V00A	100	±20	25	28.8	125	8*10	25	18	300	0.300	3000
CGL025M221F10PE50V00A	220	±20	25	28.8	125	8*10	55	18	300	0.300	3000
CGL050M101G10PE50V00A	100	±20	50	57.5	125	10*10	50	14	350	0.250	3000

REMARKS:

1. Dissipation Factor Test: at 20°C, 120 Hz
2. Capacitance Test: at 20°C, 120 Hz
3. Ripple Current Test: at 125°C, 100K Hz
4. Leakage Current: Initial specified value or less;
5. When have characteristic requested: Load life & shelf life test and etc., judgment standard reference to our catalogue.
6. Remarks: Su'scon Part Number with suffix code "A" is specially offered for automotive project, which meets AEC-Q200 standard.

US Contact Information

Tony Yang

Lumimax Optoelectronic Technology

Tel: +1 510 241 9686

Mobile: +1 510 364 7157

Email: tony.yang@lumimaxusa.com

DONG GUAN KUAN KUN ELECTRONIC CO., LTD

**YIN HE INDUSTRIAL ZONE, QING XI TOWN, TEL: +86-769- 87318000
DONG GUAN CITY, GUAN DONG CHINA (P.R.O.C) FAX: +86-769- 87318008**

CGL-REV.1