



## **Specification of Automotive MLCC**

• Supplier : Samsung electro-mechanics • Samsung P/N : CL10C120JB81PNC

• Product : Multi-layer Ceramic Capacitor • Description : CAP, 12pF, 50V, ±5%, C0G, 0603

• AEC-Q 200 Specified

## A. Samsung Part Number

<u>CL</u> <u>10</u> <u>C</u> <u>120</u> <u>J</u> <u>B</u> <u>8</u> <u>1</u> <u>P</u> <u>N</u> <u>C</u> ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

1	Series	Samsung Multi-layer Ceramic Capacitor			
2	Size	0603 (inch code)	L:	1.6 ± 0.1 mm	W: $0.8 \pm 0.1 \text{ mm}$
3	Dielectric	C0G	(	8 Inner electrode	Ni
4	Capacitance	<b>12</b> pF		Termination	Cu
(5)	Capacitance	±5 %		Plating	Sn 100% (Pb Free)
	tolerance		(	9 Product	Automotive
6	Rated Voltage	50 V	Ć	Grade code	Standard
7	Thickness	$0.8 \pm 0.1$ mm	Ć	Packaging	Cardboard Type, 7" reel(4,000ea)

## B. Reliability Test and Judgement condition

	Performance	Test condition
High Temperature	Appearance : No abnormal exterior appearance	Unpowered, 1000hrs@T=150℃
Exposure	Capacitance Change :	Measurement at 24±2hrs after test conclusion
	within ±2.5% or ±0.25pF whichever is larger	
	Q: 640 min	
	IR : More than 10,000MΩ or 500MΩ×μF	
	Whichever is Smaller	
Temperature Cycling	Appearance : No abnormal exterior appearance	1000Cycles
	Capacitance Change :	Measurement at 24±2hrs after test conclusion
	within ±2.5% or ±0.25pF whichever is larger	1 cycle condition :
	Q: 640 min	-55+0/-3 °C (15±3min) -> Room Temp(1min.)
	IR : More than 10,000№ or 500№× <i>μ</i> F	-> 125+3/-0 °C (15±3min) -> Room Temp(1min.)
	Whichever is Smaller	
Destructive Physical	No Defects or abnormalities	Per EIA 469
Analysis		
Moisture Resistance	Appearance : No abnormal exterior appearance	10Cycles, t=24hrs/cycle
	Capacitance Change :	Heat (25~65°C) and humidity (80~98%), Unpowered
	within ±2.5% or ±0.25pF whichever is larger	measurement at 24±2hrs after test conclusion
	Q: 305 min	
	IR : More than 10,000№ or 500№×μF	
	Whichever is Smaller	
Humidity Bias	Appearance : No abnormal exterior appearance	1000hrs 85°C/85%RH, Rated Voltate and 1.3~1.5V,
	Capacitance Change :	Add 100kohm resistor
	within ±2.5% or ±0.25pF whichever is larger	Measurement at 24±2hrs after test conclusion
	Q: 140 min	The charge/discharge current is less than 50mA.
	IR : More than 500№ or 25№νμF	
	Whichever is Smaller	
High Temperature	Appearance : No abnormal exterior appearance	1000hrs @ TA=125℃, 200% Rated Voltage,
Operating Life	Capacitance Change :	Measurement at 24±2hrs after test conclusion
	within ±3.0% or ±0.3pF whichever is larger	The charge/discharge current is less than 50mA.
	Q: 305 min	
	IR : More than 10,000№ or 500№× <i>μ</i> F	
	Whichever is Smaller	

	Performance	Test condition			
External Visual	No abnormal exterior appearance	Visual inspection			
Physical Dimensions	Within the specified dimensions	Using The calipers			
Mechanical Shock	Appearance : No abnormal exterior appearance	Three shocks in each direction should be applied along			
	Capacitance Change :	3 mutually perpendicular axes of the test specimen (18 shocks)			
	within ±2.5% or ±0.25pF whichever is larger	Peakvalue Duration Wave Velocity			
Q, IR : initial spec.		1,500G 0.5ms Half sine 4.7m/sec.			
Vibration Appearance : No abnormal exterior appearance		5g's for 20min., 12cycles each of 3 orientations,			
	Capacitance Change :	Use 8"x5" PCB 0.031" Thick 7 secure points on one long side			
	within ±2.5% or ±0.25pF whichever is larger	and 2 secure points at corners of opposite sides. Parts mounted			
	Q, IR: initial spec.	within 2" from any secure point. Test from 10~2000Hz.			
Resistance to	Appearance : No abnormal exterior appearance	Solder pot: 260±5°C, 10±1sec.			
Solder Heat Capacitance Change :					
within ±2.5% or ±0.25pF whichever is larger					
	Q, IR : initial spec.				
Thermal Shock	Appearance : No abnormal exterior appearance	-55°C/+125°C.			
	Capacitance Change :	Note: Number of cycles required-300,			
	within ±2.5% or ±0.25pF whichever is larger	Maximum transfer time-20 sec, Dwell time-15min. Air-Air			
	Q, IR : initial spec.				
ESD	Appearance : No abnormal exterior appearance	AEC-Q200-002			
	Capacitance Change :				
	within ±2.5% or ±0.25pF whichever is larger				
	Q, IR: initial spec.				
Solderability	95% of the terminations is to be soldered	a) Preheat at 155℃ for 4 hours, Immerse in solder for 5s at 245±5℃			
	evenly and continuously	b) Steam aging for 8 hours, Immerse in solder for 5s at 245±5℃			
		c) Steam aging for 8 hours, Immerse in solder for 120s at 260±5 ℃			
		solder : a solution ethanol and rosin			
Electrical	Capacitance : Within specified tolerance	The Capacitance /Q should be measured at 25 ℃,			
Characterization	Q: 640 max.	1Mb±10%, 0.5~5Vrms			
	IR(25 ℃): More than 100,000MΩ or 1,000MΩ×μF	I.R. should be measured with a DC voltage not exceeding			
	IR(125℃): More than10,000MΩ or 100MΩ×μF	Rated Voltage @25°C, @125°C for 60~120 sec.			
	Whichever is Smaller	Dielectric Strength: 250% of the rated voltage for 1~5 seconds			
	Dielectric Strength				
Board Flex Appearance : No abnormal exterior appearance		Bending to the limit (3mm) for 5 seconds			
	Capacitance Change :				
	within ±5.0% or ±0.5pF whichever is larger				
Terminal	Appearance : No abnormal exterior appearance	10N, for 60±1 sec.			
Strength(SMD)	Capacitance Change :				
	within ±2.5% or ±0.25pF whichever is larger				
Beam Load Destruction value should not be exceed		Beam speed			
	Chip Length < 2.5mm	0.5±0.05mm/sec			
	a) Chip Thickness > 0.5mm : 20N				
	b) Chip Thickness ≤ 0.5mm : 8N				
Temperature	COG				
Characteristics	(From -55 °C to 125 °C, Capacitance change should be within ±30PPM/ °C)				

## C. Recommended Soldering method :

Reflow ( Reflow Peak Temperature : 260+0/-5  $^{\circ}\!\!\!\mathrm{C}$  , 10sec. Max )

Meet IPC/JEDEC J-STD-020 D Standard

<sup>\*</sup> For the more detail Specification, Please refer to the Samsung MLCC catalogue.