



SPECIFICATIONS

Model	Rated Torque	Max Rotation Speed	Max Cycle Rate
FRT-E9-400-G2	(4.0±1.0)X10 ⁻³ Nm (40±10gfcm)	50 RPM	10 cycles/ min.

Operating	Weight	Body & Cap	Rotating Shaft	Gear	Oil
Temperature		Material	Material	Material	Type
0 ~ 50°C	0.38g	Polycarbonate	Polyacetal	Polyacetal	Silicone Oil

Note 1) Rated torque measured at a rotation speed of 20rpm at 23°C Note 2) Models with gears bear G1 or G2 at the end


Note 3) Torque can be customized by changing the oil viscosity


Note 4) Model E9 is a customized product with a one-sided mounting


GEAR SPECIFICATIONS

Model	Туре	Tooth Profile	Module	Pressure Angle	Number of Teeth	Pitch Circle Diameter	Weight (damper+gear)
G2	Standard Spur Gear	Involute	0.6	20°	11	ø6.6	0.38g (0.32g+0.06g)

DAMPING CHARACTERISTICS







■ Temperature characteristics: A rotary damper's torque varies according to the ambient temperature. In addition, as shown in the graph above, the torque decreases as the ambient temperature increases, and the torque increases as the ambient temperature decreases. This is because the viscosity of the silicone oil inside the damper varies according to the temperature. When the temperature returns to normal, the torque will return to normal as well.