



#### Features

- High quality silver alloy or gold plated contacts
- Sealing technology meets IP6K5
- 2- and 3-position switch actions
- Variety of available switching styles
- Locking options for individual needs

#### Applications

- Commercial vehicles
- Construction machinery
- Aviation ground support equipment
- Plant and industrial engineering
- Medical equipment

# KISSLING TOGGLE SWITCH

Series 07 - from TE Connectivity (TE)

### **Quality Safety Switch**

The KISSLING toggle switches from TE Connectivity's product family have been developed under strict guidelines to meet international standards.

This series of toggle switches is mainly used as robust, industrial and durable control switches in commercial vehicles. The housing of the Series 7 is made of thermoplastic and meets IP68 protection class standards.

All these switches are sealed themselves and we offer additional sealing rings for improved mounting solutions and optional bellows for the handles. Our broad selection of toggles includes many options for switching configuration, termination type, load carrying capabilities and locking combinations.


TE Connectivity provides switches both with and without switch guards to prevent accidental switching, as well as individual switches and complete switch assemblies with additional sealed housings for simplified vehicle assembly procedures. Series 07

# Specification

#### **Technical Data**

Housing Material	Thermoplast GF					
Construction iaw	IEC 1 020					
Seal Connection	IP65 IEC 60529 / IP6K5 DIN 40050 part 9 / IP6K5 ISO 20653 IP00 IEC 60529 / IP00 DIN 40050 PART 9 / IP00 ISO 20653					
Current carrying parts	CuZn-alloy					
Contact material	Silver-alloy or gold plated contacts					
Temperature range	-35°C to +60°C					
Electrical life (nominal load)	100.000 cycles					
Nominal voltage / Continuous current	12VDC, 20A ohmic load 28VDC, 20A ohmic load 28VDC, 15A L/R = 5msec inductive load 115VAC, 15A inductive load					
Min. switching capacity	12VDC, 20mA					

### **Technical drawings**




# **KISSLING TOGGLE SWITCH**

Series 07

### **Switching Styles**

Switch- 1-pole				2-pole Toggle position in			4-pole Toggle position in		
ing	· · · · · · · · · · · · · · · · · · ·								
Styles	keyway side	center	opposite keyway side	keyway side	center	opposite keyway side	keyway side	center	opposite keyway side
10	0	-	2-3	0 0	-	2-3 5-6	0 0 0 0	-	2-3 5-6 8-9 11-12
11	0 *	-	2-3	0 * 0	-	2-3 5-6	0 0 0 * 0	-	2-3 5-6 8-9 11-12
12	1-2 *	-	0	1-2 * 4-5	-	0 0	1-2 4-5 7-8 10-11	-	0 0 0 0
13	1-2	-	2-3	1-2 4-5	-	2-3 5-6	1-2 4-5 7-8 10-11	-	2-3 5-6 8-9 11-12
14	1-2 *	-	2-3	1-2 * 4-5	-	2-3 5-6	1-2 <sub>*</sub> 4-5 7-8 10-11	-	2-3 5-6 8-9 11-12
15	1-2	0	2-3	1-2 4-5	0 0	2-3 5-6	1-2 4-5 7-8 10-11	0 0 0 0	2-3 5-6 8-9 11-12
16	1-2 *	0	2-3	1-2 * 4-5	0 0	2-3 5-6	1-2 4-5 7-8 10-11	0 0 0 0	2-3 5-6 8-9 11-12
17	1-2 *	0	2-3 *	1-2 * 4-5	0 0	2-3 * 5-6	1-2 <sub>*</sub> 4-5 7-8 10-11	0 0 0 0	2-3 <sub>*</sub> 5-6 8-9 11-12
18	1-2	1-2	2-3	1-2 4-5	1-2 4-5	2-3 5-6	1-2 4-5 7-8 10-11	1-2 4-5 7-8 10-11	2-3 5-6 8-9 11-12
19	1-2	1-2	2-3 *	1-2 4-5	1-2 4-5	2-3 * 5-6	1-2 4-5 7-8 10-11	1-2 4-5 7-8 10-11	2-3 5-6 8-9 11-12
20				1-2 4-5	1-2 5-6	2-3 5-6	1-2 4-5 7-8 10-11	2-3 4-5 0 0	2-3 5-6 8-9 11-12
21				1-2 4-5	1-2 5-6	2-3 5-6			
22				1-2 * 4-5	1-2 5-6	2-3 * 5-6	1-2 4-5 7-8 10-11	2-3 4-5 0 0	2-3 5-6 8-9 11-12
23	1-2	2-3	2-3	1-2 4-5	2-3 4-5	2-3 5-6	1-2 4-5 7-8 10-11	2-3 4-5 7-8 11-12	2-3 5-6 8-9 11-12
24				1-2 4-5	1-2 5-6	2-3 * 5-6			
25				1-2 * 4-5	1-2 5-6	2-3 5-6	1-2 4-5 7-8 10-11	2-3 4-5 7-8 11-12	2-3 5-6 8-9 11-12
26							1-2 4-5 7-8 10-11	2-3 4-5 7-8 11-12	2-3 5-6 8-9 11-12
27							1-2 4-5 7-8 10-11	2-3 4-5 7-8 11-12	2-3 5-6 8-9 11-12

## **Ordering Information**



### Locking options


Available locking combinations			recommended for		
		keyway side center		opposite keyway side	switching style
А		locked	locked	locked	15, 18, 20, 21, 23, 26
В		locked	locked	locked out	15, 18, 19, 20, 21, 23, 24, 26
D		locked	locked out	locked	10, 13
E	-	locked out	locked	locked out	15 - 27
F		locked out	locked out	locked	10, 11, 12, 13, 14
G		locked	locked out	locked out	10, 13
К		locked out	locked	locked	15, 16, 18, 20, 21, 23, 25, 26
L		locked out	locked to keyway side	locked out	15 - 27
М		locked out	locked to opposite keyway side	locked out	15, 16, 18, 20, 21, 23, 25, 26
N		locked out	locked to opposite keyway side	locked out	15 - 27
Р		locked	locked to keyway side	locked out	15, 18, 19, 20, 21, 23, 24, 26
т		locked	locked from middle to keyway side	locked from opposite keyway side to middle	15, 18, 20, 23, 26

→ = keyway side

### Accessories

#### Switch Guard:

Prevent accidental switching of toggle



#### Receptacle:

For quick connection, increase safety and prevents from contact the fasteners (IP20) Inverse-polarity protection.


Available for switches with faston connection

#### te.com


TE Connectivity, TE, TE connectivity (logo), KISSLING (word) and FASTON are trademarks licensed or owned by the TE Connectivity family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2020 TE Connectivity | All Rights Reserved. K1166729 | Version 08/2020 Seal ring: 08.0.0.50 For sealing of mounting hole



#### Tooth lock washer





1- POLE

08.1.2.05





