

# Specification Part Number: TM141050

Description: RF Immune Supercardioid Electret Condenser Microphone (Size: 6.0mm x 2.7mm)

Ideal for situations where the user is farther from the microphone than one half meter and where a narrower angle of acceptance – the angle over which the sensitivity is not more than 3dB less than maximum – and good SNR are needed. Situations such as conference phones or robotic devices or multiple microphones arrays are some of the candidates for use of this microphone.

**RoHS Compliant** 



Revision	Date	Comments
A	11/7/2021	Initial Release

www.topshelfacoustics.com

Please contact Top Shelf Acoustics for sales inquiries or integration assistance of your microphone at sales@tsacoustics.com or Miranda Ullrich at (P) 317.512.4569

# 1. ELECTRICAL SPECIFICATIONS

Standard Conditions		Basic Test Conditions	
Ordinary Temperature	5 to 35°C	Temperature	20 ± 2°C
Ordinary Humidity 45 to 85%		Humidity	63 to 67%
Ordinary air pressure	86 to 106kPa	Ordinary air pressure	86 to 106kPa

	Parameter	SPEC	Unit
	Directional	Supercardioid	dB
	Sensitivity	-42±2	dB
	Impedance	2.2(Max)	kΩ
S/I	N Ratio ( A weighted network)	58(Min)	dB
Maxin	num Input Sound Pressure Level	100	dB
Standard Operating Voltage		2.0	Vdc
	Operating Voltage Range	1.0~10	Vdc
Decrease Voltage Characteristics(Vs=3 to 2V dc)		-3(Max)	dB
Current Consumption		500(Max)	μA
Standard Test Circuit		See Fig. 1	—
Frequency Response Characteristic		See Fig. 2	_
Memo Standard test condition		RL=2.2kΩ, Vs=2. (@f=1kHz, Pin=1Pa, 0 L=50cm)	0V dc dB=1V/pa,

www.topshelfacoustics.com Please contact Top Shelf Acoustics for sales inquiries or integration assistance of your microphone at sales@tsacoustics.com or Miranda Ullrich at (P) 317.512.4569 Top Shelf Acoustics

# 2. STANDARD TEST CIRCUIT

Fig.1



### 3. TYPICAL FREQUENCY RESPONSE IN ANECHOIC CHAMBER

Fig.2



www.topshelfacoustics.com

Please contact Top Shelf Acoustics for sales inquiries or integration assistance of your microphone at sales@tsacoustics.com or Miranda Ullrich at (P) 317.512.4569

## 4. RELIABILITY

Item		Test conditions	Evaluation standard	
1	Hi-Temp. Test	The microphone unit must be subjected to +80 ℃ for 100 Hours and exposed to room temperature for 3 Hours.		
2	Low-Temp. Test	The microphone unit must be subjected to -40℃ for 100 Hours and exposed to room temperature for 3 Hours.		
3	Humidity & Heat Test	The microphone unit must be subjected to +55℃, 90% RH-for 100 Hours and exposed to room temp for 3 Hours.		
4	Thermal Shocking Test	The microphone unit must be subjected to following condition [+80 $^{\circ}$ C 0.5H $\rightarrow$ room temp 1H $\rightarrow$ -40 $^{\circ}$ C 0.5H $\rightarrow$ room temp 1H] at 10cycle.	After any of the tests the consitivity of	
5	Vibration Test	The microphone unit must be subjected to a procedure that it is vibrating for two hours from each of the two directions(x y) with a frequency of 10-55Hz and a 1.52mm-high amplitude.	the microphone unit shall not change more than $\pm 3$ dB from initial value and shall keep its initial operation and appearance.	
6	Drop Test	The microphone unit must be subjected to a procedure that it is dropped on a slippery marble floor for 5 times from each axis for a total of 15 times from a 1.0-meter-height without package.		
7	Storage Temperature	<b>-30</b> ℃ <b>~+60</b> ℃		
8	Operating Temperature	<b>-30℃~+60℃</b>		
9	ESD Protection	The test microphone must be discharged between each ESD exposure without ground(contact :±6KV,air:±8KV)		

### NOTES:

www.topshelfacoustics.com

Please contact Top Shelf Acoustics for sales inquiries or integration assistance of your microphone at sales@tsacoustics.com or Miranda Ullrich at (P) 317.512.4569



All the soldering procedures upon microphones must be completed in a heat sink device. The temperature of the soldering iron must be limited to 360°C±20°C and the soldering time should not exceed 3 seconds.

Operators, the soldering fixture and the soldering iron must be statically grounded under each soldering process.