

date 09/05/2012

page 1 of 5

SERIES: VESD2-SIP | **DESCRIPTION:** DC-DC CONVERTER

FEATURES


- 2 W isolated output
- industry standard 7 pin SIP package
- dual unregulated outputs
- 3,000 V isolation
- short circuit protection
- wide temperature (-40~85°C)
- efficiency up to 85%



	_	_						
MODEL		nput oltage	output voltage		tput rent	output power	ripple and noise¹	efficiency
	typ (Vdc)	range (Vdc)	(Vdc)	min (mA)	max (mA)	max (W)	max (mVp-p)	typ (%)
VESD2-S5-D5-SIP	5	4.5~5.5	±5	±20	±200	2	150	82
VESD2-S5-D9-SIP	5	4.5~5.5	±9	±12	±111	2	150	83
VESD2-S5-D12-SIP	5	4.5~5.5	±12	±9	±83	2	150	84
VESD2-S5-D15-SIP	5	4.5~5.5	±15	±7	±67	2	150	82
VESD2-S12-D5-SIP	12	10.8~13.2	±5	±20	±200	2	150	80
VESD2-S12-D9-SIP	12	10.8~13.2	±9	±12	±111	2	150	83
VESD2-S12-D12-SIP	12	10.8~13.2	±12	±9	±83	2	150	85
VESD2-S12-D15-SIP	12	10.8~13.2	±15	±7	±67	2	150	82
VESD2-S24-D5-SIP	24	21.6~26.4	±5	±20	±200	2	150	82
VESD2-S24-D9-SIP	24	21.6~26.4	±9	±12	±111	2	150	82
VESD2-S24-D12-SIP	24	21.6~26.4	±12	±9	±83	2	150	85
VESD2-S24-D15-SIP	24	21.6~26.4	±15	±7	±67	2	150	85

Notes: 1. ripple and noise are measured at 20 MHz BW

PART NUMBER KEY



CUI Inc | SERIES: VESD2-SIP | DESCRIPTION: DC-DC CONVERTER date 09/05/2012 | page 2 of 5

INPUT

parameter	conditions/desc	ription	min	typ	max	units
	5 V model		4.5	5	5.5	Vdc
operating input voltage	12 V model		10.8	12	13.2	Vdc
	24 V model		21.6	24	26.4	Vdc
		5 V model	-0.7		9	Vdc
surge voltage	1 second max.	12 V model	-0.7		18	Vdc
		24 V model	-0.7		30	Vdc
reverse polarity input current	-1				0.4	Α
input filter	C filter					

1. during reverse connection, if current is not limited, may result in injury or permanent damage, testing is not recommended

OUTPUT

parameter	conditions/descriptions	on	min	typ	max	units
line regulation	for Vin change of 1%				1.2	%
load regulation	measured from 10% load to full load	5 V model 9 V model 12 V model 15 V model		10 8.3 6.8 6.3	15 15 15 15	% % % %
voltage accuracy	see derating curves					
switching frequency	100% load, input voltag	ge range		70		kHz
temperature coefficient				±0.03		%/°C

PROTECTIONS

parameter	conditions/description	min	typ	max	units
short circuit protection				1	S

SAFETY AND COMPLIANCE


parameter	conditions/description	min typ	max	units
isolation voltage	for 1 minute at 1 mA max.	3,000		Vdc
isolation resistance	at 500 Vdc	1,000		МΩ
safety approvals	UL			
MTBF		3,500,000		hours
RoHS compliant	yes			


ENVIRONMENTAL


parameter	conditions/description	min	typ	max	units
operating temperature		-40		85	°C
storage temperature		-55		125	°C
storage humidity	non-condensing			95	%
temperature rise	at full load		25		°C
lead temperature	1.5 mm from case for 10 seconds			300	°C

DERATING CURVES

1. output power vs. ambient temperature







MECHANICAL


parameter	conditions/description		min	typ	max	units
dimensions	0.772 x 0.276 x 0.394 (19.60 x 7.00 x	10.00 mm)				inch
case material	plastic (UL94-V0)					
weight				2.1		g


MECHANICAL DRAWING


units: mm [inches]

tolerance: $\pm 0.50 \ [\pm 0.020]$

pin section tolerance: ±0.10 mm [±0.004]







PIN CONNECTIONS				
PIN	FUNCTION			
1	+Vin			
2	GND			
5	-Vo			
6	0 V			
7	+Vo			

APPLICATION NOTES

Requirement on Output Load

In order to ensure the product operates efficiently and reliably, make sure the specified range of input voltage is not exceeded and the minimum output load is not less than 10% load. If the actual load is less than the specified minimum load, the output ripple may increase sharply while its efficiency and reliability will reduce greatly. If the actual output power is very small, please add an appropriate resistor as extra loading.

Overload Protection

Under normal operating conditions, the output circuit of these products has no protection against over-current and short-circuits. The simplest method is to connect a self-recovery fuse in series at the input end or add a circuit breaker to the circuit.

In some circuits which are sensitive to noise and ripple, a filtering capacitor may be added to the DC/DC output end and input end to reduce the noise and ripple. However, the capacitance of the output filter capacitor must be proper. If the capacitance is too big, a startup problem might arise. For every channel of output, provided the safe and reliable operation is ensured, the greatest capacitance of its filter capacitor sees the external capacitor table. To get an extremely low ripple, an "LC" filtering network may be connected to the input and output ends of the DC/DC converter, which may produce a more significant filtering effect. It should also be noted that the inductance and the frequency of the "LC" filtering network should be staggered with the DC/DC frequency to avoid mutual interference (Figure 1).

Vin o Figure 1 DC DC Cin **GND** o

Output Voltage Regulation and Over-voltage Protection Circuit

The simplest device for output voltage regulation, over-voltage and over-current protection is a linear voltage regulator with overheat protection that is connected to the input or output end in series (Figure 2).



External Capacitor Table

It is not recommended to connect any external capacitor in the application field with less than 0.5 W output.

Table 1

Vin (Vdc)	Cout (µF)	Vout (Vdc)	Cout (µF)
5	4.7	±5	4.7
12	2.2	±9	2.2
24	1	±12	1
		±15	0.47

REVISION HISTORY

rev.	description	date
1.0	initial release	06/09/2010
1.01	new template applied	04/13/2012
1.02	V-Infinity branding removed	09/04/2012

The revision history provided is for informational purposes only and is believed to be accurate.



Headquarters 20050 SW 112th Ave. Tualatin, OR 97062 800.275.4899

Fax 503.612.2383 cui.com techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.