




THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO POSITRONIC AND IT'S SUBSIDIARIES. POSITRONIC BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE, SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.














INSERT TREE ASSEMBLY

INSERT CODE	RADIUS "R"		
А	0.063 [1.60]		
В			
C	0.153 [3.87]		
D	0.215 [5.46]		
E	0.275 [6.99]		
F			


## NOTES:

1. MATERIAL AND FINISHES:

HOOD AND TREE INSERT: PBT(EMI), BLACK, COMPOSITE, CONDUCTIVE VOLUME RESISTIVITY [1.0 OHM-CM MAXIMUM]. JACKSCREWS: STEEL, WITH ZINC PLATE.

CABLE CLAMPS: STEEL, WITH NICKEL PLATE.

- DETAILED PRODUCT, MECHANICAL, AND ELECTRICAL INFORMATION IS AVAILABLE IN THE LATEST D-SUB ACCESSORIES PRODUCT PUBLICATION AT CONNECTPOSITRONIC.COM
- CONNECTORS ARE COMPLIANT PER CURRENT ROHS DIRECTIVE.
- DIMENSIONS ARE IN INCHES [MILLIMETERS].



## POSITRONIC INDUSTRIES INC.

		www.connectpositronic.com				FSCM 28198		
	$\bigoplus \bigoplus$	D SERIES		M m d	DRAWN BY	KUNAL V.		
İ	DECIMAL TOL.	"Y" I	H00D	N.T.S.	APPROVED BY	COLE		
	$^{\pm}$ 0.015 (0,38)	D104000Y00/AA						
		DATE	DRAWING NUMBER			REV.		
	angular tol. $\pm 5^{\circ}$	6-6-16	SK1	9065		NC		