

# **Designated client product**

This product will be discontinued its production in the near term.

And it is provided for customers currently in use only, with a time limit.

It can not be available for your new project. Please select other new or existing products.

For more information, please contact our sales office in your region.

New Japan Radio Co.,Ltd.

www.njr.com



### SINGLE-SUPPLY DUAL COMPARATOR

#### **■ GENERAL DESCRIPTION**

The NJM2903/2403 consist of two independent precision voltage comparators with an offset voltage specification as low as 5.0mV max for two comparators, which were designed specifically to operate from a single power supply over a wide range of voltages. Operation from split power supplies is also possible and the low power supply current drain is independent of the magnitude of the power supply voltage. The NJM2903/2403 have unique characteristic: the input common-mode voltage range includes ground, even though operated from a single power supply voltage. Application areas include limit comparators, simple analog-to-digital converters; pulse, square-wave and time delay generators; wide range V<sub>CO</sub>; MOS clock timers; multivibrators and high voltage digital logic gates. The NJM2903/2403 were designed to directly interface with TTL and MOS. When operated from both plus and minus power supplies, the NJM2903/2403 will directly interface with MOS logic where their low power drain is a distinct advantage over standard comparators.

#### **■ PACKAGE OUTLINE**



NJM2903D/2403D ( DIP8 )



NJM2903M/2403M ( DMP8 )



NJM2903V/2403V (SSOP8)



NJM2903L/2403L (SIP8)



NJM2903E (SOP8)



NJM2903RB1 (MSOP8 (TVSP8))

#### **■ FEATURES**

Operating Voltage +2V~+36V

• Single Supply Operation

Open Collector Output

High Output Sink Current
 15mA (@ NJM2403)


Package Outline
 DIP8, DMP8, SIP8, SSOP8,

NJM2903 only: SOP8 JEDEC 150mil,


:MSOP8 (TVSP8) MEET JEDEC MO-187-DA/THIN TYPE

Bipolar Technology

#### **■ PIN CONFIGURATION**



NJM2903D/2403D, NJM2903M/2403M NJM2903V/2403V, NJM2903E/2903RB1




NJM2903L/2403L

#### **PIN FUNCTION**

- 1. A OUTPUT
- 2. A INPUT
- 3. A +INPUT
- 4. GND
- 5. B +INPUT
- 6. B INPUT
- 7. B OUTPUT

8. V<sup>+</sup>

■ EQUIVALENT CIRCUIT (1/2 Shown)



### NJM2903/2403

### ■ ABSOLUTE MAXIMUM RATINGS

(Ta=25°C)

PARAMETER	SYMBOL	RATINGS	UNIT	
Supply Voltage	V <sup>+</sup>	36 ( or ±18 )	V	
Differential Input Voltage	$V_{\text{ID}}$	36	V	
Input Voltage	V <sub>IN</sub>	-0.3~+36	V	
Power Dissipation	P <sub>D</sub>	( DIP8 ) 500 ( DMP8 ) 300 ( SSOP8 ) 250 ( SIP8 ) 800 (SOP8) 300 (MSOP8(TVSP8))320	mW	
Operating Temperature Range	T <sub>opr</sub>	-40~+85	°C	
Storage Temperature Range	T <sub>stg</sub>	-50~+125	°C	


### **■ ELECTRICAL CHARACTERISTICS**

( V<sup>+</sup>=5V,Ta=25°C )


PARAMETER	SYMBOL	TEST CONDITION	2903			2403			UNIT
TAIMILIER			MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	OIVII
Input Offset Voltage	V <sub>IO</sub>	R <sub>S</sub> =0Ω,V <sub>O</sub> =1.4V	-	-	7	-	-	10	mV
Input Offset Current	I <sub>IO</sub>		-	-	50	-	-	100	nΑ
Input Bias Current	$I_{B}$		-	30	250	-	40	500	nΑ
Input Common Mode Voltage Range	V <sub>ICM</sub>		0~3.5	-	-	0~3.5	-	-	V
Large Signal Voltage Gain	$A_{V}$	$R_L=15k\Omega$	-	106	-	-	106	-	dB
Response Time	$t_R$	$R_L=5.1k\Omega$	-	1.5	-	-	1.5	-	μs
Output Sink Current	I <sub>SINK</sub>	$V_{IN}^{-}=1V, V_{IN}^{+}=0V, V_{O}=1.5V$	6	-	-	20	-	-	mΑ
Output Saturation Voltage	$V_{SAT}$	$V_{IN}^{-}=1V, V_{IN}^{+}=0V, I_{SINK}=3mA$	-	200	400	-	-	-	mV
Output Saturation Voltage	$V_{SAT}$	V <sub>IN</sub> =1V,V <sub>IN</sub> +=0V,I <sub>SINK</sub> =15mA	-	-	-	-	200	400	mV
Output Leakage Current	I <sub>LEAK</sub>	$V_{IN}^{-}=0V, V_{IN}^{+}=1V, V_{O}=5V$	-	-	1.0	-	-	1.0	μA
Operating Current	I <sub>CC</sub>		-	0.4	1.0	-	0.5	1.5	mA

#### **■ TYPICAL CHARACTERISTICS**


### Input Bias Current vs. Temperature




#### Input Offset Voltage vs. Temperature




# Operating Current vs. Operating Voltage




# Input Bias Current vs. Operating Voltage



# NJM2903 Output Saturation Voltage vs. Output Sink Current



### NJM2403 Output Saturation Voltage vs. Output Sink Current



#### **■ TYPICAL CHARACTERISTICS**

The diagram of the di

Time  $t(\mu s)$ 

Response Time for Various Input Overdrives  $(V^{+}=5V, R_{L}=5.1k\Omega, T_{a}=25^{\circ}C)$   $V_{0}$   $V_{0}$   $V_{0}$   $V_{1N}$   $V_{2N}$   $V_{2N}$  V


# NJM2903 Output Saturation Voltage vs. Operating Voltage

3 k


10M

OUTPUT

51k **≥** 




# NJM2403 Output Saturation Voltage vs. Operating Voltage




#### **■ TYPICAL APPLICATIONS**

 $V_{REF}$ 

INPUT O







100k

100k

51 k



### Output Strobing Circuit



#### [CAUTION]

The specifications on this databook are only given for information, without any guarantee as regards either mistakes or omissions. The application circuits in this databook are described only to show representative usages of the product and not intended for the guarantee or permission of any right including the industrial rights.