
DURACELL®

CR 2025

Lithium/Manganese Dioxide Battery





Key Features

- Industry Highest Cell Capacity & High Energy
- High voltage response, stable during most of the lifetime of the application
- Reliable Performance
- Child-Safe Markings & Retail Packaging
- Wide operating temperature range (- 20°C / + 60°C)
- Low self-discharge with long operating life (<1% after 1 year of storage at + 20 °C)
- Excellent resistance to corrosion
- Designed to meet all major quality, safety and environment standards:
 - o Safety: IEC 60086-4
 - o Transport: UN 38.3
 - o REACH compliance
 - Quality: ISO 9001, Duracell World Class Continuous Program



Berkshire Corporate Park Bethel, CT. 06801 U.S.A. Telephone: Toll-free 1-800-544-5454 www.duracell.com

Electrical characteristics

•	Nominal capacity (15k Ohm Cont., 2.0 V cut-off)	165 mAh
•	Nominal voltage (at + 20 °C)	3.0 V
•	Standard Continuous Discharge Current	0.2 mA
•	Maximum Continuous Discharge Current	6 mA
•	Maximum Pulse Discharge Current at 1 sec	20 mA
•	Nominal Energy	495 mWh
•	AC Impedance @ 1kHz	24 Ohm

Physical characteristics

- Typical weight 2.56 g (.09 oz.)
- Li metal content approx. 0.052 g

Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.

CR2025PH0920

DURACELL®

CR 2025


Lithium/Manganese Dioxide Battery

Typical applications


- Medical devices
- Security devices
- Fitness devices
- Watches
- Calculators
- Wireless sensors
- Toys
- Key-Fobs & Trackers


Operating conditions

 Operating temperature range 	-20°C to 60°C (-4°F to 140°F)
 Storage temperatures Recommended 	5°C to 30°C (41°F to 86° F)









Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.

CR2025PH0920

DURACELL®

CR 2025

Lithium/Manganese Dioxide Battery

60086-4 © IEC:2007 Edition 3.0

Test	Test designation	Observation
А	Altitude	Pass
В	Thermal cycling	Pass
С	Vibration	Pass
D	Shock	Pass
E	External short circuit	Pass
F	Impact	Pass
G	Crush	Pass
Н	Forced discharge	Pass
I	Abnormal charging	Pass
J	Free fall	Pass
К	Thermal Abuse	Pass

Warning

Fire, explosion and burn hazard

Do not recharge, short circuit, crush, disassemble, heat above 100 $^{\circ}C$ (212 $^{\circ}F), incinerate, or expose contents to water$

Warning! Keep batteries away from children!

Always keep your batteries away from children to prevent swallowing. If ingestion does occur, however, be aware that initial symptoms may be similar to other childhood illnesses such as coughing, drooling and discomfort.

Battery ingestion hotline (1-800-498-8666)

Storage

The storage area should be clean, cool (preferably not exceeding +30 $^\circ C$), dry and ventilated



Berkshire Corporate Park Bethel, CT. 06801 U.S.A. Telephone: Toll-free 1-800-544-5454

www.duracell.com

CR2025PH0920