



#### **SPECIFICATIONS**

Model	Rated Torque	Damping Direction	Max Rotation Speed	Max Cycle Rate
FRN-P2-R501-G2	0.05±0.01Nm (0.5±0.1kgfcm)	Clockwise	50 RPM	10 cycles/ min.

Operating	Weight	Body & Cap	Rotating Shaft	Gear	Oil
Temperature		Material	Material	Material	Type
0 ~ 50°C	64g	Polybutylene terephthalate (PBT)	Metal (SUS)	Polyacetal (POM)	Silicone Oil

Note 1) Rated torque measured at a rotation speed of 20rpm at 23°C

Note 2) Gear model number has G1 at the end


Note 3) Torque can be customized by changing the oil viscosity

■ There are dampers that generate torque in both directions and one-way torque in the clockwise direction or counter clockwise direction when the rotating axle is viewed from the top


#### **GEAR SPECIFICATIONS**

Model	Туре	Tooth Profile	Module	Pressure Angle	Number of Teeth	Pitch Circle Diameter	Addendum Modification Coefficient
G2	Shifted Spur Gear	Involute	3.0	20°	13	ø39	+0.25

#### DAMPING CHARACTERISTICS




■ Speed characteristics: A rotary damper's torque varies according to the rotation speed. In general, as shown in the graph above, the torque increases as the rotation speed increases, and the torque decreases as the rotation speed decreases. In addition, please note that the starting torque slightly differs from the rated torque.




■ Temperature characteristics: A rotary damper's torque varies according to the ambient temperature. In addition, as shown in the graph above, the torque decreases as the ambient temperature increases, and the torque increases as the ambient temperature decreases. This is because the viscosity of the silicone oil inside the damper varies according to the temperature. When the temperature returns to normal, the torque will return to normal as well.

# **HOW TO ADJUST TORQUE**




Turn the adjustment knob clockwise to increase damper torque and counterclockwise to decrease it.

# **RANGE OF TORQUE ADJUSTMENT**



# **EXAMPLE OF USING A DAMPER**

Application of the FRN-P2 Series





### **OPTION RACK**

G1 Rack: ROP-020P2-1

Applicable Models: FRN-P2

\*Can be used with **G1** option **ONLY** 





There is no provision for option racks complying with the gear specification G2 (shifted spur gear) of FRN-P2