



3 Type

- A Exterior hinge wings
- I Interior hinge wings

4 Identification

- C With countersunk holes

Metric table

1		2		Dimensions in: millimeters - inches									
l_1		l_2	d_1	d_2	l_3	l_4	l_5	m_1		m_2	m_3	m_4	s
Type A	Type I							Type A	Type I				
72	86	82	6.6	14	40	36	43	40.8	55	42	-	-	3.5
2.83	3.39	3.23	0.26	0.55	1.57	1.42	1.69	1.61	2.17	1.65			0.14
72	86	162	6.6	14	80	36	43	40.8	55	-	50	32	3.5
2.83	3.39	6.38	0.26	0.55	3.15	1.42	1.69	1.61	2.17		1.97	1.26	0.14

Specification

- Body
Aluminum
Anodized finish, natural color **EL**
- Bearing bushing / cover cap
Plastic
Technopolymer (Polyamide PA)
Gray, RAL 7035
- Tapered dowel pin ISO 8741
Steel, zinc plated, blue passivated finish
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

Information

GN 2294 double winged lift-off hinges are made of drawn profiled aluminum and can be used on doors and covers.

External hinge wing, type A hinges, allow mounting with a very small door gap. Type I hinges are mounted between the door gap. This results in the mounting screws being hidden when the door is closed, which reduces the chance of vandalism.

The hinges are delivered loose and must be mounted according to the accompanying instructions. Any hinge combination may be created thanks to the modular design and available accessories.

see also...

- *Product Family Standard Parts for Profile Systems* → page 18
- *List of Hinge Types* → page 1324

On request

- Other lengths and hole spacings
- Other finishes

<p>How to order</p> <p>GN 2294-72-82-A-C-EL</p>	1	Width l_1
	2	Length l_2
	3	Type
	4	Identification
	5	Finish