


## PRODUCT DATA SHFFT

Part Number: 1901x25xWEC

Туре	Size	Rating	Description	
LED	M8	12Vdc	Superflat LED Indicator with Leads	

## Dimensions in mm (Not to scale)



Part Number	Colour	Voltage	Typ. Current (mA)	Typ. Luminous Intensity (mcd)
1901x253WEC	Red	12Vdc	20	13
1901x251WEC	Green	12Vdc	20	8
1901x252WEC	Yellow	12Vdc	20	8

x = 0: Satin chrome bezel x = 1: Black chrome bezel x = 2: Matt chrome bezel

## Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 The stated luminous intensity is for dc operation
- 3 Due to component tolerances, colour temperature variations may be observed
- 4 Storage temperature range: -25 °C to +80°C
- 5 Operating temperature range: -20 °C to +60°C
- 6 Sealed to IP67 above panel when the supplied gasket used
- 7 The plastic (polycarbonate) has limited chemical resistance
- 8 The plastic cartridge contains 3 wire exit holes the rear of the product is not sealed
- 9 Lead wires are internally soldered
- Lead wires: 7/0.2 (24 AWG) stranded copper, tinned annealed copper wire, PVC insulation
- 11 Marking: Part number, voltage rating, LED colour and date code
- 12 REACH SVHC compliant
- This product contains free-machining brass and is RoHS compliant via exemption clause Annex iii 6 (c) of EU Directive 2011/65/EU [Copper alloy containing lead up to 4% by weight]

Page 1 of 1 Issue 1: 19Feb20