

Label - MM-EMLF (EX14)R C1 WH/BK - 1116135

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Label, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 12 mm

Your advantages

- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- The self-adhesive material in continuous format is particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing



Key Commercial Data

| Packing unit | 1 pc |
|----------------------|-----------------|
| GTIN | 4 063151 040284 |
| GTIN | 4063151040284 |
| Custom tariff number | 96121010 |
| Country of origin | China |

Technical data

Dimensions

| Length (b) | 8 m |
|------------|-------|
| Width (a) | 14 mm |

Ambient conditions

| Ambient temperature (operation) | -20 °C 75 °C |
|---------------------------------|--------------|



Label - MM-EMLF (EX14)R C1 WH/BK - 1116135

Technical data

Ambient conditions

| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |
|--------------------------------|---|
| | packaging is recommended. |

General

| Color | white/black |
|-----------------------|--------------------------------|
| Components | Free from silicone and cadmium |
| Material | Vinyl polymer |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Marking mounting type | adhesive |

Environmental Product Compliance

| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|------------|---|
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| eCl@ss 9.0 | 27400629 |
|------------|-----------|
| 33.6333.3 | 2. 100020 |

Approvals

Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized



http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

MH48542

Phoenix Contact 2021 © - all rights reserved http://www.phoenixcontact.com