PCN Number: 202:		210713001.1		PCN Date:		ite:	July 20, 2021	
			litional Fab site (RFAB), Datasheet update and additional Assembly or select LBC7 devices					
Customer	Contact:		PCN Manager		Dept:			Quality Services
Proposed 1 st Ship Date:		Oct	. 20, 2021	Estimated Sample Availability:		nple	Date provided at sample request.	
Change Type:								
Assen	nbly Site		Assembly Process			\boxtimes	Assembly Materials	
Desig	n		\boxtimes	Electrical Specifica	ation	Mechanical Specification		anical Specification
Test S	Site		□ Packing/Shipping/Labeling				Test I	Process
Wafer Bump Site		Wafer Bump Material				Wafei	Bump Process	
		\boxtimes					Wafei	Fab Process
		Part number change			•			
PCN Details								

Description of Change:

Texas Instruments is pleased to announce the qualification of an additional fab (RFAB) and assembly (CDAT) site/BOM options for selected devices as listed below in the product affected section.

	Current Site		Additional Site		
Current Fab Site	Process	Wafer Diameter	Additional Fab Site	Process	Wafer Diameter
FFAB	LBC7	200mm	RFAB	LBC7	300mm

Construction differences are noted below:

Group 1 Adding RFAB + Clark adding CDAT A/T:

No Material differences between sites

Group 2 Adding RFAB + MLA adding CDAT A/T Site, BOM Change:

g turne : rient dading certi ri, r cito, e citanger				
	MLA	CDAT		
Mount Compound	4207768	4207123		
Mold Compound	4208625	4222198		

In addition, the datasheet number will be changing for the devices listed in group 3:

Device Family	Change From:	Change To:
TPS22930A	SLVSBL3C	SLVSBL3D

J i3	Texas
Y	Instruments

TPS22930

SLVSBL3D - NOVEMBER 2012 - REVISED JULY 2021

These changes may be reviewed at the datasheet links provided. https://www.ti.com/product/TPS22930

Qual details are provided in the Qual Data Section.

Reason for Change:

Continuity of Supply

Anticipated impact on Form, Fit, Function, Quality or Reliability (positive / negative): None

Anticipated impact on Material Declaration

 $\nabla \overline{1}$

No Impact to
the Material
Declaration

Material Declarations or Product Content reports are driven from production data and will be available following the production release. Upon production release the revised reports can be obtained from the TI ECO website.

Changes to product identification resulting from this PCN:

Fab Site Information:

Chip Site	Chip Site Origin Code (20L)	Chip Site Country Code (21L)	Chip Site City
FR-BIP-1	TID	DEU	Freising
RFAB	RFB	USA	Richardson

Assembly Site Information:

Assembly Site	Assembly Site Origin (22L)	Assembly Country Code (23L)	Assembly City
TI Malaysia	MLA	MYS	Kuala Lumpur
TI Clark	QAB	PHL	Angeles City, Pampanga
CDAT	CDA	CHN	Chengdu

Sample product shipping label (not actual product label)


TEXAS INSTRUMENTS

MADE IN: Malaysia
2DC: 2Q:

MSL 22 /260C/1 YEAR SEAL DT

MSL '2 /260C/1 YEAR SEAL DT MSL 1 /235C/UNLIM 03/29/04 OPT: 1TEM: 39

LBL: 5A (L)TO:3750



(1P) \$N74L\$07N\$R (Q) 2000 (D) 0336 (31T)LOT: 3959047MLA (4W) TKY(1T) 7523483S12 (P) (2P) REV: (V) 0035317 (20L) CSO: SHE (21L) CCO: USA (22L) ASO: MLA (23L) ACO: MYS

Product Affected:

Group 1 Device List: Adding RFAB + TI-Clark adding CDAT A/T Site					
TPS62175DQCR	TPS62175DQCT	TPS62177DQCR	TPS62177DQCT		

Group 2 Device List:	Adding RFAB + MLA adding CDAT A/T Site and BOM Change			
TCA6416ARTWR	TCA1116RTWR	TCA9539RTWR	TCA9555RTWR	

Group 3 Device List:	Adding RFAB Wafer	Fab site + Datasheet change
TPS22930AYZVR	TPS22930AYZVT	

Group 4 Device List: Adding RFAB Wafer Fab site					
TLV7031DCKT	TPS7A8701RTJT	TPS7A8801RTJR	TPS7A8801RTJT		
TPS7A8701RTJR					

Qualification Report

Approve Date 6-October-2010

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	Test Name / Condition	Duration	Qual Device: TPS51217DSC
ED	Electrical Characterization	Per Datasheet Parameters	Pass
HAST	Biased HAST, 130C/85%RH	96 Hours	3/231/0
AC	Autoclave, 121C	96 Hours	3/231/0
HBM	ESD - HBM	2000 V	3/9/0
CDM	ESD - CDM	500 V	3/9/0
HTOL	Life Test, 135C	635 Hours	3/231/0
HTSL	High Temp. Storage Bake, 170C	420 Hours	3/231/0
LU	Latch-up	(per JESD78)	3/18/0
TC	Temperature Cycle, -65/150C	500 Cycles	3/18/0

- Qual Device TPS51217DSC is qualified at LEVEL2-260C
- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles Quality and Environmental data is available at TI's external Web site: http://www.ti.com/

Green/Pb-free Status:

Qualified Pb-Free (SMT) and Green

Qualification Report Approve Date 02-June-2021

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	Test Name / Condition	Duration	Qual Device: TCA6416ARTWR	Qual Device: TCA9555RTWR	Qual Device: TCA1116RTWR	Qual Device: TCA9539RTWR	QBS Package Reference:	QBS Package Reference:
	Collaidoll		TONOTIONICITIE	TORDODORTHIC	TOATTION	TONOGOSKITTIK	THS4552IRTW	TMP116AIDRV
HAST	Biased HAST,	96 Hours	-	-	-	-	3/231/0	3/231/0
	130C/85%RH							
HTOL	Life Test, 150C	300 Hours	-	-	-	-	-	3/231/0
HTSL	High Temp Storage	420 Hours	-	-	-	-	3/231/0	-
	Bake 170C							
SD	Solderability	PB Free	-	-	-	-	2/44/0	-
TC	Temperature Cycle,	500 Cycles	-	-	-	-	3/231/0	3/231/0
	-65/150C							
UHAST	Unbiased HAST	96 Hours	-	-	-	-	3/231/0	3/231/0
	130C/85%RH						3/231/0	3/23/1/0
WBP	Bond Pull	Wires	1/30/0	1/30/0	1/30/0	1/30/0	-	-
WBS	Ball Bond Shear	Wires	1/30/0	1/30/0	1/30/0	1/30/0	-	-

- Qual Device TCA6416ARTWR is qualified at LEVEL2-260C
- Qual Device TCA9555RTWR is qualified at LEVEL2-260C
- Qual Device TCA1116RTWR is qualified at LEVEL2-260C
- Qual Device TCA9539RTWR is qualified at LEVEL2-260C
- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV: 125C/rk Hours, 140C/480 Hours.
 The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/rk Hours, and 170C/420 Hours.
 The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: http://www.ti.com/

Green/Pb-free Status:

Qualified Pb-Free (SMT) and Green

For questions regarding this notice, e-mails can be sent to the contacts shown below or your local Field Sales Representative.

Location	E-Mail
USA	PCNAmericasContact@list.ti.com
Europe	PCNEuropeContact@list.ti.com
Asia Pacific	PCNAsiaContact@list.ti.com
WW PCN Team	PCN www admin_team@list.ti.com

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.