Cornell Dubilier

Engineering


Cornell Dubilier Marketing, Inc Liberty, South Carolina TEL: 864-843-2277 FAX:864-843-3800

Catalog Number:<u>DCM152T450CC2B</u> Customer Part Number:<u>None</u> Date: <u>2/11/2010</u>

Capacitance: 1500μ F Tolerance: -10% + 50%Working Volts: 450 VDC Surge Volts: 500VDC Leakage Current @ 25° C: 4930μ A ESR @ 120 Hz @ 25° C: 0.078Ω max. Ripple Current @ 120 Hz, 85° C: 6.15A

Diameter (D): 2.50 ± 0.031 inches Length (L): 4.125 ± 0.062 inches Total Length, W/Insulation (TL): 4.376 ± 0.062 inches Terminal Spacing (S): 1.125 ± 0.015 inches Terminal Thread (T): 10-32 UNF Insulation: <u>PVC</u>

Operating Temperature: $-40^{\circ}C \sim +85^{\circ}C$



ROHS Compliant for all date codes after "0513", Per provisions of CD document 10-28.

"Controlled Copy" if viewed on CD Server or if copy is stamped in Red, Otherwise considered as an "Uncontrolled Copy"